SynFlex Elektro GmbH Auf den Kreuzen 24 D-32825 Blomberg Germany Telefon +49-5235-968-0 E-Mail info@synflex.de



Extruded Sleeving H

Sleeving H is an extruded silicone sleeving.

Attributes

Sleeving H is flexible, non-transparent and available in various colours. Due to the silicone rubber coating, this sleeving provides high permanent temperature resistance of class H (180 °C) and thermal resistance up to 200 °C; the special quality version guarantees thermal resistance up to 250 °C.

Application

Sleeving H is used as lightweight, additional mechanical protection for applications with very high thermal stress. Furthermore, it offers additional electrical insulation for cables and enamelled copper wires in electric machines and transformers as well as in certain electronic applications.

Standards

Acc. IEC 60684-123/124 UL 94HB compliant RoHS compliant according to 2011/65/EU

Delivery forms

Standard: transparent (inner diameter / ID 5)

Special colours on request:

Red, blue, white, black (ID5) and green (ID2)

Length in m on a cardboard ring:

0.3 - 2.0 mm 200 m rings/ cardboard spools

2.5 - 3.5 mm 100 m rings/ cardboard spools

4.0 - 9.0 mm 100 m rings

10.0 mm 50 m rings

Updated 04/19

14.0 - 30.0 mm on request

All dimensions can be delivered in adapted lengths.







SynFlex Elektro GmbH Auf den Kreuzen 24 D-32825 Blomberg Germany Telefon +49-5235-968-0 E-Mail info@synflex.de



	Unit of measure						
Inner diameter (ID)	mm	0.3	0.5	0.8+	1.0	1.5	2.0
Tolerance (ID)	mm	+0.10/-0.05	+0.15/-0.10	+0.15/-0.10	+0.20/-0.15	+0.20/-0.15	+0.20/-0.15

	Unit of measure						
Inner diameter (ID)	mm	2.5	3.0	4.0	5.0	6.0	8.0
Tolerance (ID)	mm	+0.20/-0.20	+0.20/-0.20	+0.20/-0.20	+0.20/-0.20	+0.25/-0.25	+0.25/-0.25

	Unit of measure						
Inner diameter (ID)	mm	10.0	12.0	16.0	20.0	25.0	30.0
Tolerance (ID)	mm	+0.25/-0.25	+0.25/-0.25	+0.50/-0.50	+0.50/-0.50	+0.50/-0.50	+0.50/-0.50

	Unit of measure						
Wall thickness (wt) nominal	mm	0.20	0.40	0.50	0.70	1.0	1.5
Tolerance (wt)	mm	-0.05/+0.15	-0.05/+0.15	0.05/0.15	-0.05/+0.15	-0.05/+0.15	-0.20/+0.20

The information on this data sheet is based on the information provided by our supplier. It does not represent any specification or agreements regarding conditions or properties. The indicated values are standard values. Deviations from those values due to production and application cannot be excluded. The information on this data sheet is addressed to experts who use it at their own discretion and at their own risk. We do not guarantee results, or accept liability for the indicated specifications or for results obtained based on the specifications. Please contact us for more detailed information. Non-toxic and toxic substances are listed on the safety data sheet.







SynFlex Elektro GmbH Auf den Kreuzen 24 D-32825 Blomberg Germany Telefon +49-5235-968-0 E-Mail info@synflex.de



		Conditions	Values	Test method	Values
Wall thickness (wt) nominal	2.0				
Tolerance (wt)	-0.20/+0.20				
Dielectric strength		appr. 1 / 0.1 mm wall thickness	DIN EN 60684		
Specific volume resistance	room temperature	min. 10^11	DIN EN 60684		
Resistance	weather, ozone, UV				

Products	Unit of measure	Values	Test method
Elongation at break	%	500 (min. 200)	DIN EN 60684
Tear force	MPa	11 (min. 5.5)	DIN EN 60684

Category	Unit of measure	Values
Thermal class	°C	180
Application range	°C	-60 up to 200 (special version up to 250)





