



**Product:** [83029](#)

Lead Wire, #18 Str SPC, TFE Ins, AWM 1180

[Request Sample](#)

**Product Description**

High Temp Plastic Lead Wire, 18AWG (19x30) Silver Plated Copper, TFE Insulation, AWM 1180 300V 200C TYPE EE MIL-W-16878/5 1000V 200C

**Technical Specifications**

**Product Overview**

Suitable Applications:	high temperature, inter-connection circuits, internal wiring of computer and electronic equipments, (Type EE) MIL-W-16878/5 applications
------------------------	--

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Conductors
18	19x30	SC - Silvered Copper	1

Conductor Count:	1
------------------	---

**Insulation**

Material	Nominal Diameter	Nominal Wall Thickness
PTFE - Polytetrafluoroethylene	0.0765 in	0.015 in

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR
5.75 Ohm/1000ft

**Current**

Element	Max. Recommended Current [A]
Mil-Std-975M Table 3.16 (single wire)	Mil-Std-975M Table 3.16 (single wire): 9.2 A

**Voltage**

UL Description	UL Voltage Rating
UL AWM 1180	300 V RMS
Mil-W-16878/5	1000 V RMS

**Temperature Range**

UL Temp Rating:	200°C
Operating Temp Range:	-70°C To +200°C

**Mechanical Characteristics**

Bulk Cable Weight:	8.5 lbs/1000ft
--------------------	----------------

**Standards**

UL AWM Style Compliance:	UL AWM Style 1180
NEMA Compliance:	HP3
Military Compliance:	MIL-W-16878/5

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

## Flammability, LSOH, Toxicity Testing

UL Flammability:	VW-1
UL voltage rating:	300 V RMS (UL AWM Style 1180)

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
83029 010500	Black			
83029 010100	Black	Reel	100 ft	612825353706
83029 0101000	Black	Reel	1,000 ft	612825399568
83029 006100	Blue, Light			612825354468
83029 006500	Blue, Light			612825353713
83029 0061000	Blue, Light	Reel	1,000 ft	612825354550
83029 001100	Brown	Reel	100 ft	
83029 0011000	Brown	Reel	1,000 ft	612825353737
83029 0081000	Gray			
83029 008100	Gray	Reel	100 ft	
83029 005100	Green, Dark	Reel	100 ft	612825354451
83029 005500	Green, Dark	Reel	500 ft	
83029 0051000	Green, Dark	Reel	1,000 ft	612825399551
83029 003100	Orange	Reel	100 ft	612825354154
83029 0031000	Orange	Reel	1,000 ft	
83029 002100	Red	Reel	100 ft	612825354178
83029 002500	Red	Reel	500 ft	
83029 0021000	Red	Reel	1,000 ft	612825399544
83029 007100	Violet	Reel	100 ft	
83029 0071000	Violet	Reel	1,000 ft	
83029 009500	White	Reel	500 ft	
83029 0091000	White	Reel	1,000 ft	612825354567
83029 004100	Yellow			612825353720
83029 0041000	Yellow	Reel	1,000 ft	

Footnote:	S - STRIPING ADDERS FOR TYPES E AND EE: 1, 2, 3 STRIPES. MINIMUM ORDER 10,000' PER STRIPE COMBINATION. (SEE STRIPING ADDER TABLE)
Footnote:	W - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 75'.

## History

Update and Revision:	Revision Number: 0.312 Revision Date: 07-26-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief

at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Belden Wire & Cable:

[83029 0091000](#) [83029 0101000](#) [83029 0011000](#) [83029 0051000](#) [83029 0081000](#) [83029 0031000](#) [83029 0021000](#)  
[83029 0071000](#) [83029 0041000](#) [83029 007100](#) [83029 003100](#) [83029 001100](#) [83029 002100](#) [83029 010100](#) [83029](#)  
[004100](#) [83029 005500](#) [83029 0061000](#) [83029 008100](#) [83029 010500](#) [83029 005100](#) [83029 006100](#)