



## 3601 - MALE STUD, BSP PARALLEL AND METRIC



<b>maximum working pressure</b>	30 bar 3 MPa 435 psi
<b>working temperature</b>	-25 to 150 °C -13 to 302 °F 248 to 423 °K
<b>vacuum capability</b>	755 mm Hg
<b>body</b>	FDA CHEMICAL NICKEL PLATED BRASS
<b>'O'-rings</b>	FKM
<b>collar</b>	FDA CHEMICAL NICKEL PLATED BRASS
<b>sealing washer</b>	FDA CHEMICAL NICKEL PLATED BRASS

Part Nb	ØD (MM)	C	E (mm)	(mm)	F2 (mm)	H (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾
3601 04 10	4	G1/8	5.5	13	3	14.5	.009
3601 04 13	4	G1/4	6.5	16	3	14.5	.015
3601 04 19	4	M5x0,8	3.5	10	2.5	15.5	.006
3601 04 52	4	M6x1	4.5	10	3	16	.006
3601 04 56	4	M8x1	5	11	3	14.5	.007
3601 06 10	6	G1/8	5.5	13	4	17.5	.011
3601 06 13	6	G1/4	6.5	16	4	17	.015
3601 06 19	6	M5x0,8	3.5	13	2.5	19	.01
3601 06 60	6	M10x1	5.5	13	4	17.5	.011
3601 08 10	8	G1/8	5.5	16	5	21	.014
3601 08 13	8	G1/4	6.5	16	6	18	.016
3601 08 17	8	G3/8	7.5	20	6	19	.028
3601 10 13	10	G1/4	6.5	18	7	25	.025
3601 10 17	10	G3/8	7.5	20	8	22.5	.028
3601 10 21	10	G1/2	9	24	8	22.5	.043
3601 12 13	12	G1/4	6.5	20	7	26.5	.03
3601 12 17	12	G3/8	7.5	20	9	26	.034
3601 12 21	12	G1/2	9	24	10	23.5	.042
3601 14 17	14	G3/8	7.5	22	9	28	.038
3601 14 21	14	G1/2	9	24	11	26.5	.045