



Описание

112-2 Dual Lens Inspection Camera - это оборудование инженерного класса с функцией просмотра видео в режиме реального времени, видеозаписи и захвата изображения и т.д., который подходит для использования в узких областях например: ремонт транспортных средств, осмотр / техническое обслуживание канализации и т. Д.

Параметры:

1. 4.3 " LCD Display
2. 1920*1080 pixel resolution, 70°/70° front/side (Total 140° viewing angle)
3. Focusing distance: 4cm-500cm
4. Waterproof level: IP67
5. High-intensity auxiliary light source: 6 adjustable LED lights for easy use in dark environments
6. Record video and take photos: The device can create high-definition photos and videos and save them in the SD card.
7. 3.7v 2600mAh rechargeable lithium battery

Technical indexes:

Infrared temperature measurement	
Resolution	1920*1080P
Monitor	4.3" LCD screen
Lens	Dual lens
Lens diameter	8mm
Front mirror	70°
Side mirror	70°
Hard wire	Flexible semi-rigid cable, freely deformable
Line length	5M
Focal length	4CM-500CM
Waterproof level	IP67 (only for lens/lamp)
Power charging interface	DC 5V input

TF card slot	MAX 64G (only support TF card in FAT32 format at level 10 or higher, normal shipment without TF card)
Battery	2600 mAh lithium battery