

Please download the latest datasheet of DLM0NSN900HY2# from the official website of Murata Manufacturing Co., Ltd.

https://www.murata.com/en-global/products/productdetail?partno=DLM0NSN900HY2%23

DLM0NSN900HY2#

"#" indicates a package specification code.

Note: This datasheet may be out of date








< List of part numbers with package codes > DLM0NSN900HY2B DLM0NSN900HY2D



Appearance & Shape









- 1. Small size and tight dimensional tolerance Size:0.85x0.65x0.45mm
- Tolerance:+-0.05mm
- 2. High common mode impedance up to 90ohm (at 100MHz) is available.
- DLMONSN series enables noise suppression for differential signal line without distortion in highspeed signal transmission due to its line impedance matching.
- 4. High Cut-off Frequency.



Limited Usage	For differential signal interface line
Other Usage	For general



Packaging Information

Packaging	Specifications	Minimum Order Quantity
В	Bulk(Bag)	500
D	180mm Paper Tape	10000

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated :2019/07/18



$\underline{\text{Co., Ltd.}} \\ \text{https://www.murata.com/en-global/products/productdetail?partno=DLM0NSN900HY2\%23} \\$

Note: This datasheet may be out of date

 $\underline{ \text{Please download the latest datasheet of DLM0NSN900HY2\# from the official website of Murata Manufacturing} \\$

DLM0NSN900HY2#

"#" indicates a package specification code.



Shape	SMD
Size Code (in mm)	0806
Size Code (in inch)	03025
Length	0.85mm
Length Tolerance	±0.05mm
Width	0.65mm
Width Tolerance	±0.05mm
Thickness	0.45mm
Thickness Tolerance	±0.05mm
Common Mode Impedance (at 100MHz)	90Ω
Common Mode Impedance (at 100MHz) Tolerance	±25%
Rated Current	100mA
Rated Voltage	5Vdc
Withstanding Voltage	12.5Vdc
DC Resistance(max.)	5Ω
DC Resistance	4.0Ω±25%
Insulation Resistance(min.)	10ΜΩ

Cut-off Frequency	2.0GHz (Typ.)
Operating Temperature Range	-40°C to 85°C
Mass(typ.)	0.9mg
Number of Circuit	1
Operating Temperature Range(Self-temperature rise is included)	No

2 of 3

Attention

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated :2019/07/18

^{1.} This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Note: This datasheet may be out of date


Please download the latest datasheet of DLM0NSN900HY2# from the official website of Murata Manufacturing


https://www.murata.com/en-global/products/productdetail?partno=DLM0NSN900HY2%23

DLM0NSN900HY2#


"#" indicates a package specification code.









Impedance-Frequency Characteristics







Differential Mode Transmission Characteristics (Typical Value)

Equivalent Circuit

3 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/