
Connector A: SMA Jack (Female Socket)				
Connector B: MMCX Plug (Male Pin)				
Connector B: IVIIVI	• ,			
Body Style	Straight			
	Connector A		Connector B	
Connector Part	Material	Finish	Material	Finish
Body	Brass	Gold	Brass	Gold
Center Contact	Be Cu	Gold	Be Cu	Gold
Insulator	PTFE	_	PTFE	-
Washer	_	_	Be Cu	Gold

	REVISIONS		
REV	DESCRIPTION	DATE	APPV
Α	INITIAL RELEASE OF LINX INTERNAL DRAWING	9-OCT-17	CLL
В	added additional specifications tables	17/JAN/19	SH



NOTES: (UNLESS OTHERWISE SPECIFIED)

- 1. ALL DIMENSIONS ARE IN mm [INCHES].
- 2. DIMENSIONS APPLY AFTER FINISHING.
- 3. MANUFACTURE TO BE COMPLIANT WITH EU ROHS DIRECTIVE, USE MATERIALS THAT DO NOT CONTAIN REACH SUBSTANCES OF VERY HIGH CONCERN >1000ppm, AND USE DRC CONFLICT-FREE SOURCED MATERIALS.
- 4. SAFETY BREAK ALL SHARP CORNERS AND EDGES 0.5 MAXIMUM.
- 5 SEE TABLE I FOR ELECTRICAL SPECIFICATIONS. (SHEET 2)
- SEE TABLE II FOR ENVIRONMENTAL SPECIFICATIONS. (SHEET 2)
- 7 SEE TABLE III FOR MECHANICAL SPECIFICATIONS. (SHEET 2)

WARNING: THIS DRAWING CONTAINS PROPRIETARY INFORMATION THAT IS THE SOLE PROPERTY OF LINX TECHNOLOGIES, AND SHALL BE TREATED AS SUCH. NO DISCLOSURE OR REPRODUCTION OF THIS DOCUMENT IS PERMITTED, IN WHOLE OR IN PART, WITHOUT THE EXPRESS WRITTEN PERMISSION OF LINX TECHNOLOGIES OR ITS

DESIGNATED AGENTS.			
MATERIAL:	5.00 [.200]-30.00 [1.200]=±0.40 30.0 [1.20]-120.0 [4.75]=±0.60 [0	TOLERANCES: 0.50 [.020]-5.00 [.200]=±0.20 [.008] 5.00 [.200]-30.00 [1.200]=±0.40 [.016] 30.0 [1.20]-120.0 [4.75]=±0.60 [0.24]	
	120.0 [4.75]-315.0 [12.40]=±1.0 [.040]		ANGLES: ±1°
FINISH:	DRAWN: M. SCHULTE	DT: 3	30/OCT/18

DT: 30/OCT/18 ENGR: D. VARATHARAJAN DT: 17/JAN/19

159 ORT LANE **MERLIN, OR 97532**

ADAPTER, SMA JACK (FEMALE SOCKET) TO MMCX PLUG (MALE PIN)

SIZE DWG. NO. REV ADP-SMAF-MMXM В SCALE: 3:1 SHEET 1 OF 2 DO NOT SCALE DRAWING



5 TABLE I

Electrical Data	Detail	
Impedance	50 Ω	
Frequency Range	0 to 6 GHz	
VSWR	≤ 1.2 : 1	
Insulation Resistance	5 000 M Ω min.	
Voltage Rating	170 V RMS	
	Connector A	Connector B
Contact Resistance, Center	10.0 m Ω max.	10.0 m Ω max.
Contact Resistance, Outer	5.0 m Ω max .	5.0 m Ω max .
Insertion Loss	0.06 dB max. x √f GHz	_
RF Leakage	-60 dB min. @ 3 GHz	_

6 TABLE II

Environmental Data	Detail
Corrosion (Salt spray)	ASTM B-117
Thermal Shock	MIL-STD-202 Method 107 test condition B
Vibration	MIL-STD-202 Method 204 test condition D
Mechanical Shock	MIL-STD-202 Method 213 test condition I
Temperature Range	-65 °C to +165 °C
Environmental Compliance	RoHS

7 TABLE III

Detail		
Free Hanging (In-Line)		
MIL-STD-348A & BS EN 122340		
3.8 g (0.13 oz)		
Connector A	Connector B	
1/4"-36 Threaded Coupling	"Push-Pull" Snap-on Coupling	
0.9 N·m (8 in·lbs)	_	
60 lbs. min.	-	
500 cycles min.	500 cycles min.	
	Free Hanging (In-Line) MIL-STD-348A & BS EN 1223-3.8 g (0.13 oz) Connector A 1/4"-36 Threaded Coupling 0.9 N·m (8 in·lbs) 60 lbs. min.	

SIZE	DWG	. NO.		REV
A ADP-SMAF-MMXM			В	
SCALE: 1:1 DO NOT SCALE DRAWING		SHEET 2	OF 2	