

Data sheet

Art.No.: 46.052.4553.1

Connector RST16I5 S S1 ZT6 SW

RST16i5 connector, 5 pole, male, screw connection, application 250/400V with PE, 16A, for cable diameters 7.1-13mm, coding color black, color of housing black



Art.No.	46.052.4553.1
EAN	4049088269219
Order Unit	1

Certificates / Approvals



LR RINA



Technical data

General

Rated current	16 A
Rated voltage	250 V / 400 V
Rated impulse voltage	4 kV
strain relief	Yes
Pollution degree	3
Lockable	self-locking (unlocking by hand)
Color of coding/ contact carrier	black
Marking of poles	1, 2, 3, N, PE
Color of housing inclusive strain relief	black

Connection Data

Cable diameter max.	13 mm
Cable diameter min.	7.1 mm
Connection cross section solid mm ² max.	2.5 mm ²
Connection cross section solid mm ² min.	0.25 mm ²
Connection cross section fine stranded mm ² max.	2.5 mm ²
Connection cross section fine stranded mm ² min.	0.25 mm ²
Terminations per pole	1
Connection cross section stranded mm ² min.	0.25 mm ²
Connection cross section stranded mm ² max.	2.5 mm ²
sheath strip length	25 mm
Wire strip length	8 mm

Model

Model	male
Connection type	Screw connection
Degree of protection (IP)	IP66/68 (3m;2h) /IP69

Material

Housing material	Polyamide
halogen free	Yes
Contact material	CuZn
Fire load	0.147 kWh
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	74 mm
Width	24 mm
Height	24 mm

Classification

ECLASS 8.1	27440605
ETIM 7.0	EC002560
ETIM 6.0	EC002560
ETIM 5.0	EC002560
ETIM 4.0	EC002560


Note

Note	fine-stranded and stranded wires have to be used without ferrules
------	---


A
These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

C
Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig


E
F




Kodierung/
coding




C1



C2





C3



C4

Auslieferungszustand
delivery condition



Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Die Reproduktion, Distribution und Nutzung dieses Dokuments sowie die Kommunikation mit anderen ohne ausdrückliche Genehmigung ist untersagt.

46.052.4553.9	RST16i5	S	S1	ZT6S	H	BL	C4	lichtblau/light blue
46.052.4550.4	RST16i5	S	S1	ZT6S	L	BR	C3	signalbraun/signal brown
46.052.4553.6	RST16i5	S	S1	ZT6S	A	TB	C2	türkisblau/turquoise blue
46.052.4553.1	RST16i5	S	S1	ZT6	SW		C1	schwarz/black
46.052.4553.0	RST16i5	S	S1	ZT6S	GL		C1	lichtgrau/light grey

Bestellnummer/ order number	Typ/type	Kodierung/c oding	Farbe/color
--------------------------------	----------	----------------------	-------------

Tolerierung Size ISO 14405 (E) / Tolerance system Size ISO 14405 (E).
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).
ja/yes Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed 1. Verwendung: First Use: Blatt: 1 von 1 Sheet: of 1

Werkstoff / Material	Tag/Date	Name	Zeichnung Nr. / Drawing No.	Index
Maßstab / Scale	gezeichnet/drawn	Treschan		
%	geprüft/checked		T 46.052.4553.013K	a
Vol.. --- mm ³	OfL./Surf. --- mm ²	Ersatz für / Replacement for:		
Maße in mm / Dimensions are in mm				

a	05.10.2016	www.wieland-electric.com	RST16	Steckerteil
Index	Datum / Blatt Date / Sheet			
Änderung / Revision		mit Zugentlastung, 5-polig, male connector with strain relief, 5 poles		