

LTC1540

with Reference

FEATURES


- Ultralow Quiescent Current: 0.3µA Typ
- Reference Output Drives 0.01µF Capacitor
- Adjustable Hysteresis
- Available in 3mm × 3mm × 0.8mm DFN Package
- Wide Supply Range: 2V to 11V
- Input Voltage Range Includes the Negative Supply
- Reference Output Sources Up to 1mA
- TTL/CMOS Compatible Outputs
- 60µs Propagation Delay with 10mV Overdrive
- No Crowbar Current
- 40mA Continuous Source Current
- Pin Compatible with LTC1440, MAX921, MAX931

APPLICATIONS

- Battery-Powered System Monitoring
- Threshold Detectors
- Window Comparators
- Oscillator Circuits

TYPICAL APPLICATION

Nanopower 2.9V V_{CC} Threshold Detector




DESCRIPTION

The LTC®1540 is an ultralow power, single comparator with built-in reference. The comparator's features include less than 0.6μ A supply current over the commercial temperature range, a $1.182V \pm 2\%$ reference, programmable hysteresis and TTL/CMOS outputs that sink and source current. The reference output can drive a bypass capacitor of up to 0.01μ F without oscillation.

Nanopower Comparator

The comparator operates from a single 2V to 11V supply or a dual \pm 1V to \pm 5.5V supply. Comparator hysteresis is easily programmed by using two resistors and the HYST pin. Each comparator's input operates from the negative supply to within 1.3V of the positive supply. The comparator output stage can continuously source up to 40mA. By eliminating the cross-conducting current that normally occur when the comparator changes logic states, power supply glitches are eliminated.

The LTC1540 is available in the 8-pin MSOP and SO packages. For space limited applications, the LTC1540 is available in a $3mm \times 3mm$ low profile (0.8mm) dual fine-pitch leadless package (DFN).



LTC1540 Supply Current vs Temperature


ABSOLUTE MAXIMUM RATINGS (Note 1)

Voltage

| ronago | | |
|------------------------------------|-----------------------|----------------------------------|
| V+to V ⁻ , V+ to GND, G | ND to $V^- \dots$ | 12V to -0.3V |
| IN⁺, IN⁻, HYST | (V+ + C | 0.3V) to (V ⁻ – 0.3V) |
| REF | (V+ + C | 0.3V) to (V ⁻ – 0.3V) |
| OUT | (V ⁺ + 0.3 | V) to (GND – 0.3V) |
| Current | , | , , , , |
| IN+, IN ⁻ , HYST | | 20mA |
| REF | | 20mA |
| OUT | | 50mA |
| | | |

| OUT Short-Circuit Duration (V $^+ \le 5.5$ V) Continuous Power Dissipation |
|--|
| Operating Temperature Range |
| LTC1540C 0°C to 70°C |
| LTC1540I–40°C to 85°C |
| Storage Temperature Range –65°C to 150°C |
| (DD Package)65°C to 125°C |
| Lead Temperature (Soldering, 10 sec) |

PIN CONFIGURATION



ORDER INFORMATION http://www.linear.com/product/LTC1540#orderinfo

| LEAD FREE FINISH | TAPE AND REEL | *PART MARKING | PACKAGE DESCRIPTION | TEMPERATURE RANGE |
|------------------|-------------------|---------------|--------------------------------|-------------------|
| LTC1540CDD#PBF | LTC1540CDD#TRPBF | LAAS | 8-Lead (3mm × 3mm) Plastic DFN | 0°C to 70°C |
| LTC1540IDD#PBF | LTC1540IDD#TRPBF | LAAS | 8-Lead (3mm × 3mm) Plastic DFN | -40°C to 85°C |
| LTC1540CS8#PBF | LTC1540CS8#TRPBF | 1540 | 8-Lead Plastic SO | 0°C to 70°C |
| LTC1540IS8#PBF | LTC1540IS8#TRPBF | 15401 | 8-Lead Plastic SO | -40°C to 85°C |
| LTC1540CMS8#PBF | LTC1540CMS8#TRPBF | LTCE | 8-Lead Plastic MSOP | 0°C to 70°C |
| LTC1540IMS8#PBF | LTC1540IMS8#TRPBF | LTADV | 8-Lead Plastic MSOP | -40°C to 85°C |

Consult LTC Marketing for parts specified with wider operating temperature ranges. *The temperature grade is identified by a label on the shipping container. For more information on lead free part marking, go to: http://www.linear.com/leadfree/

For more information on tape and reel specifications, go to: http://www.linear.com/tapeandreel/. Some packages are available in 500 unit reels through designated sales channels with #TRMPBF suffix.

ELECTRICAL CHARACTERISTICS The \bullet denotes the specifications which apply over the full operating temperature range, otherwise specifications are at $T_A = 25^{\circ}$ C. V⁺ = 5V, V⁻ = GND = 0V unless otherwise noted.

| SYMBOL | PARAMETER | CONDITIONS | | | MIN | ТҮР | MAX | UNITS |
|-------------------------|---|---|--|---|-------------------------|-------------------------|-------------------------|----------------|
| Power Su | ipply | | | | 1 | | | |
| V+ | Supply Voltage Range | | | ٠ | 2.0 | | 11.0 | V |
| I _{CC} | Supply Current | | V, HYST = REF, C-Grade V, HYST = REF, I-Grade | • | | 0.3 | 0.68 0.71 | μΑ μΑ |
| Compara | tor | | | | | | | |
| V _{OS} | Comparator Input Offset Voltage | V _{CM} = 2.5V LTC1540CMS8/I | MS8 | • | | | ±12 ±15 ±16 | mV mV mV |
| I _{IN} | Input Leakage Current (IN+, IN ⁻) Input Leakage Current (HYST) | $V_{IN}^{+} = V_{IN}^{-} = 2.5$ | V | • | | ±0.01 ±0.02 | ±1.0 ±1.0 | nA nA |
| V _{CM} | Comparator Input Common Mode Range | | | ٠ | V- | | V+-1.3V | V |
| CMRR | Common Mode Rejection Ratio | V ⁻ to V ⁺ – 1.3V | | | | 0.1 | 1 | mV/V |
| PSRR | Power Supply Rejection Ratio | V ⁺ = 2V to 11V | | | | 0.1 | 1 | mV/V |
| V _{HYST} | Hysteresis Input Voltage Range | | | ٠ | REF – 50mV | | REF | V |
| t _{PD} | Propagation Delay | C _{OUT} = 100pF | Overdrive = 10mV Overdrive = 100mV | | | 60 50 | | μs µs |
| V _{OH} | Output High Voltage | I ₀ = -13mA | | ٠ | V ⁺ - 0.4V | | | V |
| V _{OL} | Output Low Voltage | l ₀ = 1.8mA | | ٠ | | | GND + 0.4V | V |
| Referenc | e | | | | | | | |
| V _{REF} | Reference Voltage | No Load | (SO-8)/(DFN) Commercial MS8 Commercial (SO-8)/(MS8)/(DFN) Industrial | • | 1.158 1.156 1.152 | 1.182 1.182 1.182 | 1.206 1.208 1.212 | V V V |
| ΔV_{REF} | Load Regulation | $0 \le I_{\text{SOURCE}} \le 10$ | 0μΑ | • | | 0.5 | 2.5 | mV |
| | | $0 \le I_{SINK} \le 10\mu A$ | | • | | 0.5 | 1.5 5 | mV mV |

3


ELECTRICAL CHARACTERISTICS The \bullet denotes the specifications which apply over the full operating temperature range, otherwise specifications are at T_A = 25°C. V⁺ = 3V, V⁻ = GND = 0V unless otherwise noted.

| SYMBOL | PARAMETER | CONDITIONS | | | MIN | ТҮР | MAX | UNITS |
|-------------------|---|--|--|---|-------------------------|-------------------------|-------------------------|--------------------------|
| Power Su | ipply | _ | | | 1 | | | |
| V+ | Supply Voltage Range | | | | 2 | | 11 | ١ |
| I _{CC} | Supply Current | | (, HYST = REF, C-Grade /, HYST = REF, I-Grade | • | | 0.28 | 0.61 0.64 | μ <i>Α</i> μ <i>Α</i> |
| Compara | tor | | | | | | | |
| V _{OS} | Comparator Input Offset Voltage | V _{CM} = 2.5V LTC1540CMS8/IN | 158 | • | | | ±12 ±15 ±16 | mV mV mV |
| I _{IN} | Input Leakage Current (IN+, IN ⁻) Input Leakage Current (HYST) | $V_{IN}^{+} = V_{IN}^{-} = 1.5$ | 1 | • | | ±0.01 ±0.02 | ±1 ±1 | nA nA |
| V _{CM} | Comparator Input Common Mode Range | | | • | V- | | V+ – 1.3V | V |
| CMRR | Common Mode Rejection Ratio | V ⁻ to V ⁺ – 1.3V | | | | 0.1 | 1 | mV/V |
| PSRR | Power Supply Rejection Ratio | V ⁺ = 2V to 11V | | | | 0.1 | 1 | mV/V |
| V _{HYST} | Hysteresis Input Voltage Range | | | • | REF – 50mV | | REF | V |
| t _{PD} | Propagation Delay | C _{OUT} = 100pF | Overdrive = 10mV Overdrive = 100mV | | | 70 60 | | μs μs |
| V _{OH} | Output High Voltage | $I_0 = -8mA$ | | • | V+-0.4V | | | V |
| V _{OL} | Output Low Voltage | I ₀ = 0.8mA | | • | | | GND + 0.4V | V |
| Referenc | e | | | | | | | |
| V _{REF} | Reference Voltage | No Load | (SO-8)/(DFN) Commercial MS8 Commercial (SO-8)/(MS8)/(DFN) Industrial | • | 1.158 1.156 1.152 | 1.182 1.182 1.182 | 1.206 1.208 1.212 | V V V |
| ΔV_{REF} | Load Regulation | $0 \le I_{\text{SOURCE}} \le 100$ | μΑ | | | 0.75 | 3.5 | m٧ |
| | | $0 \le I_{SINK} \le 10 \mu A$ | | • | | 0.5 | 1.5 5 | m∨ mV |


Note 1: Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. Exposure to any Absolute Maximum Rating condition for extended periods may affect device reliability and lifetime.

Note 2: The θ_{JA} specified for the DD package is with minimal PCB heat spreading metal. Using expanded metal area on all layers of a board reduces this value.


TYPICAL PERFORMANCE CHARACTERISTICS




Reference Voltage Load Regulation (Source)





Comparator Short-Circuit Current vs Supply Voltage






Comparator Output Voltage (High) vs Load Current







Comparator Output Voltage (Low) vs Load Current



Comparator Response Time vs Input Overdrive



Hysteresis Control



PIN FUNCTIONS

GND (Pin 1): Ground. Connect to V^- for single supply operation.

V⁻ (**Pin 2**): Negative Supply. Potential should be more negative than GND. Connect to ground for single supply operation.

IN⁺ (Pin 3): Noninverting Comparator Input. Input common mode range from V⁻ to V⁺ – 1.3V. Input current typically 10pA at 25°C.

IN⁻ (Pin 4): Inverting Comparator Input. Input common mode range from V⁻ to V⁺ - 1.3V. Input current typically 10pA at 25°C.

HYST (Pin 5): Hysteresis Input. Connect to REF if not used. Input voltage range is from V_{REF} to $V_{REF} - 50$ mV.

REF (Pin 6): Reference Output. 1.182V with respect to V⁻. Can source up to 1mA and sink $10\mu A$ at 25°C. Drive 0.01 μ F bypass capacitor without oscillation.

APPLICATIONS INFORMATION

The LTC1540 is a nanopower comparator with a built-in 1.182V reference. Features include programmable hysteresis, wide supply voltage range (2V to 11V) and the ability of the reference to drive up to a 0.01μ F capacitor without oscillation. The comparator's CMOS outputs can source up to 40mA while supply current glitches that normally occur when switching logic states, have been eliminated.

Power Supplies


The comparator operates from a single 2V to 11V supply. The LTC1540 includes a separate ground for the comparator output stage, allowing a split supply ranging from \pm 1V to \pm 5.5V. Connecting V⁻ to GND will allow single supply operation. If the comparator output is required to source more than 1mA, or the supply source impedance is high, V⁺ should be bypassed with a 0.1µF capacitor.

Comparator Inputs

The comparator inputs can swing from the negative supply, V⁻, to within 1.3V (max) of the positive supply V⁺. The inputs can be forced 300mV below V⁻ or above V⁺ without damage and the typical input leakage current is only ± 10 pA.

V⁺ (Pin 7): Positive Supply operating voltage is from 2V to 11V.

OUT (Pin 8): Comparator CMOS Output. Swings from GND to V⁺. Output can source up to 40mA and sink 5mA.



Comparator Output

The comparator output swings between GND and V⁺ to assure TTL compatibility with a split supply. The output is capable of sourcing up to 40mA and sinking up to 5mA while still maintaining nanoampere quiescent currents. The output stage does not generate crowbar switching currents during transitions which helps minimize parasitic feedback through the supply pins.

Voltage Reference

The internal bandgap reference has a voltage of 1.182V referenced to V⁻. The reference accuracy is $\pm 2.0\%$ from 0°C to 70°C. It can source up to 1mA and sink up to 10µA with a 5V supply. The reference can drive a bypass capacitor of up to 0.01µF without oscillation and by inserting a series resistor, capacitance values up to 10µF can be used (Figure 1).

Figure 2 shows the resistor value required for different capacitor values to achieve critical damping. Bypassing the reference can help prevent false tripping of the comparators by preventing glitches on V⁺ or reference load transients from disturbing the reference output voltage.

APPLICATIONS INFORMATION




Figure 1. Damping the Reference Output




Figure 2. Damping Resistance vs Bypass Capacitor Value

Figure 3 shows the bypassed reference output with a square wave applied to the V⁺ pin. Resistors R2 and R3 set 10mV of hysteresis voltage band while R1 damps the reference response. Note that the comparator output doesn't trip.

Low Voltage Operation: V⁺ = 1.6V

The guaranteed minimum operating voltage is 2V (or $\pm 1V$). As the total supply voltage is reduced below 2V, the performance degrades and the supply current falls. At low supply voltages, the comparator's output drive is reduced and the propagation delay increases. The V_{REF} and V_{OS} are also slightly worse. The useful input voltage range extends from the negative supply to 0.9V below the positive supply. Test your prototype over the full temperature and supply voltage range if operation below 2V is anticipated. Because of the increase in supply current, operation below 1.5V is not recommended (Figure 4).




Figure 3a. Power Supply Transient Test Circuit




Figure 3b. Power Supply Transient Rejection




Figure 4. Supply Current vs Supply Voltage

APPLICATIONS INFORMATION

Hysteresis

Hysteresis can be added to the LTC1540 by connecting a resistor (R1) between the REF and HYST pins and a second resistor (R2) from HYST to V⁻ (Figure 5).

The difference between the upper and lower threshold voltages, or hysteresis voltage band (V_{HB}), is equal to twice the voltage difference between the REF and HYST pins.

When more hysteresis is added, the upper threshold increases the same amount as the low threshold decreases. The maximum voltage allowed between REF and HYST pins is 50mV, producing a maximum hysteresis voltage band of 100mV. The hysteresis band may vary by up to

TYPICAL APPLICATIONS

Level Detector

The LTC1540 is ideal for use as a nanopower level detector as shown in Figure 6. R1 and R2 form a voltage divider from V_{IN} to the noninverting comparator input. R3 and R4 set the hysteresis voltage, and R5 and C1 bypass the reference output. The following design procedure can be used to select the component values:

- 1. Choose the V_{IN} voltage trip level, in this example 4.65V.
- 2. Calculate the required resistive divider ratio.

Ratio = V_{REF}/V_{IN}

Ratio = 1.182V/4.65V = 0.254

3. Choose the required hysteresis voltage band at the input V_{HBIN} , in this example 60mV. Calculate the hysteresis voltage band referred to the comparator input V_{HB} .

 $V_{HB} = (V_{HBIN})(Ratio)$ $V_{HB} = (60mV)(0.254)$

 $V_{HB} = 15.24 \text{mV}$


4. Choose the values for R3 and R4 to set the hysteresis.

R4 = 2.4M


R3 (
$$k\Omega$$
) = 15 k , V_{HB} (mV) = 15 mV


5. Choose the values for R1 and R2 to set the trip point.

15%. If hysteresis is not wanted, the HYST pin should be shorted to REF. Acceptable values for I_{REF} range from 0.1µA to 5µA. If 2.4M is chosen for R2, then the value of R1 (k Ω) is equal to the value of V_{HB} (mV).











TYPICAL APPLICATIONS

3.3V Output Low Dropout Linear Regulator

The LTC1540 can be connected as a micropower ($I_Q = 5.5\mu$ A at $V_{IN} = 5V$) low dropout linear regulator (Figure 7). When the output is low, Q1 turns on, allowing current to charge output capacitor C1. Local feedback formed by R4, Q1 and Q2 creates a constant-current source from the 5V input to C1. R4, R1 and Q2's V_{BE} also provide current limiting in the case of an output short-circuit to ground. C2 reduces output ripple, while the R2-R3 feedback voltage divider establishes the output voltage.

Auto Power-Off Source

Figure 8 shows the circuit for a 30mA power supply that has a timed auto power-off function. The comparator output

is the switched power supply output. With a 10mA load, it typically provides a voltage of ($V_{BAT} - 0.17V$). The whole circuit draws a mere 0.8µA of quiescent current with $V_{BAT} = 5V$. The three resistor voltage divider programs 50mV of hysteresis for the comparator, and sets the IN⁻ voltage at 200mV. This gives an IN⁺ trip threshold of approximately 150mV

The RC time constant determines the maximum power-on time of the OUT pin before power down occurs. This period can be approximated by:

t = 4.6RC (seconds)

The actual time will vary with both the leakage current of the capacitor and the input current at the IN^+ pin.




Figure 7. 3.3V Output Low Dropout Linear Regulator




Figure 8. Auto Power-Off Switch Operates on 0.8µA Quiescent Current



TYPICAL APPLICATIONS

Low-Battery Detect

Figure 9 shows how to use the LTC1540 for a low-battery detect, drawing only $1.4\mu A$ at $V_{BAT} = 2V$. The circuit is powered by a 2-cell NiCd battery. The V_{BAT} pin could be as low as 1.6V when the batteries are completely depleted. The electrical specifications of the LTC1540 guarantee operation

down to a supply voltage of 2V, but it is still functional with the supply as low as 1.6V. Some parameters, such as V_{REF} and V_{OS} , will be degraded on lower supply voltages. The input voltage range extends from 0.9V below the positive supply to the negative supply.





Figure 9. Low-Battery Detect Works Down to 1.6V


PACKAGE DESCRIPTION

Please refer to http://www.linear.com/product/LTC1540#packaging for the most recent package drawings.



MS8 Package 8-Lead Plastic MSOP


(Reference LTC DWG # 05-08-1660 Rev G)



5. LEAD COPLANARITY (BOTTOM OF LEADS AFTER FORMING) SHALL BE 0.102mm (.004") MAX

PACKAGE DESCRIPTION

Please refer to http://www.linear.com/product/LTC1540#packaging for the most recent package drawings.



S8 Package

4. PIN 1 CAN BE BEVEL EDGE OR A DIMPLE

REVISION HISTORY (Revision history begins at Rev B)

| REV | DATE | DESCRIPTION | PAGE NUMBER |
|-----|-------|--|-------------|
| В | 08/17 | Reformatted Order Information. | 2 |
| | | Added web links. | All Pages |
| | | Add Information for analog devices. | All Pages |
| | | Corrected test conditions for supply current specification (I _{CC}). | 3 |

1540fb

TYPICAL APPLICATION

RF Field Detector

Figure 10 shows the complete circuit for a field detector which was tested at 445MHz. A transmission line is used to match the detector diode (1N5712) to a quarter-wave whip antenna. The 0.23 λ wavelength transmission line section transforms the 1pF (350 Ω) diode junction capacitance to a virtual short at the base of the antenna. At the same time it converts the received antenna current to a voltage loop at the diode, giving excellent sensitivity.

The rectified output is monitored by the LTC1540 comparator. The internal reference is used to set up a threshold of about 18mV at the inverting input. A rising edge at the comparator output triggers a one shot that temporarily enables answer back and any other pulsed functions.

The total supply current is 400nA. Among other monolithic one shots, the CD4047 draws the least amount of transient current.




Figure 10. Nanopower Field Detector

RELATED PARTS

| PART NUMBER | DESCRIPTION | COMMENTS |
|-----------------------------|---|---|
| LT®1178/LT1179 | Dual/Quad 17µA Precision Single Supply Op Amps | 70μV Max V _{OS} , 5nA Max I _{BIAS} |
| LT1351 | Single 250µA, 3MHz, 200V/µs Op Amp with Shutdown | C-Load [™] Op Amp Stable Driving Any Capacitive Load |
| LT1352/LT1353 | Dual/Quad 250µA, 3MHz, 200V/µs Op Amps | C-Load Op Amps Stable Driving Any Capacitive Load |
| LTC1440 | Micropower Comparator with 1% Reference | 1.182V ±1% Reference, ±10mV (Max) Input Offset |
| LTC1443/LTC1444/ LTC1445 | Micropower Quad Comparators with 1% Reference | LTC1443 Has 1.182V Reference, LTC1444/LTC1445 Have 1.221V Reference and Adjustable Hysteresis |
| LTC1474 | Low Quiescent Current High Efficiency Step-Down Converter | 10µA Standby Current, 92% Efficiency, Space Saving 8-Pin MSOP Package |
| LT1495 | 1.5µA Max, Dual Precision Rail-to-Rail Input and Output Op Amp | 375μV Max V _{OS} , 250pA I _{BIAS} , 25pA I _{OS} |
| LT1521 | 300mA Low Dropout Regulator with Micropower Quiescent Current and Shutdown | 0.5V Dropout Voltage, 12µA Quiescent Current, Adjustable Output 3V, 3.3V and 5V Fixed |
| LT1634 | Micropower Precision Shunt Voltage Reference | 1.25V, 2.5V, 4.096V, 5V Outputs, 10µA Operating Current, 0.05% Initial Accuracy 25ppm/°C Max Drift, SO-8, MSOP and TO-92 Packages |



