

TOLERANCE GENERAL: ±0.3
 GENERAL TOLERANCE: ±0.01



SPECIFICATIONS

• CONSTRUCTION

Miniature Tact switch for PC board.

• MATERIALS



Case : High temperature thermoplastic
 Contacts : Phosphor bronze, silver plated
 Actuator : Polyamide 6-6
 Terminals : Brass, silver plated

• ELECTRICAL CHARACTERISTICS

Electrical function : NO (Normally open)
 Maximum ratings : 50mA 12VDC
 Electrical life : 100 000 cycles
 Contact resistance : 100 milliohms Max
 Insulation resistance : 100 Megaohms min - 100 VDC
 Dielectric strength : 250 Vrms



• MECHANICAL AND ENVIRONMENTAL CHARACTERISTICS



Temperature range : -30°C to +80°C
 Operating force : 1.6±0.5N
 Travel : 0.30mm (.012)
 Axial static resistance : 40N max.
 Solder heat resistance : 255°C 5sec max.



SCHEMA ELECTRIQUE
(CIRCUIT DIAGRAM)

PERCAGE DU CIRCUIT
(P.C.B. LAYOUT)



				MATERIAL: /	 APEN UNISYS INTERRUPTEURS 26, Av. L. HERROU BP 1 62303 CHAUSSEE CEDIX 92463 SAS 1430 - (téléphone) 01 43 63 11 60	DRAWN: F. Ricard
				TREATMENT: /		DATE: 8-04-2002
				FINISH: /		CHECKED: 
				Scale: 3		Reference: DHA084S
						Code Nbr: /

PHAP3321
MINIATURE TACT SWITCH

Issue Modifications Date Name

This document is the property of APEN and may not be copied or used for any purpose without written authority. Dimensions and data shown in this specification are subject to change without notice.