



ENTRY LEVEL ACCESS CONTROL

Suitable for a variety of light-duty entry control applications in commercial and residential premises.

CL100

The CL100 range is available in three functions to suit a wide range of applications. The lock comes in two finishes and is excellent value for money. Delivered with random, unrecorded codes-ready to install. Change the code by following the clear instructions provided. Installation is simple; just drill one hole for the spindle, two holes for the fasteners and one extra if a mortise latch is required. Ideal for light-duty use for office doors, storage rooms, sheds, internal doors and cupboards at home.

FEATURES

- Simple, convenient control
- Easy to fit
- Three options available
- 8,191 non sequential codes available
- Choice of three latches - 2", 2³/₈" and 2³/₄" backset
- Tumbler alignment for easy code change
- Dual backplate allows option of hold /non-hold open
- Available in silver gray or polished brass finish
- Suitable for internal and external use
- Limited lifetime warranty*



CL100

Surface Deadbolt

Bolt slides on inside surface of the door, to lock or unlock. Bolt is moved manually by outside knob after code input and freely by inside knob at all times. Silver Gray finish only.



CL155

Tubular Latch

Supplied with 'hold open' option as standard, allowing free entry without inserting the access code. The option can be disabled on installation requiring code to be entered every time to open the door.

Easy Access

Staying in control has never been easier. CL100 locks can be used to restrict access in the home on doors, garages and garden sheds, and at work in offices, workshops and showrooms.

OPTIONS

Latch Options:

Light-duty with stainless steel latchbolt head, with 'anti-shim' plunger, 2³/₈" backset requires 1" edge and cross-bore hole, 3¹/₄" minimum door stile.

Also Available:

2" back-set latch requires 1" edge and cross-bore holes 2⁷/₈" minimum door stile. 2³/₄" back-set latch requires 1" edge and cross-bore holes 3⁵/₁₆" minimum door stile.


Back to Back Option (BB):

Two coded plates for installation on both sides of the door. Provides coded access in both directions.

Neoprene seals are included on both sides to provide friction against the face of the door and to avoid damage from over tightening of the fixing bolts.

For further product model options see price list.

PRODUCT DIMENSIONS



*Codelocks mechanical locks will be repaired, serviced or replaced free of charge if they develop a manufacturing fault. Faults caused by misuse, abuse and/or poor fitting are not covered by the warranty.



Code Change Method

Requires removal of lock from door. Locks are supplied with a random code commencing with the 'C' clear button. To change the code after fitting, the lock must first be removed from the door. The code is non sequential, i.e. the code can be entered in any preferred order (e.g. 1234 can be 4321 or 1342). A total of 8,191 different codes are available - any of which can be entered in any order.

TECHNICAL SPECIFICATIONS

Options	Three available
Spindle Type	Flat spring loaded spindle
Material	Zinc Alloy
Door Thickness	1 ³ / ₈ " - 2 ¹ / ₂ "
Buttons	14 stainless steel buttons
Non Handed	Locks will fit doors hung on the left or right
Fitting Options	Vertical
Finish	SG (silver gray) and PB (polished brass)
Codes	8,191 non sequential codes available
Code Storage	Single Code
Suitable For	Internal and external use

