

SEE SHEET 2 FOR CONTACT DIMENSION DETAILS

SPECIFICATIONS:

ELECTRICAL:

INSULATION RESISTANCE: DIELECTRIC WITHSTANDING VOLTAGE:

OPERATING TEMPERATURE:

WORKING VOLTAGE:

5 GOhms MIN. 1000 VAC FOR 1 MIN

250V

-55°C TO +125°C

POWER CONTACT RESISTANCE: 2.0 mOhms MAX. SIGNAL CONTACT RESISTANCE: 10 mOhms MAX. POWER CONTACT AMPERAGE: SEE P/N KEY SIGNAL CONTACT AMPERAGE: 5 AMPS

MECHANICAL:

CONTACT INSERTION FORCE: 4.5 Kg MAX. CONTACT SEPARATION FORCE: 0.3 Kg MIN.

MATERIALS:

CONTACTS: COPPER ALLOY, GOLD FLASH

INSULATOR:

PBT UL94V-0 RATED 230°C PROCESS TEMP.

SHELL:

NICKEL PLATED STEEL **NICKEL PLATED BRASS**

HARDWARE:

681M7W2103LYYY

0 = 40 AMP POWER // STANDARD PCB TAILS 1 = 40 AMP POWER // 2.22mm PCB TAILS 2 = 20 AMP POWER // STANDARD PCB TAILS

0 = NO HARDWARE

1 = 0.098" CN PCB SIDE

2 = 0.236" CN PCB SIDE

3 = 0.236" CN MATING SIDE

4 = 0.237" BOARDLOCK PCB SIDE

5 = 0.224" BOARDLOCK PCB SIDE

1 = GOLD FLASH -

ROHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DESCRIPTION: POWER / SIGNAL - VERTICAL - MALE - MACHINED

DRAWN: P. JENKINS DATE:

08/22/2011

UNITS = inches [mm]


DO NOT SCALE FROM DRAWING


REV

4

NorComp

WG NO.	681M	17V	V21	03L	YYY
NTS		1		3	
CALE:	SHEET		OF		





ROHS COMPLIANT

M

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: P. JENKINS

DATE: 08/22/2011

UNITS = inches [mm]

DO NOT SCALE FROM DRAWING

NorComp


681M7W2103LYYY


ALL CLINCH-NUTS ARE 4-40 INTERNAL THREADS


TOLERANCE:

ALL DIMENSIONS ARE ±0.010


0 NO HARDWARE









4 0.237" PCB SIDE




1 0.098" PCB SIDE



3 0.236" MATING SIDE



5 0.224" PCB SIDE



RoHS COMPLIANT



DRAWN: P. JENKINS

DATE: 08/22/2011 UNITS = inches [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE: SHEET 3 NTS 3 DWG NO. 681M7W2103LYYY

REV