

This document was generated on 04/01/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0449140601

Status: Active

Overview: Micro-Fit 3.0 Connector System Product Family

Description: Micro-Fit CPI Header, Capable Pin Interface, Dual Row, Vertical, 6 Circuits, Tin (Sn)

Plating, Glow-Wire Capable

Documents:

Drawing (PDF)Product Specification TS-43045-002-001 (PDF)3D ModelProduct Specification TS-46235-001-001 (PDF)Product Specification PS-43045 (PDF)Packaging Specification PK-70873-0314-001 (PDF)

Product Specification PS-43045-001 (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification TS-43045-001-001 (PDF)

Product Literature (PDF)

Agency Certification

CSA UL

General

Product Family Series

Application Tooling Part Link Application Tooling Part Link

Comments

Application

LR19980 E29179

PCB Headers

<u>44914</u>


Power, Wire-to-Board

62200-8400 62203-0455

"""""High Temperature|Square Pin<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glowwire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.""""""

"""""""High Temperature Square Pin<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:.

a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product



EU ELV Not Relevant

EU RoHS Compliant

REACH SVHC

Not Contained Per -ED/88/2018 (15 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit Contact US

China RoHS

China ROHS Green Image
ELV Not Relevant
ROHS Phthalates Not Contained

Search Parts in this Series

44914 Series

Mates With

430250600 Micro-Fit 3.0 Receptacle Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description Product #
Compliant Pin 622008400
Insertion Flat Rock

Tool

Removal Tool 622030455

end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for

possible product options.""""""

Overview <u>Micro-Fit 3.0 Connector System Product Family</u>

Product Literature Order No 987650-5984
Product Name Micro-Fit CPI
UPC 756054637661

Physical

Breakaway No
Circuits (Loaded) 6
Circuits (maximum) 6
Color - Resin Black
Durability (mating cycles max) 30
Flammability 94V-0
Glow-Wire Capable Yes

Material - Metal High Performance Alloy (HPA)

Material - Plating Mating Tin Material - Plating Termination Tin

Material - Resin High Temperature Thermoplastic

Net Weight 0.974/qNumber of Rows 2 Orientation Vertical **PCB** Locator Yes **PCB** Retention Yes Packaging Type Tray Pitch - Mating Interface 3.00mm 5.080µm Plating min - Mating Plating min - Termination 5.080µm Polarized to PCB Yes Shrouded Fully Stackable No Surface Mount Compatible (SMC) No

Temperature Range - Operating -40° to +105°C

Termination Interface: Style Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact 8.5A Voltage - Maximum 600V

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Packaging Specification PK-70873-0314-001

Product Specification PS-43045, PS-43045-001, TS-43045-001-001,

TS-43045-002-001, TS-46235-001-001

Sales Drawing SD-44914-002 Symbol/Footprint Data SYM-44914-0601

This document was generated on 04/01/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION