



4-9	4-3	4-5	2-9	2-3	2-5	1-8	1-3	1-6	3-9	3-2	3-5	1-9	1-2	1-5	DESCRIPTION / BENENNUNG	MATERIAL	SURFACE COLOR
															Pin contact HD.M	Brass	tin plated
		1													Pin contact HD.M	Brass	tin plated
			500	50											Pin contact HD.M	Brass	tin plated
					1										Pin contact HD.M	Brass	tin plated
						500	50								Pin contact HD.M	Brass	tin plated
								1							Pin contact HD.M	Brass	tin plated
									500	50					Pin contact HD.M	Brass	gold plated
											1				Pin contact HD.M	Brass	gold plated
												500	50		Pin contact HD.M	Brass	gold plated
													1		Pin contact HD.M	Brass	gold plated
															HD.M-C-Sti.Au.0,3-0,56 mm ²		
															HD.M-C-Sti.Au.0,3-0,56 mm ²		△
															HD.M-C-Sti.Au.0,3-0,56 mm ²		△
															HD.M-C-Sti.Au.0,8-1,5 mm ²		△
															HD.M-C-Sti.Au.0,8-1,5 mm ²		△
															HD.M-C-Sti.Au.0,8-1,5 mm ²		△
															HD.M-C-Sti.Sn.0,3-0,56 mm ²		△
															HD.M-C-Sti.Sn.0,3-0,56 mm ²		△
															HD.M-C-Sti.Sn.0,5-1,5 mm ²		△
															HD.M-C-Sti.Sn.0,5-1,5 mm ²		△
															HD.M-C-Sti.Sn.1,5-2,5 mm ²		△
															HD.M-C-Sti.Sn.1,5-2,5 mm ²		△
															HD.M-C-Sti.Sn.1,5-2,5 mm ²		△

- △1 Packaging 50
Packed in poly bag PN 0-1243085-8
- △2 Packaging 500
Packed in poly bag PN 0-1243085-8
- △3 Cut to 5000 loose pieces from roll
- △4 Cut to 4000 loose pieces from roll

Notes:
 1 For crimpdetails see AMP-SPEC. 114-19.000
 2 Meets productspecification 108-10042
 △5 0.40 max. gap between spring-nose and contact body.

<small>THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. DIESES ZEICHNUNGSDOKUMENT WIRD DURCH AMP INCORPORATED KONTROLLIERT. AENDERUNGEN, DIE DEM TECHNISCHEN FORTSCHRITT DIENEN, SIND VORBEHALTEN. DEN JEWELNS LETZTGUELTIGEN AENDERUNGSSTAND ERFAHREN SIE AUF ANFRAGE.</small>		DWN Schneider 19.10.01		HTS Elektrotechnik 53819 Neunkirchen, Germany	
<small>DIMENSIONS: DIMENSIONEN: mm</small> 		CHK Shweiger 19.10.01		NAME Pin contact Kontaktstift HD.M	
<small>TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN</small> <small>n. ISO 8015</small> <small>n. ISO 2768 - mH - E</small> <small>n. DIN 16901 - 140</small> 0 PLC # 1 PLC # 2 PLC # 3 PLC # <small>ANGLES /WINKEL #</small> <small>FINISH /OBERFLAECHE/FARBE</small>		APVD -	DRAWING NO ZEICHNUNGS-NR. A3 00779 C-1105000		
<small>MATERIAL</small>		PRODUCT SPEC PRODUKTSPEZ. -	SIZE A3	CAGE CODE 00779	RESTRICTED TO NUR FUER -
<small>APPLICATION SPEC VERARBEITUNGSSPEZ. -</small>		WEIGHT GEWICHT -	DRAWING NO ZEICHNUNGS-NR. A3 00779 C-1105000		REV A4
<small>CUSTOMER DRAWING</small>		/KUNDENZEICHNUNG		MASSSTAB 5:1	BLATT 1 OF VON 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1105000-3](#)