



PJA3440

40V N-Channel Enhancement Mode MOSFET


Voltage	40 V	Current	4.3A
----------------	-------------	----------------	-------------

Features

- $R_{DS(ON)}$, $V_{GS}@10V$, $I_D@4.3A < 42m\Omega$
- $R_{DS(ON)}$, $V_{GS}@4.5V$, $I_D@3.9A < 51m\Omega$
- Advanced Trench Process Technology
- Specially Designed for switch Load, PWM applications, and solid-state relays relay
- Lead free in compliance with EU RoHS 2011/65/EU directive
- Green molding compound as per IEC61249 Std. (Halogen Free)

Mechanical Data

- Case: SOT-23 Package
- Terminals : Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 0.0003 ounces, 0.0084 grams
- Marking: A40



Maximum Ratings and Thermal Characteristics ($T_A=25^\circ C$ unless otherwise noted)

PARAMETER		SYMBOL	LIMIT	UNITS
Drain-Source Voltage		V_{DS}	40	V
Gate-Source Voltage		V_{GS}	+20	V
Continuous Drain Current		I_D	4.3	A
Pulsed Drain Current ^(Note 4)		I_{DM}	17.2	A
Power Dissipation	$T_a=25^\circ C$	P_D	1.25	W
	Derate above $25^\circ C$		10	mW/°C
Operating Junction and Storage Temperature Range		T_J, T_{STG}	-55~150	°C
Typical Thermal resistance		$R_{\theta JA}$	100	°C/W
- Junction to Ambient ^(Note 3)				



PJA3440

Electrical Characteristics ($T_A=25^\circ\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNITS
Static						
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{GS}=0V, I_D=250\mu A$	40	-	-	V
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	1.0	1.5	2.5	V
Drain-Source On-State Resistance	$R_{DS(on)}$	$V_{GS}=10V, I_D=4.3A$	-	35	42	m Ω
		$V_{GS}=4.5V, I_D=3.9A$	-	44	51	
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=40V, V_{GS}=0V$	-	0.01	1	μA
Gate-Source Leakage Current	I_{GSS}	$V_{GS}=\pm 20V, V_{DS}=0V$	-	± 10	± 100	nA
Dynamic (Note 5)						
Total Gate Charge	Q_g	$V_{DS}=20V, I_D=4.3A,$ $V_{GS}=4.5V$ (Note 1,2)	-	4.8	-	nC
Gate-Source Charge	Q_{gs}		-	1.4	-	
Gate-Drain Charge	Q_{gd}		-	1.8	-	
Input Capacitance	C_{iss}	$V_{DS}=20V, V_{GS}=0V,$ $f=1.0\text{MHz}$	-	410	-	pF
Output Capacitance	C_{oss}		-	50	-	
Reverse Transfer Capacitance	C_{rss}		-	30	-	
Turn-On Delay Time	$t_{d(on)}$	$V_{DD}=20V, I_D=3.5A,$ $V_{GS}=10V,$ $R_G=1\Omega$ (Note 1,2)	-	4	-	ns
Turn-On Rise Time	t_r		-	30	-	
Turn-Off Delay Time	$t_{d(off)}$		-	15	-	
Turn-Off Fall Time	t_f		-	8	-	
Drain-Source Diode						
Maximum Continuous Drain-Source Diode Forward Current	I_S	---	-	-	1.0	A
Diode Forward Voltage	V_{SD}	$I_S=1.0A, V_{GS}=0V$	-	0.78	1.2	V
Reverse Recovery Time	t_{rr}	$V_{GS}=0V, I_S=3.5A$ $di_F/dt=100A/\mu s$	-	10.2	-	ns
Reverse Recovery Charge	Q_{rr}		-	5.5	-	nC

NOTES :

1. Pulse width $\leq 300\mu s$, Duty cycle $\leq 2\%$
2. Essentially independent of operating temperature typical characteristics.
3. $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins mounted on a 1 inch FR-4 with 2oz. square pad of copper.
4. The maximum current rating is package limited.
5. Guaranteed by design, not subject to production testing.



PJA3440

TYPICAL CHARACTERISTIC CURVES




Fig.1 On-Region Characteristics




Fig.2 Transfer Characteristics




Fig.3 On-Resistance vs. Drain Current




Fig.4 On-Resistance vs. Junction temperature




Fig.5 On-Resistance Variation with VGS.




Fig.6 Body Diode Characteristics



PJA3440

TYPICAL CHARACTERISTIC CURVES




Fig.7 Gate-Charge Characteristics




Fig.8 Threshold Voltage Variation with Temperature.




Fig.9 Capacitance vs. Drain-Source Voltage.




PJA3440

PART NO PACKING CODE VERSION

PART NO PACKING CODE	Package Type	Packing type	Marking	Version
PJA3440_R1_00001	SOT-23	3K pcs / 7" reel	A40	Halogen free
PJA3440_R2_00001	SOT-23	12K pcs / 13" reel	A40	Halogen free

MOUNTING PAD LAYOUT





PJA3440

Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panjit:](#)

[PJA3440_R1_00001](#) [PJA3440_R2_00001](#)