Vishay Dale Thin Film




Precision Thin Film Non-Magnetic Resistor, Surface Mount Chip, ± 25 ppm/°C, Tolerances to 0.1 %



These devices eliminate materials that would disturb magnetic fields applications such as in MRI magnetic resonance imaging machines. The PNM series chip resistor has been carefully engineered with non-magnetic materials to eliminate the effects of these stray magnetic fields on circuit performance, thereby resulting in simplified shielding requirements and improved sound quality in audio applications. Providing signal conditioning without distortion from magnetic fields.

CONSTRUCTION



FEATURES

- Non-magnetic
- Moisture resistant
- High purity alumina substrate · Non-standard values available
- MIL-STD-202 method
- 106 moisture resistance with 10 % power
- 100 % visual inspected per MIL-PRF-55342
- Very low noise and voltage coefficient (< -30 dB)
- Non-inductive
- Laser-trimmed tolerances to ± 0.1 %
- Wraparound resistance less than 10 mΩ
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

Note

This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

TYPICAL PERFORMANCE

	ABSOLUTE	
TCR	25	
TOL.	0.1	

STANDARD ELECTRICAL SPECIFICATIONS				
TEST	SPECIFICATIONS	CONDITIONS		
Material	Tantalum nitride	-		
Resistance Range	10 Ω to 3 MΩ	-		
TCR: Absolute	± 25 ppm/°C to ± 100 ppm/°C	-55 °C to +125 °C		
Tolerance: Absolute	± 0.1 % to ± 1.0 %	+25 °C		
Stability: Absolute	$\Delta R \pm 0.03 \%$	-		
Stability: Ratio	-	-		
Voltage Coefficient	0.1 ppm/V	-		
Working Voltage	75 V to 200 V	-		
Operating Temperature Range	-55 °C to +155 °C	-		
Storage Temperature Range	-55 °C to +155 °C	-		
Noise	< -30 dB	-		
Shelf Life Stability: Absolute	-	-		

COMPONENT RATINGS						
CASE SIZE ⁽¹⁾	POWER RATING (mW)	WORKING VOLTAGE (V)	RESISTANCE RANGE (Ω)			
0402	50	75	20 to 35K			
0502	100	75	20 to 65K			
0505	150	75	20 to 130K			
0603	150	75	10 to 130K			
0805	200	100	10 to 301K			
0705	200	100	10 to 301K			
1005	250	100	10 to 301K			
1010	500	150	50 to 600K			
1206	400	200	10 to 1M			
1505	400	150	10 to 1M			
2208	750	150	10 to 1.75M			
2010	800	200	10 to 2M			
2512	1000	200	10 to 3M			

Note

⁽¹⁾ 0705 and 0805 are the same (only use 0805 when ordering)

Revision: 13-Sep-2018

Document Number: 60057



RoHS

HALOGEN

FREE

PNM




www.vishay.com

Vishay Dale Thin Film

PNM

DIMENSIONS in inches



<i>←</i> ↓						
CASE SIZE	L	w	т	D	E	
0402	0.042 ± 0.008	0.022 ± 0.005	0.012 to 0.033	0.010 ± 0.005	0.010 ± 0.005	
0502	0.055 ± 0.006	0.025 ± 0.005	0.012 to 0.033	0.010 ± 0.005	0.015 ± 0.005	
0505	0.055 ± 0.006	0.050 ± 0.005	0.012 to 0.033	0.010 ± 0.005	0.015 ± 0.005	
0603	0.064 ± 0.006	0.032 ± 0.005	0.020 Max.	0.012 ± 0.005	0.015 ± 0.005	
0705, 0805 ⁽¹⁾	0.080 ± 0.006	0.050 ± 0.005	0.015 to 0.033	0.015 ± 0.005	0.015 ± 0.005	
1005	0.105 ± 0.007	0.050 ± 0.005	0.015 to 0.033	0.015 ± 0.005	0.015 ± 0.005	
1010	0.105 ± 0.007	0.100 ± 0.005	0.015 to 0.033	0.015 ± 0.005	0.015 ± 0.005	
1206	0.126 ± 0.008	0.063 ± 0.005	0.015 to 0.033	0.020 + 0.005/- 0.010	0.020 + 0.005/- 0.010	
1505	0.155 ± 0.007	0.050 ± 0.005	0.015 to 0.033	0.015 ± 0.005	0.015 ± 0.005	
2010	0.209 ± 0.009	0.098 ± 0.005	0.015 to 0.033	0.020 ± 0.005	0.020 ± 0.005	
2208	0.230 ± 0.007	0.075 ± 0.005	0.015 to 0.033	0.020 ± 0.005	0.020 ± 0.005	
2512	0.259 ± 0.009	0.124 ± 0.005	0.015 to 0.033	0.020 ± 0.005	0.020 ± 0.005	

Note


 $^{(1)}\,$ 0705 and 0805 are the same (only use 0805 when ordering)

ENVIRONMENTAL TESTS (Vishay Performance vs. MIL-PRF-55342 Requirements)					
ENVIRONMENTAL TEST		LIMITS MIL-PRF-55342 CHARACTERISTIC "H"	TYPICAL VISHAY PERFORMANCE		
Resistance Temperature Characteristic		± 50 ppm/°C	± 35 ppm/°C		
Max. Ambient Temperature at Rated Wattage		+70 °C	+70 °C		
Max. Ambient Temperature at Power Derating		+150 °C	+150 °C		
Thermal Shock	Δ R	± 0.25 %	± 0.040 %		
Low Temperature Operation	Δ R	± 0.25 %	± 0.005 %		
Short Time Overload	Δ R	± 0.10 %	± 0.010 %		
High Temperature Exposure	Δ R	± 0.20 %	± 0.150 %		
Resistance to Bonding Exposure	Δ R	± 0.25 %	± 0.005 %		
Moisture Resistance	Δ R	± 0.40 %	± 0.029 %		
Life + 70 °C at 1000 hours	Δ R	± 0.50 %	± 0.03 %		
Insulation Resistance		10 000 Ω minimum	> 100 000 MΩ		

2

For technical questions, contact: <u>thinfilm@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u> www.vishay.com

Vishay Dale Thin Film



GLOBAL PART NUMBER INFORMATION						
P	P N M 1 2 0 6 E 1 0 0 2 B B T 1					
GLOBAL MODEL	CASE SIZE	TCR CHARACTERISTIC	RESISTANCE	TOLERANCE	TERMINATION	PACKAGING
PNM non- magnetic resistor	0402 0502 0505 0603 0805 1005 1010 1206 1505 2208 2010 2512	E = 25 ppm (<i>R</i> > 100 Ω) H = 50 ppm (<i>R</i> > 50 Ω) K = 100 ppm (<i>R</i> > 10 Ω)	The first 3 digits are significant figures and the last digit specifies the number of zeros to follow. "R" designates the decimal point. Example: $10R0 = 10 \Omega$ $1000 = 100 \Omega$ $1001 = 1 k\Omega$		B = wraparound Sn/Pb solder 63 % Sn/ 37 % Pb S = wraparound lead (Pb)-free solder 96.5 % Sn/3.0 % Ag/ 0.5 % Cu RoHS compliant - e1	BS = BULK 100 min., 1 mult WS = WAFFLE 100 min., 1 mult TAPE AND REEL T0 = 100 min., 100 mult T1 = 1000 min., 1000 mult ⁽²⁾ T3 = 300 min., 300 mult T5 = 500 min., 500 mult TF = Full reel TS = 100 min., 1 mult

Notes

 $^{(1)}~$ B = 0.1 % tolerance available only above 100 Ω

⁽²⁾ Preferred packaging code



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

PNM0603E1002BST	5 PNM0603E2001BST	5 PNM0603E2502BST	5 PNM0603E5001BST	5 PNM0603E5002BST5
PNM0805E1001BST5	PNM0805E1002BST5	PNM0805E1003BST5	PNM0805E2002BST5	PNM0805E2502BST5
PNM0805E5001BST5	PNM0805E5002BST5	PNM1206E1001BST5	PNM1206E1002BST5	PNM1206E1003BST5
PNM1206E1004BST5	PNM1206E2502BST5	PNM1206E5001BST5	PNM1206E5002BST5	PNM0603E1002BST1
PNM0603E2001BST1	PNM0603E2502BST1	PNM0603E5001BST1	PNM0603E5002BST1	PNM0805E1000JBT0
PNM0805E1001BST1	PNM0805E1001JBT0	PNM0805E1002BST1	PNM0805E1003BST1	PNM0805E1003JBT0
PNM0805E2002BST1	PNM0805E2002FBT0	PNM0805E2502BST1	PNM0805E5001BST1	PNM0805E5002BST1
PNM1206E1001BST1	PNM1206E1002BST1	PNM1206E1003BST1	PNM1206E1004BST1	PNM1206E1004JBT0
PNM1206E16R7JBT0	PNM1206E2001BST1	PNM1206E2002BST1	PNM1206E2502BST1	PNM1206E5001BST1
PNM1206E5002BST1	PNM0402E5000BST1	PNM0402E5001BST1	PNM0402E2502BST1	PNM0402E1002BST1
PNM0402E1000BST1	PNM0402E3502BST1	PNM1206E33R0FST1		