

## **Piezoelectronic Buzzers**

Pin terminal/Lead Without oscillator circuit

## PS series

Issue date: August 2010

<sup>•</sup> All specifications are subject to change without notice.

<sup>•</sup> Conformity to RoHS Directive: This means that, in conformity with EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.



# Piezoelectronic Buzzers(without circuit) PS Series(Pin Terminal/Lead)

## **Conformity to RoHS Directive**


### **FEATURES**

- The PS series are high-performance buzzers that employ unimorph piezoelectric elements and are designed for easy incorporation into various circuits.
- They feature extremely low power consumption in comparison to electromagnetic units.
- Because these buzzers are designed for external excitation, the same part can serve as both a musical tone oscillator and a buzzer
- They can be used with automated inserters. Moisture-resistant models are also available.
- The lead wire type(PS1550L40N) with both-sided adhesive tape installed easily is prepared.

### **APPLICATIONS**

Electric ranges, washing machines, computer terminals, various devices that require speech synthesis output.

### **SOUND MEASURING METHOD**



#### SPECIFICATIONS AND CHARACTERISTICS

		External dimensions			Characteristics	Characteristics		
Type	Part No.	Outer diameter	Height	Pitch	Sound pressure	Frequency	Input voltage	
		(mm)	(mm)	(mm)	(dB(A)/10cm)	(kHz)	(Vo-p)[Rectangular wave]	
PS12 Type	PS1240P02BT	ø12.2	6.5	5	70 min.	4	3	
	PS1240P02CT3	ø12.2	3.5	5	60 min.	4	3	
DC14 Tupo	PS1440P02BT	ø14	8	5	75 min.	4	3	
PS14 Type	PS1420P02CT	ø14	11	5	70 min.	2	5	
	PS1720P02	ø17	8	10	70 min.	2	3	
PS17 Type	PS1740P02E	ø17	7.5	10	75 min.	4	3	
	PS1740P02CE	ø17	4.6	10	60 min.	4	3	
PS19 Type	PS1927P02	ø19	10.5 [excluding terminal]	20	90 min.	2.7	10	
	PS1920P02	ø19	10.5 [excluding terminal]	20	80 min.	2	10	
Others	PS1550L40N	ø15	1.6	<ul> <li>Depend on the installation condition</li> </ul>				
Туре	Part No.	Applications		Features				
D040 T	PS1240P02BT	•		• Compact	Automatic mountal	ole • 12.7mm p	oitch radial taping	
PS12 Type	PS1240P02CT3			Thin type • Automatic mountable • 12.7mm pitch radial taping				
DO44 T	PS1440P02BT	J	d alarm sounds of	High sound pressure				
PS14 Type	PS1420P02CT	• • • • • • • • • • • • • • • • • • • •	es(air conditioners,	• Low frequency tone • Automatic mountable • 15mm pitch radial taping				
	PS1720P02	— reirigerators, ia — cordless teleph	n forced heaters,	Low frequency tone				
PS17 Type	PS1740P02E	— cordiess telepir	ones, etc.)	High sound pressure				
	PS1740P02CE	<del></del>		• Thin type				
	PS1927P02	For potted circu	iit (washing	High sour	nd pressure • Water-	proof processir	ng element	
PS19 Type	PS1920P02		machines, drying machines, hot water supply systems, etc.)		Low frequency tone       Water-proof processing element			
Others	PS1550L40N	Digital camera		Compact	mpact, Thin type • Fix in both-sided adhesive tape			

• Conformity to RoHS Directive: This means that, in conformity with EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.




5000

10000

## **PIN TERMINAL TYPE PS12 TYPE** PS1240P02BT **FEATURES**

- Miniature size(ø12.2×T6.5mm).
- · High cost performance.
- Suitable for automatic radial taping machine(12.7mm-pitch).

### SHAPES AND DIMENSIONS






### **SPECIFICATIONS AND CHARACTERISTICS**

Sound pressure		70dBA/ 10cm min.	[at 4kHz, 3V <sub>0-P</sub> rectangular wave, measuring temperature: 25±5°C, humidity: 60±10%]
Temperature	Temperature Operating		_
range	Storage	−30 to +80°C	
Maximum input voltage		30V <sub>0-P</sub> max.	[without DC bias]
Minimum delivery unit		2500 pieces	[500 pieces/1 reel×5 reels]

#### FREQUENCY SOUND PRESSURE CHARACTERISTICS **SINE WAVE DRIVE SQUARE WAVE DRIVE**




## PS1240P02CT3

## **FEATURES**

- Thin type(ø12.2×T3.5mm).
- Suitable for automatic radial taping machine(12.7mm-pitch).

## **SHAPES AND DIMENSIONS**









## **SPECIFICATIONS AND CHARACTERISTICS**

Sound pressure		60dBA/ 10cm min.	[at 4kHz, 3Vo-P rectangular wave, measuring temperature: 25±5°C, humidity: 60±10%]
Temperature Operating		−20 to +70°C	
range	Storage	−30 to +80°C	
Maximum input voltage		30V <sub>0-P</sub> max.	[without DC bias]
Minimum delivery unit		2500 pieces	[500 pieces/1 reel×5 reels]








## PS14 TYPE PS1440P02BT

## FEATURESHigh sound pressure.

- Miniature size(ø14×T8mm).
- Suitable for automatic radial taping machine(15mm-pitch).

## **SHAPES AND DIMENSIONS**






## PS1420P02CT FEATURES

- Low frequency tone(2kHz).
- Suitable for automatic radial taping machine(15mm-pitch).

## **SHAPES AND DIMENSIONS**







### **SPECIFICATIONS AND CHARACTERISTICS**

Sound pressure		75dBA/ 10cm min.	[at 4kHz, 3V <sub>0-P</sub> rectangular wave, measuring temperature: 25±5°C, humidity: 60±10%]
Temperature Operating		–20 to +70°C	
range Storage		−30 to +80°C	
Maximum input voltage		30V <sub>0-P</sub> max.	[without DC bias]
Minimum delivery unit		1750 pieces	[350 pieces/1 reel×5 reels]


## FREQUENCY SOUND PRESSURE CHARACTERISTICS SINE WAVE DRIVE SQUARE WAVE DRIVE






## **SPECIFICATIONS AND CHARACTERISTICS**

70dBA/ 10cm min.	[at 2kHz, 5Vo-P rectangular wave, measuring temperature: 25±5°C, humidity: 60±10%]
−20 to +70°C	
–30 to +80°C	
30V <sub>0-P</sub> max.	[without DC bias]
1750 pieces	[350 pieces/1 reel×5 reels]
	10cm min. 1 –20 to +70°C –30 to +80°C 30Vo-P max.






<sup>•</sup> All specifications are subject to change without notice.

## **ATDK**

## PS17 TYPE PS1720P02 FEATURES

- Low frequency tone.
- · High sound pressure.

## **SHAPES AND DIMENSIONS**







## **SPECIFICATIONS AND CHARACTERISTICS**

Sound pressure		70dBA/ 10cm min.	[at 2kHz, 3Vo-P rectangular wave, measuring temperature: 25±5°C, humidity: 60±10%]
Temperature Operating		–20 to +70°C	
range	Storage	−30 to +80°C	
Maximum input voltage		30V <sub>0-P</sub> max.	[without DC bias]
Minimum delivery unit		1500 pieces	

## FREQUENCY SOUND PRESSURE CHARACTERISTICS SINE WAVE DRIVE SQUARE WAVE DRIVE






## PS1740P02E

## **FEATURES**

· High sound pressure.


## **SHAPES AND DIMENSIONS**






## **SPECIFICATIONS AND CHARACTERISTICS**

Sound pressure  Temperature Operating		75dBA/ 10cm min.	[at 4kHz, 3Vo-P rectangular wave, measuring temperature: 25±5°C, humidity: 60±10%]
		−20 to +70°C	
range	Storage	−30 to +80°C	
Maximum input voltage		30V <sub>0-P</sub> max.	[without DC bias]
Minimum delivery unit		1500 pieces	








## PS17 TYPE PS1740P02CE FEATURES

• Thin type.

## **SHAPES AND DIMENSIONS**







### **SPECIFICATIONS AND CHARACTERISTICS**

Sound pressure		60dBA/ 10cm min.	[at 4kHz, 3V <sub>0-P</sub> rectangular wave, measuring temperature: 25±5°C, humidity: 60±10%]
Temperature Operating		−20 to +70°C	<u> </u>
range	Storage	−30 to +80°C	<del>-</del>
Maximum input voltage		30V <sub>0-P</sub> max.	[without DC bias]
Minimum delivery unit		1500 pieces	

## FREQUENCY SOUND PRESSURE CHARACTERISTICS SINE WAVE DRIVE SQUARE WAVE DRIVE






## PS19 TYPE PS1920P02 FEATURES

- Low frequency tone(2kHz).
- Piezo element is coated with water proof processing.

## **SHAPES AND DIMENSIONS**





• It considers that water escapes from sound release hole and please decide an attachment angle.



## **SPECIFICATIONS AND CHARACTERISTICS**

Sound pressure		80dBA/ 10cm min.	[at 2kHz, 10Vo-P rectangular wave, measuring temperature: 25±5°C, humidity: 60±10%]
Temperature Operating		–20 to +70°C	
range	Storage	-30 to +80°C	
Maximum input voltage		20V <sub>0-P</sub> max.	[without DC bias]
Minimum delivery unit		600 pieces	





<sup>•</sup> All specifications are subject to change without notice.




## PS19 TYPE PS1927P02 FEATURES

## • High sound pressure.

· Piezo element is coated with water proof processing.

## **SHAPES AND DIMENSIONS**







### **SPECIFICATIONS AND CHARACTERISTICS**

Sound pressure		90dBA/ 10cm min.	[at 2.7kHz, 10Vo-P rectangular wave, measuring temperature: 25±5°C, humidity: 60±10%]
Temperature Operating		–20 to +70°C	
range	Storage	−30 to +80°C	
Maximum input voltage		20V <sub>0-P</sub> max.	[without DC bias]
Minimum delivery unit		600 pieces	-

## FREQUENCY SOUND PRESSURE CHARACTERISTICS SINE WAVE DRIVE SQUARE WAVE DRIVE






## LEAD WIRE TYPE PS15 TYPE PS1550L40N

## **FEATURES**


- Miniature size(ø15×T1.6mm).
- High cost performance.
- The installation of this type is easy with both-sided tape.
- This product adopts an excellent both-sided adhesive tape in bonding and the sound characteristic.


## **SHAPES AND DIMENSIONS**



## **SPECIFICATIONS AND CHARACTERISTICS**

Temperature	Operating	–20 to +70°C		_
range	Storage	−30 to +80°C		
Maximum input voltage		20V <sub>0-P</sub> max.	[without DC bias]	
Minimum delivery unit		4000 pieces		






<sup>\*</sup> The frequency characteristic changes depending on the case shape and the installation method.

## **ATDK**

### PRECAUTIONS FOR USE

- Do not apply DC bias to the piezoelectric buzzer; otherwise insulation resistance may become low and affect the performance.
- Do not supply any voltage higher than applicable to the piezoelectric buzzer.
- Do not use the piezoelectric buzzer outdoors. It is designed for indoor use. If the piezoelectric buzzer has to be used outdoors, provide it with waterproofing measures; it will not operate normally if subjected to moisture.
- Do not wash the piezoelectric buzzer with solvent or allow gas to enter it while washing; any solvent that enters it may stay inside a long time and damage it.
- A piezoelectric ceramic material of approximately 100µm thick is used in the sound generator of the buzzer. Do not press the sound generator through the sound release hole otherwise the ceramic material may break. Do not stack the piezoelectric buzzers without packing.
- Do not apply any mechanical force to the piezoelectric buzzer; otherwise the case may deform and result in improper operation.
- Do not place any shielding material or the like just in front of the sound release hole of the buzzer; otherwise the sound pressure may vary and result in unstable buzzer operation. Make sure that the buzzer is not affected by a standing wave or the like.
- Be sure to solder the buzzer terminal at 350°C max.(80W max.)(soldering iron trip) within 5 seconds using a solder containg silver.
- Avoid using the piezoelectric buzzer for a long time where any corrosive gas (H<sub>2</sub>S, etc.) exists; otherwise the parts or sound generator may corroded and result in improper operation.
- · Be careful not to drop the piezoelectric buzzer.

### RECOMMENDED OPERATING CIRCUIT EXAMPLE



\* Resistor to do charging and discharging to a piezoelectric element (Value of about  $1k\Omega$  is good efficiency).