

Han-Mod RJ45 IDC cable jack 8P AWG 28-24



Part number	09 14 545 1561
Specification	Han-Mod RJ45 IDC cable jack 8P AWG 28-24
HARTING eCatalogue	https://b2b.harting.com/09145451561

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Inserts
Element	Data connectors
Specification	Han [®] RJ45 cable jack

Version

Termination method	IDC termination
Gender	Female
Number of contacts	8

Technical characteristics

Conductor cross-section	AWG 28 AWG 24
Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s
Limiting temperature	-40 +70 °C
Mating cycles	≥500

Material properties

Material (insert)	Polyamide (PA)
Material (shielding)	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0



Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	28.64 g
Country of origin	Latvia
European customs tariff number	85366990
GTIN	5713140161986
eCl@ss	27440218 Module for industrial connectors (data)