


www.vishay.com

Vishay General Semiconductor

## Miniature Glass Passivated Single-Phase Bridge Rectifiers



### **LINKS TO ADDITIONAL RESOURCES**



PRIMARY CHARACTERISTICS							
I <sub>F(AV)</sub>	1 A						
V <sub>RRM</sub>	50 V, 100 V, 200 V, 400 V, 600 V, 800 V, 1000 V						
I <sub>FSM</sub>	50 A						
I <sub>R</sub>	5 μA						
V <sub>F</sub> at I <sub>F</sub> = 1.0 A	1.1 V						
T <sub>J</sub> max.	150 °C						
Package	DFM						
Circuit configuration	Quad						

### **FEATURES**

• UL recognition, file number E54214



• Ideal for printed circuit boards

• Applicable for automated insertion

· High surge current capability

• Solder dip 275 °C max. 10 s, per JESD 22-B106

 Material categorization: for definitions of compliance please see <a href="https://www.vishay.com/doc?99912"><u>www.vishay.com/doc?99912</u></a>

#### **TYPICAL APPLICATIONS**

General purpose use in AC/DC bridge full wave rectification for SMPS, lighting ballaster, adapter, battery charger, home appliances, office equipment, and telecommunication applications.

### **MECHANICAL DATA**

Case: DFM

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade

Terminals: matte tin plated leads, solderable per

J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test

Polarity: as marked on body

MAXIMUM RATINGS (T <sub>A</sub> = 25 °C unless otherwise noted)									
PARAMETER	SYMBOL	DF005M	DF01M	DF02M	DF04M	DF06M	DF08M	DF10M	UNIT
Device marking code		DF005	DF01	DF02	DF04	DF06	DF08	DF10	
Maximum repetitive peak reverse voltage	$V_{RRM}$	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V <sub>RMS</sub>	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	$V_{DC}$	50	100	200	400	600	800	1000	V
Maximum average forward output rectified current at $T_A = 40\ ^{\circ}C$	I <sub>F(AV)</sub>	1.0					Α		
Peak forward surge current single sine-wave superimposed on rated load	I <sub>FSM</sub>	50					Α		
Rating for fusing (t < 8.3 ms)	l <sup>2</sup> t	t 10					A <sup>2</sup> s		
Operating junction and storage temperature range	T <sub>J</sub> , T <sub>STG</sub>	T <sub>STG</sub> -55 to +150						ô	

Revision: 03-Sep-2020 1 Document Number: 88571



www.vishay.com

# Vishay General Semiconductor

<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>A</sub> = 25 °C unless otherwise noted)										
PARAMETER	TEST CONDITIONS	SYMBOL	DF005M	DF01M	DF02M	DF04M	DF06M	DF08M	DF10M	UNIT
Maximum instantaneous forward voltage drop per diode	1.0 A	V <sub>F</sub>	1.1					٧		
Maximum reverse current at	T <sub>A</sub> = 25 °C					5.0				
rated DC blocking voltage per diode	T <sub>A</sub> = 125 °C	IR	500						μA	
Typical junction capacitance per diode	4.0 V, 1 MHz	C <sub>J</sub> 25					pF			

THERMAL CHARACTERISTICS (T <sub>A</sub> = 25 °C unless otherwise noted)								
PARAMETER	SYMBOL	DF005M DF01M DF02M DF04M DF06M DF08M DF10M UNI						UNIT
Typical thermal resistance (1)	$R_{\theta JA}$	40						°C/W
Typical thermal resistance (9)	$R_{\theta JL}$	15						C/VV

#### Note

<sup>(1)</sup> Thermal resistance from junction to ambient and from junction to lead mounted on PCB with 0.5" x 0.5" (13 mm x 13 mm) copper pads

ORDERING INFORMATION (Example)								
PREFERRED P/N	UNIT WEIGHT (g) PREFERRED PACKAGE CODE BASE QUANTITY DELIVERY MODE							
DF06M-E3/45	0.416	45	50	Tube				



www.vishay.com

## Vishay General Semiconductor

### RATINGS AND CHARACTERISTICS CURVES (T<sub>A</sub> = 25 °C unless otherwise noted)




Fig. 1 - Derating Curve Output Rectified Current




Fig. 4 - Typical Reverse Leakage Characteristics Per Diode




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current Per Diode




Fig. 5 - Typical Junction Capacitance Per Diode




Fig. 3 - Typical Forward Characteristics Per Diode




Fig. 6 - Typical Transient Thermal Impedance


Revision: 03-Sep-2020 3 Document Number: 88571



www.vishay.com

Vishay General Semiconductor

### **PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)



# **Legal Disclaimer Notice**



Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

© 2023 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED