

Safety data sheet according to Regulation (EC) No. 1907/2006

SECTION 1. Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Code **HI93701-0**
Product name **Free Chlorine Reagent**

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use **Determination of Chlorine in Water Samples.**

1.3. Details of the supplier of the safety data sheet

Name **Hanna Instruments S.R.L.**
Full address **str. Hanna Nr 1**
District and Country **457260 loc. Nusfalau (Salaj)**
Romania
Tel. **+40 260607700**
Fax **+40 260607700**

e-mail address of the competent person responsible for the Safety Data Sheet

msds@hanna.ro

1.4. Emergency telephone number

For urgent inquiries refer to **Emergency Number - International: +1 7035273887 - UK, London: +44 8708200418 - CHEMTREC 24 hours/365 days**

SECTION 2. Hazards identification

2.1. Classification of the substance or mixture

The product is not classified as hazardous pursuant to the provisions set forth in EC Regulation 1272/2008 (CLP). However, since the product contains hazardous substances in concentrations such as to be declared in section no. 3, it requires a safety data sheet with appropriate information, compliant to EC Regulation 1907/2006 and subsequent amendments.

Hazard classification and indication: --

2.2. Label elements

Hazard labelling pursuant to EC Regulation 1272/2008 (CLP) and subsequent amendments and supplements.

Hazard pictograms: --

Signal words: --

Hazard statements:
EUH210 Safety data sheet available on request.

Precautionary statements: --

2.3. Other hazards

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

SECTION 3. Composition/information on ingredients

3.1. Substances

Information not relevant

SECTION 3. Composition/information on ingredients ... / >>

3.2. Mixtures

Contains:

Identification x = Conc. % Classification 1272/2008 (CLP)

N,N-DIETHYL-1,4-PHENYLENEDIAMMONIUM SULFATE

CAS 6283-63-2 1 ≤ x < 5 **Acute Tox. 4 H302**

EC 228-500-6

INDEX

The full wording of hazard (H) phrases is given in section 16 of the sheet.

SECTION 4. First aid measures

4.1. Description of first aid measures

EYES: Remove contact lenses, if present. Wash immediately with plenty of water for at least 15 minutes, opening the eyelids fully. If problem persists, seek medical advice.

SKIN: Remove contaminated clothing. Wash immediately with plenty of water. If irritation persists, get medical advice/attention. Wash contaminated clothing before using it again.

INHALATION: Remove to open air. In the event of breathing difficulties, get medical advice/attention immediately.

INGESTION: Get medical advice/attention. Induce vomiting only if indicated by the doctor. Never give anything by mouth to an unconscious person, unless authorised by a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Specific information on symptoms and effects caused by the product are unknown.

N,N-DIETHYL-1,4-PHENYLENEDIAMMONIUM SULFATE

Irritant effects. The following applies to aromatic amines in general: systemic effect: methaemoglobinaemia with headache, cardiac dysrhythmia, drop in blood pressure, dyspnoea, and spasms, principal symptom: cyanosis (blue discolouration of the blood).

4.3. Indication of any immediate medical attention and special treatment needed

Information not available

SECTION 5. Firefighting measures

5.1. Extinguishing media

SUITABLE EXTINGUISHING EQUIPMENT

The extinguishing equipment should be of the conventional kind: carbon dioxide, foam, powder and water spray.

UNSUITABLE EXTINGUISHING EQUIPMENT

None in particular.

5.2. Special hazards arising from the substance or mixture

HAZARDS CAUSED BY EXPOSURE IN THE EVENT OF FIRE

Do not breathe combustion products. The product is combustible and, when the powder is released into the air in sufficient concentrations and in the presence of a source of ignition, it can create explosive mixtures with air. Fires may start or get worse by leakage of the solid product from the container, when it reaches high temperatures or through contact with sources of ignition.

N,N-DIETHYL-1,4-PHENYLENEDIAMMONIUM SULFATE

Combustible. Development of hazardous combustion gases or vapours possible in the event of fire. Fire may cause evolution of: nitrous gases, nitrogen oxides, Sulphur oxides.

5.3. Advice for firefighters

GENERAL INFORMATION

Use jets of water to cool the containers to prevent product decomposition and the development of substances potentially hazardous for health. Always wear full fire prevention gear. Collect extinguishing water to prevent it from draining into the sewer system. Dispose of contaminated water used for extinction and the remains of the fire according to applicable regulations.

SPECIAL PROTECTIVE EQUIPMENT FOR FIRE-FIGHTERS

Normal fire fighting clothing i.e. fire kit (BS EN 469), gloves (BS EN 659) and boots (HO specification A29 and A30) in combination with self-contained open circuit positive pressure compressed air breathing apparatus (BS EN 137).

SECTION 6. Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

If there are no contraindications, spray powder with water to prevent the formation of dust.

Wear suitable protective equipment (including personal protective equipment referred to under Section 8 of the safety data sheet) to prevent any contamination of skin, eyes and personal clothing. These indications apply for both processing staff and those involved in emergency procedures.

6.2. Environmental precautions

The product must not penetrate into the sewer system or come into contact with surface water or ground water.

6.3. Methods and material for containment and cleaning up

Collect the leaked product and place it in containers for recovery or disposal. If the product is flammable, use explosion-proof equipment. If there are no contraindications, use jets of water to eliminate product residues.

Make sure the leakage site is well aired. Evaluate the compatibility of the container to be used, by checking section 10. Contaminated material should be disposed of in compliance with the provisions set forth in point 13.

6.4. Reference to other sections

Any information on personal protection and disposal is given in sections 8 and 13.

SECTION 7. Handling and storage

7.1. Precautions for safe handling

Before handling the product, consult all the other sections of this material safety data sheet. Avoid leakage of the product into the environment. Do not eat, drink or smoke during use. Remove any contaminated clothes and personal protective equipment before entering places in which people eat.

7.2. Conditions for safe storage, including any incompatibilities

Store only in the original container. Store the containers sealed, in a well ventilated place, away from direct sunlight. Keep containers away from any incompatible materials, see section 10 for details.

7.3. Specific end use(s)

Information not available

SECTION 8. Exposure controls/personal protection

8.1. Control parameters

During the risk assessment process, it is essential to take into consideration the ACGIH occupational exposure levels for inert particulate not otherwise classified (PNOC respirable fraction: 3 mg/m³; PNOC inhalable fraction: 10 mg/m³). For values above these limits, use a P type filter, whose class (1, 2 or 3) must be chosen according to the outcome of risk assessment.

8.2. Exposure controls

As the use of adequate technical equipment must always take priority over personal protective equipment, make sure that the workplace is well aired through effective local aspiration.

When choosing personal protective equipment, ask your chemical substance supplier for advice.

Personal protective equipment must be CE marked, showing that it complies with applicable standards.

HAND PROTECTION

In the case of prolonged contact with the product, protect the hands with penetration-resistant work gloves (see standard EN 374).

Work glove material must be chosen according to the use process and the products that may form. Latex gloves may cause sensitivity reactions.

SKIN PROTECTION

Wear category I professional long-sleeved overalls and safety footwear (see Directive 89/686/EEC and standard EN ISO 20344). Wash body with soap and water after removing protective clothing.

EYE PROTECTION

Wear airtight protective goggles (see standard EN 166).

RESPIRATORY PROTECTION

Use a type P filtering facemask, whose class (1, 2 or 3) and effective need, must be defined according to the outcome of risk assessment

SECTION 8. Exposure controls/personal protection ... / >>

(see standard EN 149).

ENVIRONMENTAL EXPOSURE CONTROLS

The emissions generated by manufacturing processes, including those generated by ventilation equipment, should be checked to ensure compliance with environmental standards.

SECTION 9. Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	powder
Colour	ivory
Odour	odourless
Odour threshold	Not available
pH	5.8 - 6.2 pH, 12 g/L
Melting point / freezing point	Not available
Initial boiling point	Not applicable
Boiling range	Not available
Flash point	Not applicable
Evaporation rate	Not available
Flammability (solid, gas)	not flammable
Lower inflammability limit	Not available
Upper inflammability limit	Not available
Lower explosive limit	Not available
Upper explosive limit	Not available
Vapour pressure	Not available
Vapour density	Not available
Relative density	2,00
Solubility	soluble in water
Partition coefficient: n-octanol/water	Not available
Auto-ignition temperature	Not available
Decomposition temperature	Not available
Viscosity	Not available
Explosive properties	not applicable
Oxidising properties	not applicable

9.2. Other information

Total solids (250°C / 482°F)	98,00 %
VOC (Directive 2010/75/EC) :	0
VOC (volatile carbon) :	0

SECTION 10. Stability and reactivity

10.1. Reactivity

There are no particular risks of reaction with other substances in normal conditions of use.

10.2. Chemical stability

The product is stable in normal conditions of use and storage.

N,N-DIETHYL-1,4-PHENYLENEDIAMMONIUM SULFATE
Sensitive to moisture, Sensitivity to light.

10.3. Possibility of hazardous reactions

The powders are potentially explosive when mixed with air.

N,N-DIETHYL-1,4-PHENYLENEDIAMMONIUM SULFATE
Violent reactions possible with: Strong oxidizing agents.

10.4. Conditions to avoid

Avoid environmental dust build-up.

N,N-DIETHYL-1,4-PHENYLENEDIAMMONIUM SULFATE
Strong heating (decomposition).

SECTION 10. Stability and reactivity ... / >>

10.5. Incompatible materials

Information not available

10.6. Hazardous decomposition products

Information not available

SECTION 11. Toxicological information

In the absence of experimental data for the product itself, health hazards are evaluated according to the properties of the substances it contains, using the criteria specified in the applicable regulation for classification.
It is therefore necessary to take into account the concentration of the individual hazardous substances indicated in section 3, to evaluate the toxicological effects of exposure to the product.

11.1. Information on toxicological effects

N,N-DIETHYL-1,4-PHENYLENEDIAMMONIUM SULFATE

Acute inhalation toxicity, Symptoms: Irritation symptoms in the respiratory tract - Skin irritation, slight irritation - Sensitisation, Sensitisation possible in predisposed persons.

Metabolism, toxicokinetics, mechanism of action and other information

Information not available

Information on likely routes of exposure

Information not available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Information not available

Interactive effects

Information not available

ACUTE TOXICITY

LC50 (Inhalation) of the mixture:	Not classified (no significant component)
LD50 (Oral) of the mixture:	>2000 mg/kg
LD50 (Dermal) of the mixture:	Not classified (no significant component)

N,N-DIETHYL-1,4-PHENYLENEDIAMMONIUM SULFATE

LD50 (Oral) > 497 mg/kg Rat

SKIN CORROSION / IRRITATION

Does not meet the classification criteria for this hazard class

SERIOUS EYE DAMAGE / IRRITATION

Does not meet the classification criteria for this hazard class

RESPIRATORY OR SKIN SENSITISATION

Does not meet the classification criteria for this hazard class

GERM CELL MUTAGENICITY

Does not meet the classification criteria for this hazard class

CARCINOGENICITY

Does not meet the classification criteria for this hazard class

REPRODUCTIVE TOXICITY

Does not meet the classification criteria for this hazard class

SECTION 11. Toxicological information ... / >>

STOT - SINGLE EXPOSURE

Does not meet the classification criteria for this hazard class

STOT - REPEATED EXPOSURE

Does not meet the classification criteria for this hazard class

ASPIRATION HAZARD

Does not meet the classification criteria for this hazard class

SECTION 12. Ecological information

Use this product according to good working practices. Avoid littering. Inform the competent authorities, should the product reach waterways or contaminate soil or vegetation.

12.1. Toxicity

Information not available

12.2. Persistence and degradability

Information not available

12.3. Bioaccumulative potential

N,N-DIETHYL-1,4-PHENYLENEDIAMMONIUM SULFATE

Partition coefficient: n-octanol/water, log Pow: 2.24 (calculated), (Lit.) Bioaccumulation is not expected.

12.4. Mobility in soil

Information not available

12.5. Results of PBT and vPvB assessment

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

12.6. Other adverse effects

N,N-DIETHYL-1,4-PHENYLENEDIAMMONIUM SULFATE

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

13.1. Waste treatment methods

Reuse, when possible. Neat product residues should be considered special non-hazardous waste.

Disposal must be performed through an authorised waste management firm, in compliance with national and local regulations.

CONTAMINATED PACKAGING

Contaminated packaging must be recovered or disposed of in compliance with national waste management regulations.

SECTION 14. Transport information

The product is not dangerous under current provisions of the Code of International Carriage of Dangerous Goods by Road (ADR) and by Rail (RID), of the International Maritime Dangerous Goods Code (IMDG), and of the International Air Transport Association (IATA) regulations.

14.1. UN number

Not applicable

14.2. UN proper shipping name

Not applicable

14.3. Transport hazard class(es)

Not applicable

SECTION 16. Other information ... / >>

- IMDG: International Maritime Code for dangerous goods
- IMO: International Maritime Organization
- INDEX NUMBER: Identifier in Annex VI of CLP
- LC50: Lethal Concentration 50%
- LD50: Lethal dose 50%
- OEL: Occupational Exposure Level
- PBT: Persistent bioaccumulative and toxic as REACH Regulation
- PEC: Predicted environmental Concentration
- PEL: Predicted exposure level
- PNEC: Predicted no effect concentration
- REACH: EC Regulation 1907/2006
- RID: Regulation concerning the international transport of dangerous goods by train
- TLV: Threshold Limit Value
- TLV CEILING: Concentration that should not be exceeded during any time of occupational exposure.
- TWA STEL: Short-term exposure limit
- TWA: Time-weighted average exposure limit
- VOC: Volatile organic Compounds
- vPvB: Very Persistent and very Bioaccumulative as for REACH Regulation
- WGK: Water hazard classes (German).

GENERAL BIBLIOGRAPHY

1. Regulation (EU) 1907/2006 (REACH) of the European Parliament
 2. Regulation (EC) 1272/2008 (CLP) of the European Parliament
 3. Regulation (EU) 790/2009 (I Atp. CLP) of the European Parliament
 4. Regulation (EU) 2015/830 of the European Parliament
 5. Regulation (EU) 286/2011 (II Atp. CLP) of the European Parliament
 6. Regulation (EU) 618/2012 (III Atp. CLP) of the European Parliament
 7. Regulation (EU) 487/2013 (IV Atp. CLP) of the European Parliament
 8. Regulation (EU) 944/2013 (V Atp. CLP) of the European Parliament
 9. Regulation (EU) 605/2014 (VI Atp. CLP) of the European Parliament
 10. Regulation (EU) 2015/1221 (VII Atp. CLP) of the European Parliament
 11. Regulation (EU) 2016/918 (VIII Atp. CLP) of the European Parliament
- The Merck Index. - 10th Edition
 - Handling Chemical Safety
 - INRS - Fiche Toxicologique (toxicological sheet)
 - Patty - Industrial Hygiene and Toxicology
 - N.I. Sax - Dangerous properties of Industrial Materials-7, 1989 Edition
 - IFA GESTIS website
 - ECHA website
 - Database of SDS models for chemicals - Ministry of Health and ISS (Istituto Superiore di Sanità) - Italy

Note for users:

The information contained in the present sheet are based on our own knowledge on the date of the last version. Users must verify the suitability and thoroughness of provided information according to each specific use of the product.

This document must not be regarded as a guarantee on any specific product property.

The use of this product is not subject to our direct control; therefore, users must, under their own responsibility, comply with the current health and safety laws and regulations. The producer is relieved from any liability arising from improper uses.

Provide appointed staff with adequate training on how to use chemical products.

Changes to previous review:

The following sections were modified:

09.