

467.SLS - Metric standard ratchet combination wrenches





Standards:

NF ISO 1711-1, NF ISO 691, ISO 1711-1, ISO 691, DIN ISO 1711-1, DIN ISO 691, ASME B107.100

Description:

- Tool equipped with a FACOM SLS attachment solution, preventing any risk of accidental falls.
- The crimped "sliding" cable solution, selected and tested by FACOM, maintains user ergonomics (8 - 30 mm wrenches).
- Standard ratchet combination wrenches: for all current applications.
- Compact ratchet mechanism and reversible by lever.
- Increment 5° (6° for dimensions 8 and 9 mm).
- Ring head angled at 15°.
- Open end head angled at 15°.
- Metric sizes: 8 to 32 mm.
- Presentation: satin chrome finish.



	A [mm]	A [in]	Length L [mm]	Thickness E [mm]	Thickness E1 [mm]	Thickness E2 [mm]	Head Height C [mm]	Head Width B [mm]	Head Width B1 [mm]	Weight [Kg]
467.10SLS	10.0		158.0	5.1	7.3	3.4	10.4	22.7	20.2	0.075
467.11SLS	11.0		165.0	5.2	7.7	3.5	10.6	23.7	22.0	0.085
467.12SLS	12.0		171.0	5.4	8.2	3.8	11.3	26.8	23.2	0.095
467.13SLS	13.0		178.0	5.7	8.6	4.3	12.2	28.4	25.3	0.11
467.14SLS	14.0		190.0	5.9	9.0	4.3	13.0	30.8	27.0	0.125
467.15SLS	15.0		199.0	6.1	9.4	4.7	14.0	32.3	28.3	0.14
467.16SLS	16.0		208.0	6.6	9.9	5.3	14.1	34.9	30.0	0.165
467.17SLS	17.0		225.0	6.6	10.3	5.4	15.4	36.8	31.7	0.19
467.18SLS	18.0		236.0	7.4	10.7	5.8	15.6	38.4	32.8	0.21
467.19SLS	19.0		247.0	7.4	11.2	6.0	16.0	41.2	33.9	0.235
467.21SLS	21.0		287.0	8.6	13.0	6.3	18.0	46.9	39.7	0.34
467.22SLS	22.0		287.0	8.6	13.0	6.3	18.0	46.9	39.7	0.34
467.24SLS	24.0		320.0	8.9	14.5	6.7	19.5	51.0	46.0	0.44
467.27SLS	27.0		356.0	9.8	15.5	7.1	21.0	57.9	52.0	0.595
467.30SLS	30.0		400.0	10.5	17.0	8.3	24.2	64.9	58.0	0.82
467.32SLS	32.0		422.0	11.0	17.5	8.5	26.0	67.9	62.2	0.975
467.8SLS	8.0		140.0	4.6	6.5	3.1	8.2	18.6	16.8	0.055
467.9SLS	9.0		149.0	4.6	6.9	3.2	9.0	21.0	18.6	0.065