

## Coaxial Cable Connector 24\_QMA-50-2-1/111\_N

### Description

Straight bulkhead cable feed through

Interface standards  
QMA QLF compliant



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	18 GHz

#### Mechanical Data

Centre contact	plugged
Outer contact	soldered
Weight	0.0041 kg

#### Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPRO Plating
Washer	Bronze	SUCOPRO Plating

### Related Documents

Outline drawing	DOU-00009765
Catalogue drawing	DCA-00009767
Assembly instruction	DOC-0000389604
Mounting hole	DOU-00008748

### Ordering Information

Single package	24_QMA-50-2-1/111_NE
Bulk 100 pcs package	24_QMA-50-2-1/111_NH

### Additional Information

Suitable cables	SUCOFORM_86, EZ_86_TP_M17, MULTIFLEX_86
-----------------	---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[24\\_QMA-50-2-1/111\\_NE](#)