


NOTES:

1. MATERIAL: HEADER-GLASS FILLED POLYESTER, 94V-0, MOLDED NATURAL (WHITE).
2. FINISH: (197) OVERALL REFLOWED MATTE TIN: 0.00152/.000060 MIN. OVER 0.00127/.000050 MIN. NICKEL OVERALL (222) OVERALL MATTE TIN: 0.00254/.000100 MIN TIN OVER 0.00127/.000050 MIN NICKEL. (208) SELECT GOLD: 0.00038/.000015 MIN, SELECT TIN: 0.00254/.000100 MIN, OVERALL NICKEL UNDERPLATE: 0.00127/.000050 MIN. (228) SELECT GOLD: 0.00076/.000030 MIN, SELECT TIN: 0.00254/.000100 MIN, OVERALL NICKEL UNDERPLATE: 0.00127/.000050 MIN. (241) SELECT GOLD: 0.00051/.000020 MIN. SELECT TIN: 0.00254/.000100 MIN. OVERALL NICKEL UNDERPLATE: 0.00127/.000050 MIN.
3. PRODUCT SPECIFICATION: SEE PS-08-50 & PS-40-02.
4. PACKAGING INFORMATION: SEE CHARTS
5. SOLDERABILITY: PER SMES-152.
6. PIN PUSH-OUT FORCE: 3 LB MIN PRIOR TO SOLDERING
7. PARTS ARE STACKABLE END TO END ON 3.96/.156 CENTERS.
8. FOR PARTS WITH PEGS, SEE DWG.NO. SDA-42491.
9. PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.



RECOMMENDED PC BOARD HOLE LAYOUT

CKT	DIM. A	DIM. B
2	7.77 306	3.96±0.05 .156±.002
3	11.73 462	7.92±0.08 .312±.003
4	15.70 618	11.89±0.08 .468±.003
5	19.66 774	15.85±0.10 .624±.004
6	23.62 930	19.81±0.10 .780±.004
7	27.58 1086	23.77±0.10 .936±.004
8	31.55 1242	27.74±0.13 1.092±.005
9	35.51 1398	31.70±0.13 1.248±.005
10	39.47 1554	35.66±0.13 1.404±.005
11	43.43 1710	39.62±0.15 1.560±.006
12	47.40 1866	43.59±0.15 1.716±.006
13	51.36 2022	47.55±0.15 1.872±.006
14	55.32 2178	51.51±0.18 2.028±.007
15	59.28 2334	55.47±0.18 2.184±.007
16	63.25 2490	59.44±0.18 2.340±.007

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

QUALITY SYMBOLS	REMOVE 17,18 CKT EC NO: 105925 DRWN: BAPPELDORN CHK'D: MKIPPER REV APPR: FSMITH	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE		
		MM	INCH	MM/IN	2:1		
▽ = 0	2016/06/08 2016/08/15 2016/08/25	4 PLACES ±	±	DRWN BY	DATE		KK .156 HEADER ASSY FLAT VERT W/O PEGS
▽ = 0		3 PLACES ±	± 0.01	JSCHAFFER	2003/11/03		
▽ = 0	REMOVE 17,18 CKT EC NO: 105925 DRWN: BAPPELDORN CHK'D: MKIPPER REV APPR: FSMITH	2 PLACES ±	± 0.015	CHK'D BY	DATE	PRODUCT CUSTOMER DRAWING	
▽ = 0		1 PLACES ±	± 0.38	SAMIEC	2004/03/24		
▽ = 0	REMOVE 17,18 CKT EC NO: 105925 DRWN: BAPPELDORN CHK'D: MKIPPER REV APPR: FSMITH	0 PLACES ±	±	APPR BY	DATE	SERIES MATERIAL NUMBER CUSTOMER 41771 SEE CHART GENERAL MARKET	
▽ = 0		ANGULAR TOL ± 0.5	±	MARGULIS	2004/03/24		
▽ = 0	REMOVE 17,18 CKT EC NO: 105925 DRWN: BAPPELDORN CHK'D: MKIPPER REV APPR: FSMITH	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE	THIRD ANGLE PROJECTION	DOCUMENT NUMBER DOC TYPE DOC PART SHEET NUMBER SD-41771-001 PSD 000 1 OF *	
▽ = 0				A			

RELEASE STATUS	RELEASE DATE
----------------	--------------

2-*	K
1	K
SHEET	REV