



# Interchangeable Line Optic 30° Fan Angle

## 1. Product Overview.


The Interchangeable line lens consists of a moulded acrylic multi rod lens element fitted with in an 11mm diameter lens holder with an M9 thread section for mounting. The lens produces a line with typical full fan angle of 30 degree with a 5mm by 1.5 mm input beam and the intensity distribution is gaussian in the width and homogeneous in the line. The homogeneous line produces a line with high uniformity at shorter working distances, however due to the effects of divergence the uniformity levels will decrease over longer working distance. An M9 threaded section allows the lens assembly to simply screw into any laser module with a M9 thread for lens assembly and a suitable focal length collimator.

## 2. Specification.

<b>Lens Material</b>	Acrylic
<b>Lens Type</b>	Moulded Multi Rod
<b>Exit Aperture</b>	5mm
<b>A/R Coated</b>	No
<b>Typical Input Beam Size</b>	5 by 1.5mm
<b>Typical Fan Angle</b>	30°
<b>Typical Transmission Loss (650nm)</b>	≤25%

## 3. Diagram.

Interchangeable Line Lens (30° Fan Angle)



Please Note: Global Laser reserve the right to change descriptions and specifications without notice.



T: +44 (0)1495 212213  
F: +44 (0)1495 214004  
E: sales@globallasertech.com  
www.globallasertech.com

Global Laser Ltd  
Unit 9-10  
Roseheyworth Business Park  
Abertillery, Gwent NP13 1SP UK