Surface Mount Fuses Ceramic Fuse > 407 Series

407 Series - 1206 Time-Lag Fuse





Agency Approvals

| AGENCY | AGENCY FILE NUMBER | AMPERE RANGE | | |
|-----------------|--------------------|--------------|--|--|
| c FL °us | E10480 | 1A – 8A | | |

Electrical Characteristics

| % of Ampere Ampere Rating Rating | | | | |
|----------------------------------|---------|------------------------------|--|--|
| 100% | 1A – 8A | 4 hours Minimum | | |
| 200% | 1A – 8A | 1 sec Min; 120 secs Max | | |
| 300% | 1A – 8A | 0.1 sec Min; 3 secs Max | | |
| 800% | 1A – 8A | 0.002 sec Min; 0.05 secs Max | | |

Additional Information









I²t time lag fuse is designed to have ultra-high in-rush

Description

- Operating Temperature from -55° C to +150° C
- 100% Lead-free, RoHS compliant and Halogen-free
- Suitable for both leaded and lead-free reflow/wave soldering
- Ultra high l²t values

Littelfuse 407 Series is a 100% Lead-free, RoHS compliant and Halogen-free fuse designed specifically to provide

overcurrent protection to circuits that operate under high working ambient temperatures up to 150° C and high in-rush currents. The general design ensures excellent temperature stability and performance reliability. This high

current withstand capability to avoid nuisance fuse open.

Benefits

Features

 Avoids nuisance opening due to high inrush and surge current inherent in the system

• High current ratings in small size

Applications

- Displays
- Servers
- Computers
- Printers

- Scanners
- Data Modems
- Gaming Consoles





Electrical Specifications by Item

| Ampere Rating (A) | Amp Code | Max. Voltage Rating (V) | Interrupting Rating (AC/DC) ¹ | Nominal Resistance (Ohms) ² | Nominal Melting l²t (A²Sec.)³ | Nominal Voltage Drop At Rated Current (V)4 | Nominal Power Dissipation At Rated Current (W) | Agency Approval |
|-------------------------|-------------|----------------------------------|--|--|-------------------------------------|---|---|--------------------|
| 1.00 | 001. | 63 | | 0.360 | 0.142 | 0.456 | 0.456 | X |
| 1.25 | 1.25 | 63 | 50A@63VDC | 0.200 | 0.329 | 0.404 | 0.500 | X |
| 1.50 | 01.5 | 63 | 50A@63VDC | 0.180 | 0.567 | 0.347 | 0.525 | Х |
| 2.00 | 002. | 63 | | 0.100 | 0.870 | 0.323 | 0.640 | Х |
| 2.50 | 02.5 | 32 | | 0.055 | 1.000 | 0.252 | 0.625 | Х |
| 3.00 | 003. | 32 | | 0.040 | 1.300 | 0.187 | 0.570 | Х |
| 3.50 | 03.5 | 32 | 50A@32VDC | 0.030 | 2.260 | 0.153 | 0.525 | Х |
| 4.00 | 004. | 32 | 50A@32VDC | 0.025 | 4.180 | 0.142 | 0.560 | Х |
| 4.50 | 04.5 | 32 | | 0.020 | 5.200 | 0.134 | 0.585 | Х |
| 5.00 | 005. | 32 | | 0.016 | 7.800 | 0.133 | 0.650 | Х |
| 5.50 | 05.5 | 24 | 50A@24VDC | 0.014 | 8.550 | 0.130 | 0.715 | Х |
| 6.00 | 006. | 24 | | 0.012 | 15.560 | 0.128 | 0.780 | Х |
| 7.00 | 007. | 24 | 60A@24VDC | 0.010 | 16.230 | 0.110 | 0.770 | Х |
| 8.00 | 008. | 24 | | 0.009 | 24.120 | 0.097 | 0.800 | Х |


Note:

- 1. AC Interrupting Rating tested at rated voltage with unity power factor. DC Interrupting Rating tested at rated voltage with time constant < 0.8 msec.
- 2. Nominal Resistance measured with < 10% rated current.
- 3. Nominal Melting I²t measured at 1 msec opening time.
- 4. Nominal Voltage Drop measured at rated current after temperature has stabilized.

Devices designed to carry rated current for 4 hours minimum. It is recommended that devices be operated continuously at no more than 80% rated current. See *Temperature Derating Curve* for additional derating information.

• Devices designed to be mounted with marking code facing up.

Temperature Re-rating Curve



Note:


Re-rating depicted in this curve is in addition to the standard re-rating of 20% for continuous operation.

Example:

For continuous operation at 75° C, the fuse should be rerated as follows:

 $I = (0.80)(0.85)I_{RAT} = (0.68)I_{RAT}$


Average Time Current Curves



Surface Mount Fuses Ceramic Fuse > 407 Series

Soldering Parameters

| Reflow Co | ndition | Pb – free assembly | |
|---------------------------------------|--|--------------------------|--|
| | -Temperature Min (T _{s(min)}) | 150°C | |
| Pre Heat | -Temperature Max (T _{s(max)}) | 200°C | |
| | -Time (Min to Max) (t _s) | 60 - 180 seconds | |
| Average R (T _L) to pea | amp-up Rate (Liquidus Temp k) | 3° C/second max. | |
| T _{S(max)} to T _I | - Ramp-up Rate | 5° C/second max. | |
| Reflow | -Temperature (T _L) (Liquidus) | 217° C | |
| nellow | -Temperature (t _L) | 60 – 150 seconds | |
| PeakTemp | erature (T _P) | 260+ ^{0/-5} ° C | |
| Time with Temperatu | in 5°C of actual peak ure (t _p) | 10 - 30 seconds | |
| Ramp-dov | vn Rate | 6° C/second max. | |
| Time 25°C | to peakTemperature (T _P) | 8 minutes max. | |
| Do not exc | ceed | 260°C | |




T_D T_L T_{S(max)} T_{S(min)} T_{S(min)} Preheat T_{S(min)} Time Time


Product Characteristics

| Materials | Body: Advanced Ceramic Terminations: Ag / Ni / Sn (100% Lead- free) Element Cover Coating: Lead-free Glass | | | | |
|-------------------------------|---|--|--|--|--|
| Moisture Sensitivity Level | IPC/JEDEC J-STD-020, Level 1 | | | | |
| Solderability | IPC/ECA/JEDEC J-STD-002, Condition C | | | | |
| Humidity Test | MIL-STD-202, Method 103, Conditions D | | | | |
| Resistance to Solder Heat | MIL-STD-202, Method 210, Condition B | | | | |
| Moisture Resistance | MIL-STD-202, Method 106 | | | | |
| Thermal Shock | MIL-STD-202, Method 107, Condition B | | | | |
| Mechanical Shock | MIL-STD-202, Method 213, Condition A | | | | |
| Vibration | MIL-STD-202, Method 201 | | | | |
| Vibration, High Frequency | MIL-STD-202, Method 204, Condition D | | | | |
| Dissolution of Metallization | IPC/ECA/JEDEC J-STD-002, Condition D | | | | |
| Terminal Strength | IEC 60127-4 | | | | |





| Part Marking System | | | | | | |
|---------------------|--------------|--|----------|--------------|--|--|
| Amp Code | Marking Code | | Amp Code | Marking Code | | |
| 001. | <u>H</u> | | 004. | <u>s</u> | | |
| 1.25 | <u>J</u> | | 04.5 | <u>s.</u> | | |
| 01.5 | <u>K</u> | | 005. | I | | |
| 002. | N | | 05.5 | <u>U</u> | | |
| 02.5 | <u>o</u> | | 006. | V | | |
| 003. | <u>P</u> | | 007. | w | | |
| 03.5 | <u>R</u> | | 008. | X | | |



| Pa | ackaging | | | | |
|----|-------------------|--|-------------------------------|------------------------------------|----|
| | Packaging Option | Option Form Factor Packaging Specification | | Quantity Quantity & Packaging Code | |
| | 8mm Tape and Reel | Surface Mount | EIA-481, IEC 60286, Part 3 | 3000 | WR |

Disclaimer Notice - Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

<u>0407001.WR</u> <u>0407002.WR</u> <u>0407003.WR</u> <u>0407004.WR</u> <u>0407005.WR</u> <u>040704.5WR</u> <u>040705.5WR</u> <u>04071.25WR</u> 0407006.WR 0407007.WR 0407008.WR 040701.5WR 040702.5WR 040703.5WR