

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0039301062](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit Jr. Power Connectors](#)  
**Description:** Mini-Fit Jr. Header, Dual Row, Right-Angle, with Snap-in Plastic Peg PCB Lock, 6 Circuits, PA Polyamide Nylon 6/6 94V-0, 0.76µm Select Gold (Au) Plating

**Documents:**

|  |   |
|--|---|
| <a href="#">3D Model (PDF)</a>                               | <a href="#">Application Specification AS-5557-001-001 (PDF)</a> |
| <a href="#">3D Model</a>                                     | <a href="#">Packaging Specification PK-5569-002-001 (PDF)</a>   |
| <a href="#">Drawing (PDF)</a>                                | <a href="#">Test Summary TS-5556-002-001 (PDF)</a>              |
| <a href="#">Product Specification PS-45750-001-001 (PDF)</a> | <a href="#">Symbol Footprint Data SYM-39-30-1060 (PDF)</a>      |
| <a href="#">Product Specification PS-5556-001-001 (PDF)</a>  | <a href="#">RoHS Certificate of Compliance (PDF)</a>            |

**Agency Certification**


|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |   |
|----------------|---|
| Product Family | PCB Headers   |
| Series         | <a href="#">5569</a>  |
| Application    | Power, Wire-to-Board  |
| Comments       | Current = 13A max. per circuit when header is mated to a receptacle loaded with <a href="#">45750</a> Mini-Fit Plus HCS Crimp Terminal Crimped to 16 AWG wire., See Molex Product specification PS-5556-001 for additional current de-rating information. |
| Overview       | <a href="#">Mini-Fit Jr. Power Connectors</a>   |
| Product Name   | Mini-Fit Jr.  |
| UPC            | 800754379175  |

**Physical**

|                                |             |
|--------------------------------|-------------|
| Breakaway                      | No          |
| Circuits (Loaded)              | 6           |
| Circuits (maximum)             | 6           |
| Color - Resin                  | Natural     |
| Durability (mating cycles max) | 30          |
| First Mate / Last Break        | No          |
| Flammability                   | 94V-0       |
| Glow-Wire Capable              | No          |
| Guide to Mating Part           | No          |
| Keying to Mating Part          | None        |
| Lock to Mating Part            | Yes         |
| Material - Metal               | Brass       |
| Material - Plating Mating      | Gold        |
| Material - Plating Termination | Matte Tin   |
| Material - Resin               | Nylon       |
| Net Weight                     | 2.244/g     |
| Number of Rows                 | 2           |
| Orientation                    | Right Angle |
| PCB Locator                    | Yes         |
| PCB Retention                  | Yes         |
| PCB Thickness - Recommended    | 1.78mm      |
| Packaging Type                 | Bag         |
| Pitch - Mating Interface       | 4.20mm      |
| Pitch - Termination Interface  | 4.20mm      |
| Plating min - Mating           | 0.762µm     |
| Plating min - Termination      | 2.540µm     |



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[5569](#) Series

**Mates With**

[5557](#) Mini-Fit Jr. Receptacle Housing, Mini-Fit TPA2 Receptacle Housing [172708](#)

|                                |                |
|--------------------------------|----------------|
| Polarized to Mating Part       | Yes            |
| Polarized to PCB               | Yes            |
| Shrouded                       | Fully          |
| Stackable                      | No             |
| Surface Mount Compatible (SMC) | No             |
| Temperature Range - Operating  | -40° to +105°C |
| Termination Interface: Style   | Through Hole   |

**Electrical**

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 13.0A |
| Voltage - Maximum             | 600V  |

**Solder Process Data**

|  |      |
|--|------|
| Duration at Max. Process Temperature (seconds) | 005  |
| Lead-free Process Capability                   | WAVE |
| Max. Cycles at Max. Process Temperature        | 001  |
| Process Temperature max. C                     | 240  |

**Material Info**

|                    |                |
|--------------------|----------------|
| Engineering Number | 5569-06A2G-210 |
|--------------------|----------------|

**Reference - Drawing Numbers**

|                           |                                   |
|---------------------------|-----------------------------------|
| Application Specification | AS-5557-001-001                   |
| Packaging Specification   | PK-5569-002-001                   |
| Product Specification     | PS-45750-001-001, PS-5556-001-001 |
| Sales Drawing             | 55690002-SD-000                   |
| Symbol/Footprint Data     | SYM-39-30-1060                    |
| Test Summary              | TS-5556-002-001                   |

This document was generated on 12/03/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39-30-1062](#)