

Minitek® Pwr 5.7 Connector System

5.7MM COMPREHENSIVE SOLUTION WITH CURRENT RATING UP TO 23A

Minitek® Pwr 5.7mm is a flexible and comprehensive solution for power application with high current rating up to 23A per contact and wire gauge range from 16 – 12AWG for wire-to-board application. Minitek® Pwr 5.7mm features polarized mating geometry, this helps to prevent mis-mating. It offers a wide operating temperature, ranging -40°C to 105°C, making it suitable for a wide range of applications. The scoop proof housing prevents terminals from damage.

- High current rating up to 23A per contact
- Solution for vertical through hole
- Solution for wire-to-board



FEATURES

- High current alloy material used for contact
- Positive locking on housing with low thumb latch operation
- · High retention force in housing
- Post-plated terminal
- Glow wire compliant
- UL94V-0 flammability rated LCP material
- Halogen-free resin material
- RoHS compliant and lead-free

BENEFITS

- Rated up to 23A per contact
- Ensures secured mating retention
- Well secured terminal in housing
- Prevents environmental corrosion such as salt spray and gas corrosion
- Complies with International Standard IEC 60335-1 for household appliances
- High flammability rating
- Meets environmental standards
- Meets environmental, health and safety requirements

TECHNICAL INFORMATION

MATERIAL

- Board Connector: High-Conductivity Copper with optional Tin and Gold plating
- Housing: Nylon 66 & LCP, Black, UL94V-0
- Crimping Terminal: High-Conductivity Copper with optional Tin and Gold plating

MECHANICAL PERFORMANCE

- Mating Force:
- Tin plated: 6.8N
- Gold plated 6.0N per circuit max.
- Unmating Force:
 - Tin plated: 6.5N
 - Gold plated: 5.6N per circuit max.
- Durability:
 - Tin plated: 25 cycles
 - Gold plated: 200 cycles

ELECTRICAL PERFORMANCE

- Low Level Contact Resistance: $2m\Omega$ max. (Initial)
- Insulation Resistance: $1000M\Omega$ min.
- Voltage Rating: 600V AC (RMS)/DC
- Contact Resistance: Tin plated 10m Ω / Gold Plating 5m Ω max.
- Current Rating: Up to 23A/contact

PACKAGING

- PCB Header: Tray
- Receptacle Housing: Bag
- Crimping Terminal: Reel

APPROVALS & CERTIFICATION

- UL approval: E66906
- TUV approval: B171234414032

SPECIFICATION

- Amphenol Product Specification: GS-12-1405
- Amphenol Packaging Specification: GS-14-2595

ENVIRONMENTAL

• Operating Temperature: -40°C to 105°C

TOOLING INFORMATION

• Ratchet Hand Crimping Tool: RCY21282

TARGET MARKETS/APPLICATIONS



1U Rack Box Customer Premises Equipment Generic Telecom Box Interface Converter WiMax Box



Air Conditioner Microwave Oven Refrigerator Set Top Box



Blade Server
Desktop PC and Motherboard
HDD Application
Rack-Mount Server
Server-Orthogonal Configuration



Defibrillator Hospital Bed Patient Monitor Ultrasound Equipment



Chemical Detection System Radar Equipment

PART NUMBERS

Description	Part Numbers
Minitek® Pwr 5.7 Vertical PCB header, through hole	10142708
Minitek® Pwr 5.7 Receptacle housing	10142707
Minitek® Pwr 5.7 Crimping terminal	10143250