







INTERCONNECTS













SERIES 850, 851, 852, 853 • 1,27 GRID HEADERS AND SOCKETS • SINGLE AND DOUBLE ROW STRIPS



- Series 850, 851, 852, 853 single and double row interconnects have 1,27 pin spacing and permit board stacking as low as 6,3
- Pin headers have 0,41 dia. pins (MM #4006-0) See page 208 for details
- MM #0467 and MM #4890 receptacles use Hi-Rel, 3-finger BeCu #11 contact rated at 3 amps. (#11 contact accepts pin diameters from 0,38 - 0,51). See pages 158 and 160 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 850...001	Single Row 2,21 Profile Pin Header			
	850-XX-0__-10-001000	Specify number of pins \uparrow 01-50			
FIG. 2	Series 852...001	Double Row 2,11 Profile Pin Header			
	852-XX-__-10-001000	Specify number of pins \uparrow 004-100			
					
SPECIFY PLATING CODE XX=		10 	90	40 	
Pin Plating 		0,25µm Au	5,08µm Sn/Pb	5,08µm Sn	
FIG. 3	Series 851...001	Single Row 4,09 Profile Socket			
	851-XX-0__-10-001000	Specify number of pins \uparrow 01-50			
FIG. 4	Series 853...001	Double Row 4,09 Profile Socket			
	853-XX-__-10-001000	Specify number of pins \uparrow 004-100			
FIG. 5	Series 851...002	Single Row 4,7 Profile Socket			
	851-XX-0__-10-002000	Specify number of pins \uparrow 01-77			
					
SPECIFY PLATING CODE XX=		91	93	99	41 
Sleeve (Pin) 		5,08µm Sn/Pb	5,08µm Sn/Pb	5,08µm Sn/Pb	5,08µm Sn
Contact (Clip) 		0,25µm Au	0,76µm Au	2,54µm Sn/Pb	Au Flash

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mill-Max:](#)

[852-10-010-10-001000](#) [852-10-026-10-001000](#) [850-40-003-10-001000](#) [852-10-012-10-001000](#) [853-43-016-10-001000](#) [853-47-100-10-001000](#) [853-47-100-20-001000](#) [853-47-010-10-001000](#)