

WMS 19,1 (EX30)R YE - Shrink sleeve



0800306

<https://www.phoenixcontact.com/us/products/0800306>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shrink sleeve, Roll, yellow, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLLMASTER 300/600, THERMOMARK ROLL X1, THERMOMARK ROLL, THERMOMARK ROLL 2.0, THERMOMARK W, THERMOMARK X1.2, unperforated, mounting type: slide-on, cable diameter range: 6.4 ... 19.1 mm, lettering field size: 30 x 20000 mm, Number of individual labels: 1, roll length: 20 m

Product description

The continuous shrink sleeves in the WMS... product family can be assembled to create individual marker lengths using the THERMOMARK E. CUTTER or E.CUTTER/P. After the printing, assembly, and applying process, you have the option of shrinking the marked shrink sleeves by applying heat manually and thus fixing them on the cable/wire.

Your advantages

- Permanent and captive identification of single-core wires, wires, cables, pneumatic hoses, and other cylindrical objects
- High flexibility, as individual marker lengths ranging from 3.45 mm ... 2000 mm (0.14" ... 78.7") can be realized in combination with the cutter and perforation cutter
- As an option, the sleeves can be shrunk by applying heat manually to fix the sleeve in position
- High diameter coverage with a shrink ratio of 3:1
- Widely used and proven worldwide in control cabinet and machine building, the oil and gas industry, and the railway industry

Commercial data

Item number	0800306
Packing unit	1 pc
Sales key	BG14
Product key	BG2216
Catalog page	Page 227 (C-3-2019)
GTIN	4046356626033
Weight per piece (including packing)	691 g
Weight per piece (excluding packing)	526.1 g
Customs tariff number	39173200
Country of origin	CN

Technical data

Notes

General	For the THERMOMARK ROLL and THERMOMARK ROLL 2.0 roll printers, this material can only be processed with an external media hub.
General	<p>The specified minimum wire diameter of the shrink sleeve refers to its use as a marking material and does not guarantee any insulation characteristics once shrunk.</p> <p>Depending on the processed material batch, as well as the storage and processing conditions, the maximum insertable wire diameter may be reduced.</p>

Product properties

Product type	Shrink sleeve
Type	Shrink sleeve

Marking

Number of individual labels	1
Identification technology	Thermal transfer for rolls

Dimensions

Width	30 mm
Length of roll	20.00 m

External dimensions

Outside diameter	6.4 mm ... 19.1 mm
------------------	--------------------

Material specifications

RoHS compliant	yes
Color	yellow
Material	Polyolefine
Base element material	polyolefine
Components	halogen-free

Cable/line

External cable diameter	6.4 mm ... 19.1 mm
-------------------------	--------------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

WMS 19,1 (EX30)R YE - Shrink sleeve



0800306

<https://www.phoenixcontact.com/us/products/0800306>

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

WMS 19,1 (EX30)R YE - Shrink sleeve



0800306

<https://www.phoenixcontact.com/us/products/0800306>

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-55 °C ... 125 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	5 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	slide-on
---------------	----------

WMS 19,1 (EX30)R YE - Shrink sleeve



0800306

<https://www.phoenixcontact.com/us/products/0800306>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0800306>



CSA

Approval ID: 252259



cULus Recognized

Approval ID: E310982_Vol2_Sec1

WMS 19,1 (EX30)R YE - Shrink sleeve



0800306

<https://www.phoenixcontact.com/us/products/0800306>

Classifications

ECLASS

ECLASS-11.0	27281102
ECLASS-12.0	27281102
ECLASS-13.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

WMS 19,1 (EX30)R YE - Shrink sleeve

0800306

<https://www.phoenixcontact.com/us/products/0800306>



Accessories

THERMOMARK E.300 D US - Thermal transfer printer

1287033

<https://www.phoenixcontact.com/us/products/1287033>



Thermal transfer printer with internal rewinder for printing all materials in roll format with a print resolution of 300 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

THERMOMARK E.300 US - Thermal transfer printer

1287021

<https://www.phoenixcontact.com/us/products/1287021>



Thermal transfer printer for printing all materials in roll format with a print resolution of 300 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

WMS 19,1 (EX30)R YE - Shrink sleeve

0800306

<https://www.phoenixcontact.com/us/products/0800306>



THERMOMARK E.600 D US - Thermal transfer printer

1287040

<https://www.phoenixcontact.com/us/products/1287040>



Thermal transfer printer with internal rewinder for printing all materials in roll format with a print resolution of 600 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

THERMOMARK E.600 US - Thermal transfer printer

1287029

<https://www.phoenixcontact.com/us/products/1287029>



Thermal transfer printer for printing all materials in roll format with a print resolution of 600 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

WMS 19,1 (EX30)R YE - Shrink sleeve

0800306

<https://www.phoenixcontact.com/us/products/0800306>



THERMOMARK ROLL 2.0 - Thermal transfer printer

1085260

<https://www.phoenixcontact.com/us/products/1085260>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

THERMOMARK-RIBBON 110-WMSU - Ink ribbon

0801358

<https://www.phoenixcontact.com/us/products/0801358>



Ink ribbon, For roll printer for printing product groups WMS..., WMS-2 HF..., and WMTB HF-HP, length: 300 m, roll length: 300 m, width: 110 mm, color: black

WMS 19,1 (EX30)R YE - Shrink sleeve

0800306

<https://www.phoenixcontact.com/us/products/0800306>



THERMOMARK-RIBBON 64-WMSE - Ink ribbon

5145724

<https://www.phoenixcontact.com/us/products/5145724>



Ink ribbon, for roll printer for printing product group WMS..., length: 300 m, roll length: 300 m, width: 64 mm, color: black

THERMOMARK-RIBBON 64-WMSU - Ink ribbon

0801360

<https://www.phoenixcontact.com/us/products/0801360>



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., length: 300 m, roll length: 300 m, width: 64 mm, color: black

WMS 19,1 (EX30)R YE - Shrink sleeve

0800306

<https://www.phoenixcontact.com/us/products/0800306>



TM-RIBBON 40 BK 105 - Ink ribbon

1259008

<https://www.phoenixcontact.com/us/products/1259008>



Ink ribbon, for the E-WMS... product group in combination with the THERMOMARK E.SLEEVE applicator and the WMS... and WMS-2 HF... product groups in combination with conventional roll printers, length: 300 m, roll length: 300 m, width: 40 mm, color: black

TR-PRESSURE ROLLER STANDARD - Pressure roller

0801802

<https://www.phoenixcontact.com/us/products/0801802>

Standard pressure roller



WMS 19,1 (EX30)R YE - Shrink sleeve

0800306

<https://www.phoenixcontact.com/us/products/0800306>



TR-PRESSURE ROLLER DR4-50 - Pressure roller

0801800

<https://www.phoenixcontact.com/us/products/0801800>

Pressure roller for continuous shrink sleeve



TRM-PRESSURE ROLLER STANDARD - Pressure roller

0804655

<https://www.phoenixcontact.com/us/products/0804655>

Standard pressure roller



WMS 19,1 (EX30)R YE - Shrink sleeve

0800306

<https://www.phoenixcontact.com/us/products/0800306>



TRM-PRESSURE ROLLER 4-50 - Pressure roller

0804656

<https://www.phoenixcontact.com/us/products/0804656>



Pressure roller for continuous shrink sleeve

THERMOMARK ROLL-ERH - Media hub

5146448

<https://www.phoenixcontact.com/us/products/5146448>



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

WMS 19,1 (EX30)R YE - Shrink sleeve

0800306

<https://www.phoenixcontact.com/us/products/0800306>



THERMOMARK-ERH 500 - Media hub

5146309

<https://www.phoenixcontact.com/us/products/5146309>



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

THERMOMARK ROLLMASTER 300 - Thermal transfer printer

0804501

<https://www.phoenixcontact.com/us/products/0804501>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

WMS 19,1 (EX30)R YE - Shrink sleeve

0800306

<https://www.phoenixcontact.com/us/products/0800306>



THERMOMARK ROLLMASTER 600 - Thermal transfer printer

0804663

<https://www.phoenixcontact.com/us/products/0804663>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

THERMOMARK ROLL - Thermal transfer printer

5146477

<https://www.phoenixcontact.com/us/products/5146477>



Thermal transfer printer, 300 dpi, incl. European power cable, US power cable, and USB cable. DVD with CLIP PROJECT advanced planning and marking software, user manuals in various languages, Windows® printer driver, and firmware. German/English user manual in DIN A5 format, EML (20x8)R roll of labels, white, with 1000 labels, and ink ribbon: 50 m

WMS 19,1 (EX30)R YE - Shrink sleeve

0800306

<https://www.phoenixcontact.com/us/products/0800306>



THERMOMARK X1.2 - Thermal transfer printer

5146231

<https://www.phoenixcontact.com/us/products/5146231>



Thermal transfer printer, weight: 10 kg, length: 0.446 m, width: 242 mm, height: 274 mm, color: gray

THERMOMARK W2 - Thermal transfer printer

5146147

<https://www.phoenixcontact.com/us/products/5146147>



Thermal transfer printer for material off the roll, incl. Euro/US power cable, USB cable, and perforation knife. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English.

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com