

Printed-circuit board connector - LPC 6/3-ST-7,62 - 1716922

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Plug component, nominal current: 41 A, rated voltage (III/2): 1000 V, number of positions: 3, pitch: 7.62 mm, connection method: Push-in spring connection, color: green, contact surface: Tin

The figure shows the 4-position version

Why buy this product

- ☑ Tool-free lever principle enables time-saving connection and release of conductors with/without ferrules
- ☑ Clear lever positions provide reliable feedback on opened or closed clamping spaces
- Defined contact force ensures that contact remains stable over the long term



Key Commercial Data

Packing unit	25 STK
GTIN	4 055626 513287
GTIN	4055626513287
Weight per Piece (excluding packing)	23.000 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Item properties

Brief article description	Printed-circuit board connector
Range of articles	LPC 6/ST
Pitch	7.62 mm
Type of contact	Female connector
Plug-in system	POWER COMBICON 6
Number of positions	3
Connection method	Push-in spring connection
Locking	without



Printed-circuit board connector - LPC 6/3-ST-7,62 - 1716922

Technical data

11		
ITAM	nra	perties
ILCIII	טוט	טטו ווכט

Number of levels	1.1
Number of levels	'

Electrical parameters

Rated current	41 A
Rated insulation voltage (III/2)	1000 V
Rated surge voltage (III/2)	8 kV

Connection capacity

Conductor cross section solid	0.75 mm² 6 mm²
Conductor cross section flexible	0.75 mm² 6 mm²
Conductor cross section AWG / kcmil	18 10
Conductor cross section flexible, with ferrule without plastic sleeve	0.75 mm² 6 mm²
Conductor cross section, flexible, with ferrule, with plastic sleeve	0.75 mm² 6 mm²
Cylindrical gauge a x b / diameter	4.3 mm x 4.0 mm / 4.0 mm
Stripping length	18 mm

Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/ JEDEC JESD 201
Contact material	Cu alloy
Surface characteristics	hot-dip tin-plated
Metal surface terminal point (top layer)	Tin (4 - 8 µm Sn)
Metal surface contact area (top layer)	Tin (4 - 8 µm Sn)

Material data - housing

Housing color	green (6021)
---------------	--------------

Material data - actuating element

Color of the actuating lever	orange (2003)
------------------------------	---------------

Dimensions for the product

Length [1]	48 mm
Width [w]	24.86 mm
Pitch	7.62 mm
Dimension a	15.24 mm

Packaging information

Type of packaging	packed in cardboard
Pieces per package	25
Denomination packing units	Pcs.

Termination and connection method

Conductor connection test	The stripped-off ends of the largest conductor can be completely inserted in the opening of the terminal point without using excessive force.
Test result	Test passed



Printed-circuit board connector - LPC 6/ 3-ST-7,62 - 1716922

Technical data

Termination and connection method

Test – repeated connection and release	IEC 60999-1:1999-11
	Test passed
Test for conductor damage and slackening	IEC 60999-1:1999-11
	Test passed

Pull-out test

Pull-out test	Test passed IEC 60999-1:1999-11
	IEC 60999-1:1999-11
	Test passed
Conductor cross section / conductor type / tensile force	0.75 mm² solid > 30 N
	0.75 mm² stranded > 30 N
	6 mm² solid > 80 N
	6 mm² stranded > 80 N
	stranded > 80 N

Mechanical tests according to standard

Test specification	IEC 61984
Visual examination	Test passed IEC 60512-1-1:2002-02
Dimensional test	Test passed IEC 60512-1-2:2002-02
Resistance of marking	Test passed IEC 60068-2-70:1995-12
Result	Test passed
Specification	IEC 60512-13-2:2006-02
No. of cycles	25
Insertion strength per pos. approx.	11 N
Withdraw strength per pos. approx.	16 N
Polarization and coding	Test passed IEC 60512-13-5:2006-02 20 N
Test force	20 N
Result	Test passed
Specification	IEC 60512-15-1:2008-05
Test force per pos.	20 N

Air clearances and creepage distances

Insulating material group	I
Voltage	800 V
Rated insulation voltage (III/3)	800 V
Rated insulation voltage (III/2)	1000 V
Rated insulation voltage (II/2)	1000 V
Rated surge voltage (III/3)	8 kV
Rated surge voltage (III/2)	8 kV
Rated surge voltage (II/2)	6 kV

Electrical tests - Function

Specification	IEC 61984



Printed-circuit board connector - LPC 6/ 3-ST-7,62 - 1716922

Technical data

Temperature cycles

Specification	IEC 61984
Current carrying capacity / derating curves	

Specification	IEC 61984
---------------	-----------

Mechanical tests (A)

Test specification	IEC 61984
Insertion strength per pos. approx.	11 N
Withdraw strength per pos. approx.	16 N
Polarization when inserted requirement >20 N	Test passed
Contact holder in insert requirements >20 N	Test passed

Durability tests (B)

Specification	IEC 60512-9-1:2010-03
Contact resistance R ₁	0.5 mΩ
Insertion/withdrawal cycles	25
Contact resistance R ₂	0.5 mΩ
Impulse withstand voltage at sea level	9.8 kV
Power-frequency withstand voltage	4.26 kV

Thermal tests (C)

Specification	IEC 60512-5-1:2002-02
Number of positions	4
Conductor cross section	6 mm²
Test current	41 A
Upper limiting temperature requirements <100 °C	Test passed

Climatic tests (D)

Specification	ISO 6988:1985-02
Cold stress	-40 °C/2 h
Thermal stress	100 °C/168 h
Corrosive stress	0.2 dm³ SO₂ on 300 dm³/40 °C/1 cycle
Impulse withstand voltage at sea level	7.3 kV
Power-frequency withstand voltage	3.31 kV

Environmental and durability tests (E)

Specification	IEC 61984:2008-10
Result, degree of protection, IP code	Finger safety with IP20 test finger

Classifications

eCl@ss

eCl@ss 8.0	27440309
eCl@ss 9.0	27440309



Printed-circuit board connector - LPC 6/ 3-ST-7,62 - 1716922

Classifications

ETIM

ETIM 5.0 EC002638

Phoenix Contact 2018 © - all rights reserved http://www.phoenixcontact.com