



ES3A/AB - ES3D/DB

### 3.0A SURFACE MOUNT SUPER-FAST RECTIFIER

### **Features**

- Glass Passivated Die Construction
- Super-Fast Recovery Time For High Efficiency
- Surge Overload Rating to 100A Peak
- Ideally Suited for Automated Assembly
- Lead Free Finish/RoHS Compliant (Note 1)
- Green Molding Compound (No Halogen and Antimony)
  (Note 2)

# **Mechanical Data**

- Case: SMB/SMC
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Lead Free Plating (Matte Tin Finish). Solderable per MIL-STD-202, Method 208 (23)
- Polarity: Cathode Band or Cathode Notch
- SMB Weight: 0.093 grams (approximate)
- SMC Weight: 0.21 grams (approximate)



Top View

Bottom View

# Ordering Information (Note 3)

Part Number	Case	Packaging
ES3x-13-F	SMC	3000/Tape & Reel
ES3xB-13-F	SMB	3000/Tape & Reel

\* x = Device type, e.g. ES3A-13-F (SMC package); ES3AB-13-F (SMB package).

Notes: 1. EU Directive 2002/95/EC (RoHS). All applicable RoHS exemptions applied, see EU Directive 2002/95/EC Annex Notes.

2. Product manufactured with Data Code 0924 (week 24, 2009) and newer are built with Green Molding Compound.

3. For packaging details, go to our website at http://www.diodes.com.

# **Marking Information**



ES3x = Product type marking code, ex: ES3A (SMC package) ES3xB = Product type marking code, ex: ES3AB (SMB package) D++ = Manufacturers' code marking YWW = Date code marking Y = Last digit of year (ex: 2 for 2002) WW = Week code (01 to 53)



### Maximum Ratings @T<sub>A</sub> = 25°C unless otherwise specified

Single phase, half wave, 60Hz, resistive or inductive load.

Characteristic	Symbol	ES3A/AB	ES3B/BB	ES3C/CB	ES3D/DB	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage (Note 4)	V <sub>RRM</sub> V <sub>RWM</sub> V <sub>R</sub>	50	100	150	200	V
RMS Reverse Voltage	V <sub>R(RMS)</sub>	35	70	105	140	V
Average Rectified Output Current @ T <sub>T</sub> = 100°C	lo		3	.0		Α
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half Sine-Wave Superimposed on Rated Load			1(	00		А

# **Thermal Characteristics**


Characteristic	Symbol	Value	Unit
Typical Thermal Resistance, Junction to Terminal	$R_{\theta JT}$	10	°C/W
Typical Thermal Resistance, Junction to Ambient (Note 5)	$R_{ heta JA}$	50	°C
Operating and Storage Temperature Range	T <sub>J,</sub> T <sub>STG</sub>	-55 to +150	°C


# Electrical Characteristics @T<sub>A</sub> = 25°C unless otherwise specified

Characteristic		Symbol	Value	Unit
Maximum Forward Voltage	@ I <sub>F</sub> = 3.0A	V <sub>FM</sub>	0.9	V
Peak Reverse Current at Rated DC Blocking Voltage (Note 4)	@ T <sub>A</sub> = 25°C @ T <sub>A</sub> = 125°C	I <sub>RM</sub>	10 500	μA
Maximum Reverse Recovery Time (Note 6)		t <sub>rr</sub>	25	ns
Typical Total Capacitance (Note 7)		CT	45	pF

Notes: 4. Short duration pulse test used to minimize self-heating effect.

5. Unit mounted on PC board with 5.0 mm<sup>2</sup> (0.013 mm thick) copper pads as heat sink. 6. Measured with  $I_F = 0.5A$ ,  $I_R = 1.0A$ ,  $I_{rr} = 0.25A$ . See Figure 5. 7. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.







# ES3A/AB - ES3D/DB





Fig. 5 Reverse Recovery Time Characteristic and Test Circuit

# **Package Outline Dimensions**




SMB			
Dim	Min	Max	
Α	3.30	3.94	
В	4.06	4.57	
С	1.96	2.21	
D	0.15	0.31	
E	5.00	5.59	
G	0.05	0.20	
Н	0.76	1.52	
J	2.00	2.50	
All Dimensions in mm			

SMC			
Dim	Min	Max	
Α	5.59	6.22	
В	6.60	7.11	
С	2.75	3.18	
D	0.15	0.31	
E	7.75	8.13	
G	0.10	0.20	
Н	0.76	1.52	
J	2.00	2.50	
All Dimensions in mm			



## Suggested Pad Layout



SMB Dimensions	Value (in mm)
Z	6.7
G	1.8
Х	2.3
Y	2.5
С	4.3

SMC Dimensions	Value (in mm)
Z	9.3
G	4.4
Х	3.3
Y	2.5
С	6.8

#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2010, Diodes Incorporated

www.diodes.com

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

**Diodes Incorporated:** 

ES3DB-13-F ES3AB-13-F ES3B-13-F ES3D-13-F ES3CB-13-F ES3C-13-F ES3A-13-F ES3BB-13-F