

DSUB SV MA TSDP STR 50P PL3



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 050 5654
Specification	DSUB SV MA TSDP STR 50P PL3
HARTING eCatalogue	https://b2b.harting.com/09670505654

Identification

Category	Connectors
Series	D-Sub
Identification	Standard
Element	Connector
Description of the contact	Turned Straight

Version

Termination method	Wave soldering termination
Gender	Male
Locking type	Fixing flange with feed through hole \varnothing 3.1 mm
Size	D-Sub 5
Connection type	Motherboard to daughtercard Mezzanine
Number of contacts	50
Termination length	5.8 mm
Performance level	3
PCB fixing	Without board locks
Pack contents	Carton

Technical characteristics

Distance between rows	2.54 mm
Flange height	6.5 mm
Rated current	7.5 A



Pushing Performance

Technical characteristics

Clearance distance	≥1 mm
Creepage distance	≥1 mm
Insulation resistance	>10 ¹⁰ Ω
Contact resistance	≤10 mΩ
Limiting temperature	-55 ... +125 °C
Insertion force	≤167 N
Mating cycles	≥50
Test voltage U _{r.m.s.}	1 kV
Isolation group	IIIa (175 ≤ CTI < 400)
Hot plugging	No

Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled (PBTP) Plated steel
Colour (insert)	White
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated Termination side Gold plated Mating side
Material (hood/housing)	Steel
Surface (hood/housing)	Tin plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	DIN 41652
UL / CSA	UL 1977 ECBT2.E102079



Pushing Performance

Commercial data

Packaging size	25
Net weight	16.6 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440214 D-Sub coupler

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09670505654](#)