



AH1806

# HIGH SENSITIVITY MICROPOWER OMNIPOLAR HALL-EFFECT SWITCH

# **Description**


The AH1806 is a high-sensitivity, micro-power Omnipolar Hall effect switch IC, designed for portable and battery powered consumer to home appliance and industrial applications such as smart-meter magnetic tamper detection. Based on two sensitive Hall effect plates and a copper stabilized architecture the AH1806 provides a reliable solution over the whole operating range. To support portable and battery powered equipment, the design has been optimized to operate over the supply range of 2.5V to 5.5V and consumes only 24µW with a supply of 3V.


The single-open-drain output can be switched on with either a North or South pole of sufficient field strength. When the magnetic flux density (B) perpendicular to the package is larger than operate point (Bop) the output is switched on (pulled low). The output is turned off when B becomes lower than the release point (Brp). The output will remain off when there is no magnetic field.


#### **Features**

- Omnipolar (North or South Pole) Operation
- High Sensitivity
- Single Open Drain Output
- Micropower Operation
- 2.5V to 5.5V Operating Range
- Chopper Stabilized Design Provides: Superior Temperature Stability
   Minimal Switch Point Drift
   Enhanced Immunity to Stress
- · Good RF Noise Immunity
- -40°C to +85°C Operating Temperature
- ESD (HBM) > 6KV
- Small Low Profile SOT553 and Industry Standard SC59, SIP-3 (Ammo Pack) and SIP-3 (Bulk Pack) Packages
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)

## **Pin Assignments**







SIP-3 (Bulk Pack)

### **Applications**


- Doors, Lids, Cover and Tray Position Detect Switches
- Display Switch for Portable PCs and Tablets
- On/Off Switch for PDAs and Digital Cameras
- Liquid Level Detection
- Smart Meters
- Position, Proximity and Level Detection Contact-Less Switch in Battery Powered Consumer, Home Appliances and Industrial Applications

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



# **Typical Applications Circuit**



Note:

4.  $C_{IN}$  is for power stabilization and to strengthen the noise immunity, the recommended capacitance is 10nF to 100nF.  $R_L$  is the pull-up resistor; the recommended resistance is 10k $\Omega$  to 100k $\Omega$ .

## **Pin Descriptions**

Packages: SC59 and SIP-3 (Ammo Pack) and SIP-3 (Bulk Pack)


Pin Number	Pin Name	Function			
1	$V_{DD}$	Power Supply Input			
2	GND	Ground			
3	OUTPUT	Output			

Package: SOT553

Pin Number	Pin Name	Function			
1	NC	No Connection (Note 5)			
2	GND	Ground			
3	NC	No Connection (Note 5)			
4	$V_{DD}$	Power Supply Input			
5	OUTPUT	Output			

Note: 5. NC is "No Connection" pin and is not connected internally. This pin can be left open or tied to ground.

# **Functional Block Diagram**





### Absolute Maximum Ratings (Note 6) (@TA = +25°C, unless otherwise specified.)

Symbol	Cha	aracteristics	Values	Unit
$V_{DD}$	Supply Voltage (Note 7)		7	V
V <sub>OUT</sub>	Output Pin Voltage (Note 7)		7	V
V <sub>DD REV</sub>	Reverse Supply Voltage	-0.3	V	
V <sub>OUT_REV</sub>	Reverse Output Pin Voltage	-0.3	V	
Гоитрит	Output Current (Source And Sink)	2.5	mA	
В	Magnetic Flux Density		Unlimited	
В	Package Power Dissipation	SC59 and SOT553	230	mW
P <sub>D</sub>	Package Power Dissipation	SIP-3 (Ammo Pack) and SIP-3 (Bulk Pack)	230	mW
T <sub>S</sub>	Storage Temperature Range	-65 to +150	°C	
$T_J$	Maximum Junction Temperature	+150	°C	
ESD HBM	Human Body Model ESD Capability	,	6	kV

Notes:

- 6. Stresses greater than the 'Absolute Maximum Ratings' specified above may cause permanent damage to the device. These are stress ratings only; functional operation of the device at these or any other conditions exceeding those indicated in this specification is not implied. Device reliability may be affected by exposure to absolute maximum rating conditions for extended periods of time.
- 7. The absolute maximum V<sub>DD</sub> of 7V is a transient stress rating and is not meant as a functional operating condition. It is not recommended to operate the device at the absolute maximum rated conditions for any period of time.


# Recommended Operating Conditions (@TA = +25°C, unless otherwise specified.)

Symbol	Characteristic Conditions		Rating	Unit
$V_{DD}$	Supply Voltage	Operating	2.5 to 5.5	V
$V_{\text{OUT\_MAX}}$	Maximum Output Pin Voltage	Operating	5.5	V
T <sub>A</sub>	Operating Temperature Range	Operating	-40 to +85	°C

# Electrical Characteristics (@T<sub>A</sub> = +25°C, V<sub>DD</sub> = 3V, unless otherwise specified.)

Symbol	Characteristic	Conditions	Min	Тур	Max	Unit
V <sub>OUT_ON</sub>	Output On Voltage (V <sub>OL</sub> )	I <sub>OUT</sub> = 1mA	_	0.1	0.3	V
loff	Output Leakage Current	$V_{OUT} = 5.5V$ , Output off	_	< 0.1	1	μΑ
l (avvalva)		During 'awake' period, T <sub>A</sub> = +25°C, V <sub>DD</sub> = 3V	_	3	6	mA
I <sub>DD</sub> (awake)	Supply Current	During 'awake' period, T <sub>A</sub> = -40 to +85°C, V <sub>DD</sub> = 2.5V to 5.5V	_	3	12	mA
I <sub>DD</sub> (sleep)	Supply Current	During 'sleep' period, T <sub>A</sub> = +25°C, V <sub>DD</sub> = 3V	_	5	10	μΑ
I <sub>DD</sub> (sleep)		During 'sleep' period, T <sub>A</sub> = -40 to +85°C, V <sub>DD</sub> = 2.5V to 5.5V	_		28	μΑ
J (0)(0)	Average Supply Current	$T_A = +25$ °C, $V_{DD} = 3V$	_	8	16	μΑ
I <sub>DD</sub> (avg)	Average Supply Current	$T_A = -40 \text{ to } +85^{\circ}\text{C}, V_{DD} = 2.5\text{V to } 5.5\text{V}$	_	_	40	μΑ
t <sub>AWAKE</sub>	Awake Time	(Note 8)	_	75	125	μs
t <sub>PERIOD</sub>	Period	(Note 8)	_	75	125	ms
D.C.	Duty Cycle	_	_	0.1	_	%

Note: 8. When power is initially turned on, the operating V<sub>DD</sub> must be within its correct operating range (2.5V to 5.5V) to guarantee the output sampling. The output state is valid after the second operating cycle (typical 150ms).





# Magnetic Characteristics (Notes 9 & 10) (@T<sub>A</sub> = +25°C, V<sub>DD</sub> = 3V, unless otherwise specified.)

(1mT=10 Gauss)


Symbol	Characteristic	Conditions	Min	Тур	Max	Unit
Dana (acuth mala ta mant mandina acida)	On a ration Daint	_	15	30	45	
Bops (south pole to part marking side)	Operation Point	$V_{DD} = 2.5V \text{ to } 5.5V$	10	30	45	
	On and the Daint	-	-45	-30	-15	
Bopn (north pole to part marking side)	Operation Point	$V_{DD} = 2.5V \text{ to } 5.5V$	-45	-30	-10	
Dung (agaith mala ta mant manting aide)	Dalance Daint	_	10	20	40	Gauss
Brps (south pole to part marking side)	Release Point	$V_{DD} = 2.5V \text{ to } 5.5V$	4	20	40	
Duran (conthe male to mant months a side)	Dalance Daint	_	-40	-20	-10	
Brpn (north pole to part marking side)	Release Point	$V_{DD} = 2.5V \text{ to } 5.5V$	-40	-20	-4	
Bhy ( Bopx - Brpx )	Hysteresis (Note 11)	_	5	10	_	1

Notes:

- 9. Typical data is at T<sub>A</sub> = +25°C, V<sub>DD</sub> = 3V, and for design information only.

  10. The magnetic characteristics may vary with supply voltage, operating temperature and after soldering.

  11. Maximum and minimum hysteresis is guaranteed by design and characterization.







## **Thermal Performance Characteristics**

### (1) Package Types: SC59, SOT553, SIP-3 (Ammo Pack) and SIP-3 (Bulk Pack)

T <sub>A</sub> (°C)	25	50	60	70	80	85	90	100	110	120	130	140	150
P <sub>D</sub> (mW)	230	184	166	147	129	120	110	92	74	55	37	18	0



# **Ordering Information**



Z: SOT553

P: SIP-3 (Ammo Pack) SIP-3 (Bulk Pack)

A: Ammo Box (Note 12)

B: Bulk (Note 13)

	Package		Bulk		7" Tape and Reel		Ammo Box	
Device	Code	Packaging	Quantity	Part Number Suffix	Quantity	Part Number Suffix	Quantity	Part Number Suffix
AH1806-P-A	Р	SIP-3 (Ammo Pack)	NA	NA	NA	NA	4,000/Box	-A
AH1806-P-B	Р	SIP-3 (Bulk Pack)	1,000	-B	NA	NA	NA	NA
AH1806-W-7	W	SC59	NA	NA	3,000/Tape & Reel	-7	NA	NA
AH1806-Z-7	Z	SOT553	NA	NA	3,000/Tape & Reel	-7	NA	NA


12. Ammo Box is for SIP-3 Spread Lead.13. Bulk is for SIP-3 Straight Lead. Notes:



## **Marking Information**

### (1) Package Type: SC59





XX : Identification code

Y : Year 0 to 9

 $\underline{W}$ : Week: A to Z: 1 to 26 week;


a to z: 27 to 52 week; z represents

52 and 53 week

X : Internal Code

Part Number	Package	Identification Code	
AH1806	SC59	H6	

#### (2) Package Type: SOT553



XX: Identification Code

Y: Year: 0 to 9

 $\underline{W}$ : Week: A to Z: 1~26 week;


a to z: 27~52 week; z represents

52 and 53 week

 $\underline{X}$ : Internal code

Part Number	Package	Identification Code	
AH1806	SOT553	H6	

#### (3) Package Types: SIP-3 (Ammo Pack) and SIP-3 (Bulk Pack)



Y: Year: 0~9

WW: Week: 01~52, "52" represents

52 and 53 week  $\underline{X}$ : Internal Code


February 2018 © Diodes Incorporated




# Package Outline Dimensions (All dimensions in mm.)

Please see http://www.diodes.com/package-outlines.html for the latest version.

### (1) Package Type: SC59



	SC	59	
Dim	Min	Max	Тур
Α	0.35	0.50	0.38
В	1.50	1.70	1.60
С	2.70	3.00	2.80
D	-	-	0.95
G	-	-	1.90
Н	2.90	3.10	3.00
J	0.013	0.10	0.05
K	1.00	1.30	1.10
L	0.35	0.55	0.40
M	0.10	0.20	0.15
N	0.70	0.80	0.75
α	0°	8°	-
All	Dimens	ions in	mm




**Sensor Location** 




# Package Outline Dimensions (Continued) (All dimensions in mm.)

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### (2) Package Type: SOT553



SOT553							
Dim	Min	Max	Тур				
Α	0.55	0.62	0.60				
b	0.15	0.30	0.20				
С	0.10	0.18	0.15				
D	1.50	1.70	1.60				
Е	1.55	1.70	1.60				
E1	1.10	1.25	1.20				
е	(	).50 BS(					
e1	1	1.00 BS0					
F	0.00	0.10					
L	0.10	0.30	0.20				
а	6°	8°	7°				
All [	All Dimensions in mm						



**Sensor Location** 


February 2018




# Package Outline Dimensions (Cont.) (All dimensions in mm.)


Please see http://www.diodes.com/package-outlines.html for the latest version.

#### (3) Package Type: SIP-3 (Bulk Pack)





SIP-3 (Bulk Pack)				
Dim	Min	Max	Тур	
Α	1.40	1.60	1.50	
b	0.33	0.43	0.38	
b2	0.40	0.508	0.46	
С	0.35	0.41	0.38	
D	3.90	4.30	4.10	
Е	2.80	3.20	3.00	
e1	1.24	1.30	1.27	
F	0.00	0.20		
J	2.62 REF			
L	14.00	15.00	14.50	
L1	1.55	1.75	1.65	
S	0.63	0.84	0.74	
a1			5°	
a2			5°	
a3			45°	
a4			3°	
All Dimensions in mm				




**Sensor Location** 




# Package Outline Dimensions (Cont.) (All dimensions in mm.)

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### (4) Package Type: SIP-3 (Ammo Pack)



SIP-3					
(Ammo Pack)					
Dim	Min	Max	Тур		
Α	1.40	1.60	1.50		
b	0.33	0.43	0.38		
b2a	0.40	0.52	0.46		
С	0.35	0.41	0.38		
D	3.90	4.30	4.10		
Е	2.80	3.20	3.00		
e1	1.24	1.30	1.27		
e2	2.40	2.90	2.65		
F	0.00	0.20			
J	2.62 REF				
L	14.00	15.00	14.50		
La	12.90	14.90	13.90		
L1	1.55	1.75	1.65		
L3	2.00	3.00	2.50		
S	0.63	0.84	0.74		
a1			5°		
a2			5°		
а3			45°		
a4			3°		
All Dimensions in mm					




**Sensor Location** 



# Suggested Pad Layout


 $\label{prop:lease} Please see \ http://www.diodes.com/package-outlines.html \ for \ the \ latest \ version.$ 

### (1) Package Type: SC59



Dimensions	Value (in mm)	
Z	3.4	
Х	0.8	
Y	1.0	
С	2.4	
Е	1.35	

### (2) Package Type: SOT553



Dimensions	Value (in mm)	
Z	2.2	
G	1.2	
Х	0.375	
Υ	0.5	
C1	1.7	
C2	0.5	



#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

**Diodes Incorporated:** 

AH1806-W-7 AH1806-Z-7 AH1806-P-B AH1806-P-A