

		•				
	PART NUMBER	PRESS-FIT TAIL PLATING TYPE	SHORT DETECT CONTACT			
	10039851-101	TIN/LEAD ALLOY OVER NICKEL	NO			
	10039851-101LF	TIN OVER NICKEL (LEAD FREE)	NO			
	10039851-111	TIN/LEAD ALLOY OVER NICKEL	YES			
	10039851-111LF	TIN OVER NICKEL (LEAD FREE)	(SEE NOTE 13)			

NOTES:


CONNECTOR MATERIALS:
HOUSING & RETAINER: HIGH TEMP THERMOPLASTIC, NATURAL, UL94V-0
IMLA PLASTIC: HIGH TEMP THERMOPLASTIC, BLACK, UL94V-0
CONTACT: COPPER ALLOY

2. CONTACT PLATING:

SEPARABLE INTERFACE:
PERFORMANCE-BASED PLATING, QUALIFIED TO MEET THE
REQUIREMENTS OF FCI PRODUCT SPECIFICATION GS-12-239
INCLUDING TELCORDIA GR-1217-CORE (NOVEMBER 1995)
CENTRAL OFFICE TEST SEQUENCE

PRESS-FIT TAILS: SEE TABLE

- 3. PRODUCT SPECIFICATION: GS-12-239
- 4. APPLICATION SPECIFICATION: GS-20-035
- (5.) PRODUCT MARKING, (PART NUMBER & LOT CODE), ON THIS SURFACE
- 6. REFER TO CUSTOMER DRAWING 10035911 FOR INFORMATION REGARDING PCB LAYOUT OF POWER AND GUIDE MODULES RELATIVE TO SIGNAL MODULES
- 7. POSITIONS F OF ODD NUMBERED COLUMNS AND POSITIONS G
 OF EVEN NUMBERED COLUMNS CORRESPOND TO EARLY MATE HEADER PINS
- 8. THERE IS NO GROUND BUSSING WITHIN THE CONNECTOR SYSTEM
- (9.) REFER TO CUSTOMER DRAWING 10045979 FOR INFORMATION ON PCB HOLE DIAMETERS AND PLATING OPTIONS.



- 10. LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- II. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 40 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- 12. PACKAGING MEETS GS-14-920 LEAD FREE LABELING SPECIFICATION.
- (13) MATING PIN E4 HAS 0.5mm LESS NOMINAL WIPE THAN THE SHORTEST SIGNAL PIN.

spec ref			dr	Chen-Hong Tan		2006/10/02		pr	projection		ММ	size	sca	l e	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED		eng	Yong-Keat Lim		2011/05/30						A 3	3:		
ASME YI4.5			OLETED INFF22	chr	-		-		1	⊕ - ⊟	-		ecn no	ELX-S	i-003991-1
-	OTHERWITCE OF ECTIVED			appr	Chen-Hong Tan		2011/05/30		produ	ıct family		AirMax VS	rel level	Re	leased
		0.X	±0.3	_		Φ Λ;	r M a v	\/ C	D / A	ПЕУИЕВ) ACCV	0 [rev
surface 3./2	linear	0.XX	±0.10		≟ AirMax VS F		I\	N/A HEAVEN		ASSI	10039851	51			
		0.XXX	±0.050			+ PRE	SS_FIT	, 54	POS,	I 4MM		<u>*</u> ♥			F
ASME YI4.5	angular	0°	±2°	www.	fci.com	cat. no	٥.			- P	roduct	- Customei	r Drw	sheet 5	of 5

2》

Copyright FCI.

D

Pro/E File - REV C - 2009-06-09

2

PDS: Rev :F

STATUS:Released

Printed: May 31, 2011

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI / Amphenol:

10039851-101LF 10039851-111LF