
Resistors Pulse Withstanding Chip Resistors

PWC Series

- Excellent pulse withstand performance
- Improved working voltage
- Improved power rating
- Custom designs available
- Anti-sulphur version available





All Pb-free parts comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)

Electrical Data

Size		PWC0603	PWC0805	PWC1206		PWC	PWC2010		PWC2512	
Power @70°C	W	0.125	0.25	0.33	0.5	0.75	1	1.5	2	
Resistance range	ohms		1R0 to 10M							
Tolerance	%		10R to 1M: 0.5, All values: 1, 5							
LEV V		75	150	20	200 400		00	500		
TCR	ppm/°C		<10R:200 ≥10R:100							
Operating temperature	°C					+155			_	
Thermal Impedance	°C/W	302	220	160	145	80	70	55	40	
Pad / trace area *	mm²	30	40	50	125	60	250	100	500	
Values		E24 or E96 preferred - other values to special order								
Pulse Capability		See graphs – full application note available on request								

*Recommended minimum pad & adjacent trace area for each termination for rated power dissipation on FR4 PCB

Physical Data

Dimensior	ns (mm) & w	/eight (mg)	\sim					
	L	W	T max	А	B min	С	Wt.	
0603	1.6±0.1	0.8±0.1	0.55	0.3±0.15	0.6	0.3±0.15	2.2	
0805	2.0±0.15	1.25±0.15	0.6	0.3±0.15	0.9	0.3±0.1	4.7	A
1206	3.2±0.2	1.6±0.2	0.7	0.4±0.2	1.7	0.4±0.15	8.5	
2010	5.1±0.3	2.5±0.2	0.8	0.6±0.3	3.0	0.6±0.25	36	Wrap-around terminations (3 faces)
2512	6.5±0.3	3.2±0.2	0.8	0.6±0.3	4.4	0.6±0.25	55	

Construction

Thick film resistor material, overglaze and organic protection are screen printed on a 96% alumina substrate. Wrap-around terminations have an electroplated nickel barrier and solder coating, this ensures excellent 'leach' resistance properties and solderability.

Note that anti-sulphur version parts below 5R are produced in flip-chip format with the resistor element on the underside.

Marking

Components are not marked. Reels are marked with type, value, tolerance, date code and quantity.

Solvent Resistance

The body protection is resistant to all normal industrial cleaning solvents suitable for printed circuits.

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print. Pulse Withstanding Chip Resistors



PWC Series

Performance Data


Size		Maximum	Typical
Load at rated power: 1000 hours at 70°C	ΔR%	1	0.25
Shelf life test: 12 months at room temperature	ΔR%	0.1	0.02
Derating from rated power at 70°C		Zero at 15	55°C
Overload: 6.25 x rated power for 2 seconds	ΔR%	1	0.1
Dry heat: 1000 hours at 155°C	ΔR%	1	0.2
Long term damp heat	ΔR%	1	0.25
Temperature rapid change	ΔR%	0.25	0.05
Resistance to solder heat	ΔR%	0.25	0.05
Resistance to sulphur-bearing gas (AS version only): ASTM-B-8	09	0.25	0.05
Voltage proof	Volts	500	

Note: A 0.01 Ohm addition to be added to the performance of all resistors <10 Ohms.

Pulse Performance Data

Lightning Surge

Lightning surge resistors are tested in accordance with IEC 60 115-1 using both 1.2/50µs and 10/700µs pulse shapes. 10 pulses are applied. The limit of acceptance is a shift in resistance of less than 1% from the initial value.



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability.

All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

IRC

BI Technologies

Welwyn

Resistors


Pulse Withstanding Chip Resistors

PWC Series




Single Impulse

The single impulse graph is the result of 50 impulses of rectangular shape applied at one minute intervals. The limit of acceptance was a shift in resistance of less than 1% from the initial value.



Continuous Load Due to Repetitive Pulses

The continuous load graph was obtained by applying repetitive rectangular pulses where the pulse period was adjusted so that the average power dissipated in the resistor was equal to its rated power at 70°C. Again the limit of acceptance was a shift in resistance of less than 1% from the initial value



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

BI Technologies IRC Welwyn

www.ttelectronics.com/resistors


Resistors

Pulse Withstanding Chip Resistors

PWC Series



Thermal Performance Data



Packaging

0603, 0805 and 1206 resistors are supplied on 8mm carrier tape and 2010 and 2512 resistors are supplied on 12mm carrier tape, all on 7 inch reels as per IEC 286-3.

Application Note

PWC resistors themselves can operate at a maximum temperature of 155°C. For soldered resistors, the joint temperature should not exceed 110°C. This condition is met when the stated power levels at 70°C and recommended pad and trace areas are used. Pad and trace area is defined as the total area of the solder pad plus all copper trace within two squares of the edge of the solder pad. Allowance should be made if smaller areas of copper are used.

A full Application Note on the PWC Series is available.

Ordering Procedure

This product has two valid part numbers:

European (Welwyn) Part Number: PWC2512-2K0JI (2512, 2 kilohms ±5%, Pb-free)

PWC	2 5 1	2 -	2 K 0	JI	
1	2	3	4	56	


1	2	3	4	5	6	
Туре	Size	Anti-Sulphur	Value	Tolerance	Termination	& Packing
PWC	0603	Omit for standard	E24 = 3/4 characters	D = ±0.5%	I = Pb-free,	Standard,
	0805	AS = Anti-sulphur	E96 = 3/4 characters	F = ±1%	PB = SnPb,	Standard
	1206		R = ohms	J = ±5%	0603	5000/reel
	2010		K = kilohms		0805, 1206,	3000/reel
	2512		M = megohms		2010	3000/reel
		-			2512	1800/reel
					T1 = Pb-fre	e. 1K reel

USA (IRC) Part Number: PWC-PWC2512LF-2K00-J

(2512, 2 kilohms ±5%, Pb-free)

All sizes

1000/reel



1	2	3	4	5	6		
Family	Model	Size	Termination	Value	Tolerance	Packing	
PWC	PWC	1206	Omit for SnPb	E24 = 4 characters	D = ±0.5%	Plastic tape	
		2010	LF = Pb-free	E96 = 4 characters	F = ±1%	1206, 2010	3000/reel
		2512		R = ohms	J = ±5%	1200, 2010	
				K = kilohms		2512	1800/reel
				M = megohms			

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability.

All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

www.ttelectronics.com/resistors

BI Technologies IRC Welwyn

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT Electronics:

PWC2512-143RJT1 PWC2010-10K2JT1 PWC2512-7M5FT1 PWC2010-51RJT1 PWC2010-51R1JT1 PWC2010-86R6JT1 PWC2512-5M11FT1 PWC2010-71R5JT1 PWC1206-422KJT1 PWC1206-620KJT1 PWC1206-750KJT1 PWC1206-523KJT1 PWC2512-3M92FT1 PWC2512-4M64FT1 PWC2010-3K4JT1 PWC2512-48R7JT1 PWC2010-75KFT1 PWC2010-88K7FT1 PWC2010-45K3FT1 PWC2010-76K8FT1 PWC2010-7K15JT1 PWC2010-11K3JT1 PWC2010-16K5JT1 PWC2010-6K81JT1 PWC2512-47R5JT1 PWC2010-1K91JT1 PWC2512-1R13JT1 PWC2512-6M98FT1 PWC2512-1M91FT1 PWC2010-23R2JT1 PWC2010-27R4JT1 PWC2512-2M94FT1 PWC2010-866RJT1 PWC2010-2K2JT1 PWC2010-3K74JT1 PWC2010-4K32JT1 PWC2512-6M19FT1 PWC2512-7M15FT1 PWC2010-41R2JT1 PWC2512-5M1FT1 PWC2512-22R6JT1 PWC2010-536RJT1 PWC2010-845RJT1 PWC2512-36RJT1 PWC2512-3M4FT1 PWC2010-30R9JT1 PWC2010-33R2JT1 PWC2010-34RJT1 PWC2512-3M32FT1 PWC2512-4M12FT1 PWC2010-1M82FT1 PWC2010-2M94FT1 PWC2010-4M02FT1 PWC2512-12KFT1 PWC2010-7R5FT1 PWC2010-11RFT1 PWC2010-8K87FT1 PWC2010-11K8FT1 PWC2010-13K7FT1 PWC1206-43K2JT1 PWC2512-27KFT1 PWC2010-1M2FT1 PWC2512-46R4JT1 PWC2512-52R3JT1 PWC1206-162RFT1 PWC1206-205RFT1 PWC1206-215RFT1 PWC2010-7K15FT1 PWC2010-2K15JT1 PWC2010-2K61JT1 PWC2512-12RJT1 PWC2512-18R2JT1 PWC2512-20R5JT1 PWC2512-22R1JT1 PWC2512-3M83FT1 PWC2010-20R5JT1 PWC2010-26R1JT1 PWC2010-21RJT1 PWC2512-2M15FT1 PWC2512-2M43FT1 PWC2010-523KFT1 PWC2010-953KFT1 PWC2010-1M62FT1 PWC2010-2M4FT1 PWC2010-44R2JT1 PWC2512-3M01FT1 PWC2512-887RFT1 PWC2010-62KFT1 PWC2010-1M21FT1 PWC2010-1M87FT1 PWC2010-8R45FT1 PWC2512-24K3FT1 PWC1206-93K1JT1 PWC2512-340RFT1 PWC2512-430RFT1 PWC2512-681RFT1 PWC1206-261KJT1 PWC2512-475RFT1 PWC2010-619RJT1 PWC2010-787RJT1