

### 150KHz, 3A PWM BUCK DC/DC CONVERTER

## **Features**

- Output voltage: 3.3V, 5V, 12V and adjustable output version
- Adjustable version output voltage range, 1.23V to  $37V\pm4\%$
- 150KHZ <u>+</u>15% fixed switching frequency
- Voltage mode non-synchronous PWM control
- Thermal-shutdown and current-limit protection
- ON/OFF shutdown control input
- Operating voltage can be up to 40V
- Output load current: 3A
- Low power standby mode
- Built-in switching transistor on chip
- Lead Free packages: TO263-5L and TO220-5L(R)
- TO263-5L and TO220-5L(R): Available in "Green" Molding Compound (No Br, Sb)
- Lead Free Finish/RoHS Compliant (Note 1)

## **General Description**

The AP1501 is a fully integrated step-down DC/DC converter, with the ability to drive 3A load without the need of additional driver components. The AP1501 operates at a switching frequency of 150KHZ enabling the use of small size filter components. As a result, board space is reduced and BOM costs are lowered.

The AP1501 has integrated the shutdown function that allows standby mode to be activated via an external logic signal input. The internal compensation facilitates feedback control for line and load regulation without the need of an external circuitry. The AP1501 has a built-in Thermal shutdown and Current Limit function to prevent damage from high operating temperature and high current operating to the output switch.

Additional features include a guaranteed +/- 4% tolerance on the output voltage under specified input and output load conditions, and +/- 15% on oscillator frequency. The AP1501 offers both fixed and a Adjustable output voltages. For fixed outputs the AP1501 supports 3.3V, 5.0V and 12V. The package options available are standard 5-lead TO263 and TO220(R) packages.

## **Applications**

- Simple High-efficiency step-down regulator
- On-card switching regulators
- Positive to negative converter

# **Ordering Information**

AP1501 - <u>XX XXX X</u> - X								
	Output version	Package	Lead Free	Packing				
	Blank : Adjustable	K5 : TO263-5L	L : Lead Free	U : Tube				
	33 : 3.3V	T5 : TO220-5L	G : Green	13 : Tape & Reel				
	50 : 5.0V	T5R : TO220-5L(R)						
	12 : 12V							


ADAEAA

		Package Packaging		Tube		13" Tape and Reel		
	Device	Code	(Note 2)	Quantity	Part Number Suffix	Quantity	Part Number Suffix	
<b>Pb</b>	AP1501-XXK5L-U	K5	TO263-5L	50	-U	NA	NA	
<b>Pb</b>	AP1501-XXK5L-13	K5	TO263-5L	NA	NA	800/Tape & Reel	-13	
<b>Pb</b> ,	AP1501-XXK5G-U	K5	TO263-5L	50	-U	NA	NA	
	AP1501-XXK5G-13	K5	TO263-5L	NA	NA	800/Tape & Reel	-13	
	AP1501-XXT5L-U	T5	TO220-5L	50	-U	NA	NA	
Pb.	AP1501-XXT5G-U	T5	TO220-5L	50	-U	NA	NA	
	AP1501-XXT5RL-U	T5R	TO220-5L(R)	50	-U	NA	NA	
Ph	AP1501-XXT5RG-U	T5R	TO220-5L(R)	50	-U	NA	NA	

Notes: 1. EU Directive 2002/95/EC (RoHS). All applicable RoHS exemptions applied, see EU Directive 2002/95/EC Annex Notes.
 Pad layout as shown on Diodes Inc. suggested pad layout document AP02001, which can be found on our website at <a href="http://www.diodes.com/datasheets/ap02001.pdf">http://www.diodes.com/datasheets/ap02001.pdf</a>.



## **Pin Assignments**




## **Pin Descriptions**

Name	Description	
V <sub>IN</sub>	Operating voltage input	
Output	Output Switching output	
Gnd Ground		
FB	Output voltage feedback control	
SD	ON/OFF shutdown	



# Block Diagram



# **Absolute Maximum Ratings**

Symbol	Parameter	Rating	Unit
ESD MM	Machine Model ESD Protection	400	V
Vcc	Supply Voltage	+45	V
V <sub>SD</sub>	ON/OFF Pin input Voltage	-0.3 to +40	V
V <sub>FB</sub>	Feedback Pin Voltage	-0.3 to +40	V
V <sub>OUT</sub>	Output Voltage to Ground	-1	V
PD	Power Dissipation	Internally limited	W
T <sub>ST</sub>	Storage Temperature	-65 to +150	°C
TJ	Operating Junction Temperature	-20 to +125	°C
T <sub>MJ</sub>	Maximum Junction Temperature	150	°C



## **Recommended Operating Conditions**

Symbol	Parameter	Rating	Units	
V <sub>OP</sub>	Operating Voltage	4.5 to 40	V	
T <sub>A</sub>	Operating Ambient Temperature	-20 to 85	°C	

## Electrical Characteristics (All Output Voltage Versions)

Unless otherwise specified,  $V_{IN} = 12V$  for 3.3V, 5V, adjustable version and  $V_{IN} = 24V$  for the 12V version.  $I_{LOAD} = 0.5A$ Specifications with **boldface type** are for full operating temperature range, the other type are for  $T_J = 25^{\circ}C$ .

Symbol	Parameter		Conditions	Min	Тур.	Max	Unit	
I <sub>FB</sub>	Feedback Bias Current		V <sub>FB</sub> = 1.3V (Adjustable version only)		40	60 <b>100</b>	nA	
Fosc	Oscillator Frequency			127 <b>110</b>	150	173 <b>173</b>	KHZ	
$V_{\text{SAT}}$	Saturation Voltage		I <sub>OUT</sub> = 3A No outside circuit V <sub>FB</sub> = 0V force driver on		1.3	1.4 <b>1.5</b>	V	
DC	Max. Duty C Min. Duty cy		$V_{FB} = 0V$ force driver on $V_{FB} = 12V$ force driver off		100 0		%	
I <sub>CL</sub>	Current Limit		Peak current no outside circuit V <sub>FB</sub> = 0V force driver on	3.6	4.0	5.5 <b>6.5</b>	A	
١L	O(100) = O(100) = O(100)		No outside circuit $V_{FB}$ = 12V force driver off (Note 3)			200	uA	
	Output = -1 Current		$V_{\rm IN} = 40V$		2	60	mA	
Ι <sub>Q</sub> Ι <sub>STBY</sub>	Quiescent Current Standby Quiescent Current		$V_{FB} = 12V$ force driver off ON/OFF pin = 5V $V_{IN} = 40V$		5 150	10 250 <b>350</b>	mA uA	
V <sub>IL</sub> V <sub>IH</sub>	ON/OFF pin Logic Input Threshold Voltage		Low (regulator ON) High (regulator OFF)	2.0	1.3	0.6	V	
Ι <sub>Η</sub>	ON/OFF Pin Logic		V <sub>LOGIC</sub> = 2.5V (OFF)		15	25		
ΙL	ON/OFF Pin Input Current		$V_{LOGIC} = 0.5V$ (ON)		0.02	5	uA	
θ <sub>JA</sub>	Thermal Resistance		TO263-5L (Note 4)		37		°C/W	
JA			TO220-5L(R) (Note 4)		31		0, 11	
θ <sub>JC</sub>	Thermal Resistance Junction to Case		TO263-5L (Note 4)		6		- °C/W	
O <sup>JC</sup>			TO220-5L(R) (Note 4)		5			

Notes: 3. Feedback pin removed from output and connected to 0V to force the output transistor switch ON. Feedback pin removed from output and connected to 12V for the 3.3V, 5V, and the ADJ. version, and 15V for the 12V version, to force the output transistor switch OFF.

4. Test condition: Device mounted with copper area of approximately 3  $in^2$ ,1oz, no air flow.



## 150KHz, 3A PWM BUCK DC/DC CONVERTER

# Electrical Characteristics (Continued)

	Symbol	Parameter	Conditions	V <sub>Min</sub>	Тур.	V <sub>Max</sub>	Unit
AP1501-ADJ	$V_{FB}$	Output Feedback	$\begin{array}{l} 4.5V \leq V_{\text{IN}} \leq 40V \\ 0.2A \leq I_{\text{LOAD}} \leq 3A \\ V_{\text{OUT}} \text{ programmed for } 3V \end{array}$	1.193 <b>1.18</b>	1.23	1.267 <b>1.28</b>	V
	η	Efficiency	$V_{IN} = 12V, I_{LOAD} = 3A$		73		%
AP1501-3.3V	V <sub>OUT</sub>	Output Voltage	$\begin{array}{l} 4.75 V \leq V_{\text{IN}} \leq 40 V \\ 0.2 A \leq I_{\text{LOAD}} \leq 3 A \end{array}$	3.168 <b>3.135</b>	3.3	3.432 <b>3.465</b>	V
1001 0.00	η	Efficiency	$V_{IN} = 12V, I_{LOAD} = 3A$		73		%
AP1501-5V	V <sub>OUT</sub>	Output Voltage	$7V \le V_{IN} \le 40V$ $0.2A \le I_{LOAD} \le 3A$	4.8 <b>4.75</b>	5	5.2 <b>5.25</b>	V
AI 1001-01	η	Efficiency	$V_{IN} = 12V, I_{LOAD} = 3A$		80		%
AP1501-12V	V <sub>OUT</sub>	Output Voltage	$15V \le V_{IN} \le 40V$ $0.2A \le I_{LOAD} \le 3A$	11.52 <b>11.4</b>	12	12.48 <b>12.6</b>	V
A 1001-120	η	Efficiency	$V_{IN} = 15V, I_{LOAD} = 3A$		90		%


#### Specifications with **boldface type** are for full operating temperature range, the other type are for $T_J = 25^{\circ}C$ .



## 150KHZ, 3A PWM BUCK DC/DC CONVERTER

## **Typical Performance Characteristics**


**Typical Performance Characteristics** 




#### Efficiency 100 95 3A Load 90 85 80 75 3.3\ 70 65 30 35 40 8 10 15 20 25 JUNCTION TEMPERATURE( °C)


EFFICIENCY (%)

#### Switch Saturation Voltage










**Switch Current Limit** 









## 150KHz, 3A PWM BUCK DC/DC CONVERTER

## Typical Performance Characteristics (Continued)



JUNCTION TEMPERATURE (°C)

**ON/OFF Pin Current (Sinking)** 




### ON/OFF Threshold Voltage


JUNCTION TEMPERATURE (°C)

150.0 120.0  $V_{IN}=40V$   $-40^{\circ}C \le T_{J} \le 125^{\circ}C$ 60.0 30.0 0.0 1.4 5 10 15 20 22 23 24 25 ON/OFF PIN VOLTAGE (V)





Feedback Pin Bias Current









## **Typical Application Circuit**


### (1) Fixed Type Circuit



### (2) Adjustable Type Circuit



(3) Delay Start Circuit









## **Functional Description**

#### **Pin Functions**

#### +V<sub>IN</sub>

This is the positive input supply for the IC switching regulator. A suitable input bypass capacitor must be present at this pin to minimize voltage transients and to supply the switching currents needed by the regulator.

#### Ground

Circuit ground.

#### Output

Internal switch. The voltage at this pin switches between (+V<sub>IN</sub> – V<sub>SAT</sub>) and approximately – 0.5V, with a duty cycle of approximately V<sub>OUT</sub> / V<sub>IN</sub>. To minimize coupling to sensitive circuitry, the PC board copper area connected to this pin should be kept a minimum.

#### Feedback

Senses the regulated output voltage to complete the feedback loop.

#### ON/OFF

Allows the switching regulator circuit to be shutdown using logic level signals thus dropping the total input supply current to approximately 150uA. Pulling this pin below a threshold voltage of approximately 1.3V turns the regulator on, and pulling this pin above 1.3V (up to a maximum of 40V) shuts the regulator down. If this shutdown feature is not needed, the ON/OFF pin can be wired to the ground pin or it can be left open, in either case the regulator will be in the ON condition.

#### **Thermal Considerations**

The AP1501 is available in 5-pin surface mount TO-263 and TO-220.

The TO-220 package needs a heat sink under most conditions. The size of the heat sink depends on the input voltage, the output voltage, the load current and the ambient temperature. The AP1501 junction temperature rises above ambient temperature for a 3A load and different input and output voltages. The data for these curves was taken with the AP1501 (TO-220 package) operating as a buck switching regulator in an ambient temperature of  $25^{\circ}C$  (still air). These temperature rise numbers are all approximate and there are many factors that can affect these temperatures. Higher ambient temperatures require more heat sinking.

The TO-263 surface mount package tab is designed to be soldered to the copper on a printed circuit board. The copper and the board are the heat sink for this package and the other heat producing components, such as the catch diode and inductor. The PC board copper area that the package is soldered to should be at least 0.4 in<sup>2</sup>, and ideally should have 2 or more square inches of 2 oz. Additional copper area improves the thermal characteristics, but with copper areas greater than approximately 6 in<sup>2</sup>, only small improvements in heat dissipation are realized. If further thermal improvements are needed, double sided, multilayer PC boards with large copper areas and/or airflow are recommended.

The AP1501 (TO-263 package) junction temperature rises above ambient temperature with a 2A load for various input and output voltages. This data was taken with the circuit operating as a buck switching regulator with all components mounted on a PC board to simulate the junction temperature under actual operating conditions. This curve can be used for a quick check for the approximate junction temperature for various conditions, but be aware that there are many factors that can affect the junction temperature. When load currents higher than 2A are used, double sided or multilayer PC boards with large copper areas and/or airflow might be needed, especially for high ambient temperatures and high output voltages.

For the best thermal performance, wide copper traces and generous amounts of printed circuit board copper should be used in the board layout. (One exception to this is the output (switch) pin, which should not have large areas of copper.) Large areas of copper provide the best transfer of heat (lower thermal resistance) to the surrounding air, and moving air lowers the thermal resistance even further.


Package thermal resistance and junction temperature rise numbers are all approximate, and there are many factors that will affect these numbers. Some of these factors include board size, shape, thickness, position, location, and even board temperature. Other factors are, trace width, total printed circuit copper area, copper thickness, single or double-sided, multilayer board and the amount of solder on the board. The effectiveness of the PC board to dissipate heat also depends on the size, quantity and spacing of other components on the board, as well as whether the surrounding air is still or moving.

Furthermore, some of these components such as the catch diode will add heat to the PC board and the heat can vary as the input voltage changes. For the inductor, depending on the physical size, type of core material and the DC resistance, it could either act as a heat sink taking heat away from the board, or it could add heat to the board.




## **Marking Information**

### (1) TO263-5L




(2) TO220-5L(R)






## **Package Information**

### (1) Package Type: TO263-5L



### (2) Package Type: TO220-5L






## 150KHz, 3A PWM BUCK DC/DC CONVERTER

## Package Information (Continued)

### (3) Package Type: TO220-5L(R) Mechanical drawing



#### IMPORTANT NOTICE

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Diodes Incorporated does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on our website, harmless against all damages.

#### LIFE SUPPORT

Diodes Incorporated products are not authorized for use as critical components in life support devices or systems without the expressed written approval of the President of Diodes Incorporated.

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

**Diodes Incorporated:** 

 AP1501-K5L-13
 AP1501-K5L-U
 AP1501-33T5RG-U
 AP1501-33T5RL-U
 AP1501-T5RG-U
 AP1501-T5RL-U

 AP1501-33K5L-U
 AP1501-33T5L-U
 AP1501-T5L-U
 AP1501-33K5L-13
 AP1501-50K5L-U
 AP1501-33K5G-U

 AP1501-K5G-13
 AP1501-K5G-U
 AP1501-K5G-U
 AP1501-K5G-U
 AP1501-S0K5L-U
 AP1501-S0K5L-U