

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Freezer BR

Revision date: 02.12.2019

Product code: 146

Page 1 of 7

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Freezer BR

1.2. Relevant identified uses of the substance or mixture and uses advised against**Uses advised against**

Reserved for industrial and professional use.

1.3. Details of the supplier of the safety data sheet

Company name: ITW LLC & Co. KG
Street: Mühlackerstrasse 149
Place: D-75417 Mühlacker
Telephone: ++49(0)7041-96340 Telefax: ++49(0)7041-963429
e-mail: info@itwcp.de
Internet: www.itwcp.de
Responsible Department: Produktsicherheit Mo. - Do. 8.00 - 16.30 Fr. 8.00 - 14.00
Swiss Toxicological Information Centre - Téléphone : +41 44 251 51 51 (in Switzerland dial 145)
United Kingdom : National Poisons Information Service - Phone number : 8448920111
Österreich : Vergiftungsinformationszentrale Vienna - Telefon-Nummer : +43 1 406 43 43
Schweiz : Tox Info Suisse - Telefon-Nummer : +41 44 251 51 51
Italia : Centro Antiveleni, Roma - Numero di telefono : +39 06 305 4343
España : Instituto Nacional de Toxicología - Teléfono : +34 91 562 04 20
Deutschland: ++49(0)7041-96340

1.4. Emergency telephone number:**SECTION 2: Hazards identification****2.1. Classification of the substance or mixture****Regulation (EC) No. 1272/2008**

Hazard categories:

Aerosol: Aerosol 1

Hazard Statements:

Extremely flammable aerosol.

Pressurised container: May burst if heated.

2.2. Label elements**Regulation (EC) No. 1272/2008****Signal word:** Danger**Pictograms:****Hazard statements**

H222

Extremely flammable aerosol.

H229

Pressurised container: May burst if heated.

Precautionary statements

P211

Do not spray on an open flame or other ignition source.

P251

Do not pierce or burn, even after use.

P102

Keep out of reach of children.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Freezer BR

Revision date: 02.12.2019

Product code: 146

Page 2 of 7

- P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
- P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
- P271 Use only outdoors or in a well-ventilated area.

2.3. Other hazards

In case of insufficient ventilation and/or through use, explosive/highly flammable mixtures may develop.

SECTION 3: Composition/information on ingredients**3.2. Mixtures****Hazardous components**

CAS No	Chemical name	Quantity
	EC No	
	Index No	
	REACH No	
	GHS Classification	
75-28-5	isobutane	50-100 %
	200-857-2	601-004-00-0
	Flam. Gas 1; H220	
74-98-6	propane	25-50 %
	200-827-9	601-003-00-5
	Flam. Gas 1; H220	
106-97-8	butane	10-20 %
	203-448-7	601-004-00-0
	Flam. Gas 1; H220	

Full text of H and EUH statements: see section 16.

SECTION 4: First aid measures**4.1. Description of first aid measures****After inhalation**

Provide fresh air.

After contact with skin

After contact with skin, wash immediately with: Water. Change contaminated clothing.

After contact with eyes

Rinse immediately carefully and thoroughly with eye-bath or water.

After ingestion

If swallowed, immediately drink: Water.

4.2. Most important symptoms and effects, both acute and delayed

No data available

4.3. Indication of any immediate medical attention and special treatment needed

No data available

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media**

Carbon dioxide (CO₂). Foam. Extinguishing powder.

Unsuitable extinguishing media

Water with tenside additive. Water.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Freezer BR

Revision date: 02.12.2019

Product code: 146

Page 3 of 7

5.2. Special hazards arising from the substance or mixture

Combustible. Vapours may form explosive mixtures with air. Heating causes rise in pressure with risk of bursting.

5.3. Advice for firefighters

In case of fire: Wear self-contained breathing apparatus.

Additional information

Use water spray jet to protect personnel and to cool endangered containers.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Remove all sources of ignition.

6.2. Environmental precautions

Do not allow to enter into surface water or drains. Explosion hazard.

6.3. Methods and material for containment and cleaning up

Ventilate affected area.

SECTION 7: Handling and storage**7.1. Precautions for safe handling****Advice on safe handling**

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Advice on protection against fire and explosion

Keep away from sources of ignition - No smoking.

7.2. Conditions for safe storage, including any incompatibilities**Requirements for storage rooms and vessels**

Keep container tightly closed. Keep in a cool, well-ventilated place. Keep away from sources of ignition - No smoking.

Hints on joint storage

Do not store together with: Material, rich in oxygen, oxidizing.

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Exposure limits (EH40)**

CAS No	Substance	ppm	mg/m ³	fibres/ml	Category	Origin
106-97-8	Butane	600	1450		TWA (8 h)	WEL
		750	1810		STEL (15 min)	WEL

8.2. Exposure controls**Appropriate engineering controls**

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Protective and hygiene measures

Change contaminated clothing. Wash hands before breaks and after work. When using do not eat or drink.

Eye/face protection

Tightly sealed safety glasses.

Hand protection

DIN EN 374 Tested protective gloves are to be worn: Butyl rubber. For special purposes, it is recommended to

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Freezer BR

Revision date: 02.12.2019

Product code: 146

Page 4 of 7

check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves.

Skin protection

Protective clothing:

Respiratory protection

In case of inadequate ventilation wear respiratory protection.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Physical state:	Aerosol
Colour:	colourless
Odour:	characteristic
Changes in the physical state	
Initial boiling point and boiling range:	-0,5 °C
Flash point:	0 °C
Lower explosion limits:	1,4 vol. %
Upper explosion limits:	9,4 vol. %
Ignition temperature:	365 °C
Vapour pressure: (at 20 °C)	2100 hPa
Vapour pressure: (at 50 °C)	4900 hPa
Density:	0,55 g/cm ³

SECTION 10: Stability and reactivity**10.1. Reactivity**

No data available

10.2. Chemical stability

No data available

10.3. Possibility of hazardous reactions

No data available .

10.4. Conditions to avoid

Keep away from heat. Ignition hazard.

10.5. Incompatible materials

No data available

10.6. Hazardous decomposition products

No data available

SECTION 11: Toxicological information**11.1. Information on toxicological effects**

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Freezer BR

Revision date: 02.12.2019

Product code: 146

Page 5 of 7

Acute toxicity

CAS No	Chemical name				
	Exposure route	Dose	Species	Source	Method
106-97-8	butane				
	inhalation (4 h) gas	LC50 ppm	273000	Rat	GESTIS

SECTION 12: Ecological information

12.3. Bioaccumulative potential

Partition coefficient n-octanol/water

CAS No	Chemical name	Log Pow
75-28-5	isobutane	2,8
74-98-6	propane	2,36
106-97-8	butane	2,89

Further information

Do not allow to enter into surface water or drains.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Advice on disposal

Dispose of waste according to applicable legislation.

Waste disposal number of waste from residues/unused products

160504 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; gases in pressure containers and discarded chemicals; gases in pressure containers (including halons) containing hazardous substances; hazardous waste

Waste disposal number of contaminated packaging

150104 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); metallic packaging

Contaminated packaging

Non-contaminated packages may be recycled. Handle contaminated packages in the same way as the substance itself.

SECTION 14: Transport information

Land transport (ADR/RID)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
 Hazard label: 2.1



Classification code: 5F
 Special Provisions: 190 327 625
 Limited quantity: 1 L
 Transport category: 2

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Freezer BR

Revision date: 02.12.2019

Product code: 146

Page 6 of 7

Tunnel restriction code: D

Other applicable information (land transport)

E0

Inland waterways transport (ADN)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
Hazard label: 2.1



Classification code: 5F
Special Provisions: 190 327 344 625
Limited quantity: 1 L

Other applicable information (inland waterways transport)

E0

Marine transport (IMDG)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
14.4. Packing group: -
Hazard label: 2, see SP63

Special Provisions: 63, 190, 277, 327, 344, 959
Limited quantity: See SP277
EmS: F-D, S-U

Other applicable information (marine transport)

E0

Air transport (ICAO-TI/IATA-DGR)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS, flammable
14.3. Transport hazard class(es): 2.1
Hazard label: 2.1



Special Provisions: A145 A167
Limited quantity Passenger: 30 kg G
IATA-packing instructions - Passenger: 203
IATA-max. quantity - Passenger: 75 kg
IATA-packing instructions - Cargo: 203
IATA-max. quantity - Cargo: 150 kg

Other applicable information (air transport)

E0

: Y203

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Freezer BR

Revision date: 02.12.2019

Product code: 146

Page 7 of 7

14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS: no

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

Restrictions on use (REACH, annex XVII):

Entry 28: isobutane; butane

2004/42/EC (VOC): 50 % (275 g/l)

National regulatory information

Water contaminating class (D): - - not water contaminating

SECTION 16: Other information**Relevant H and EUH statements (number and full text)**

H220	Extremely flammable gas.
H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)