


Description

- Temperature Compensated Crystal Oscillator (TCXO)
- Model IQXT-200-49
- Model Issue number 1

Frequency Parameters

- Frequency 10.0MHz
- Frequency Tolerance $\pm 1.00\text{ppm}$
- Frequency Stability $\pm 0.28\text{ppm}$
- Operating Temperature Range -40.00 to 105.00°C
- Ageing $\pm 0.01\text{ppm}$ max per day, $\pm 1\text{ppm}$ max/year
- Frequency Tolerance (measurement referenced to frequency observed with $T_A=25^\circ\text{C}$, $V_s=3.3\text{V}$, within 30 days after ex-works)
- Frequency Stability: TA varied across the operating temperature range, measurement referenced to frequency observed with $T_A=25^\circ\text{C}$, $V_s=3.3\text{V}$, load=15pF and temperature variable speed less than 2°C per minute.
- Ageing: $T_A=25^\circ\text{C}$, $V_s=3.3\text{V}$ and after 1hr of operation.
- Supply Voltage Variation (measurement referenced to frequency observed with $T_A=25^\circ\text{C}$, V_s varied from 3.13V to 3.47V and load=15pF): $\pm 0.05\text{ppm}$ max
- Load Variation (5% load change measurement referenced to frequency observed with $T_A=25^\circ\text{C}$, $V_s=3.3\text{V}$ and load= 15pF): $\pm 0.05\text{ppm}$ max

Electrical Parameters




- Supply Voltage $3.3\text{V} \pm 5\%$
- Current Draw 10.000mA max
- Current: @ $T_A=25^\circ\text{C}$, $V_s=3.3\text{V}$ and load=15pF

Output Details

- Output Compatibility HCMOS
- Drive Capability 15pF
- Rise and Fall Time 5.0ns max
- Duty Cycle 45/55% max
- Output Voltage Levels (@ $V_s=3.3\text{V}$ and load=15pF):
Output Low (VoL): 0.4V max
Output High (VoH): 2.4V min

Noise Parameters

- Phase Noise (typ @ 25°C):
-85dBc/Hz @ 10Hz
-115dBc/Hz @ 100Hz
-140dBc/Hz @ 1kHz
-150dBc/Hz @ 10kHz
-152dBc/Hz @ 100kHz
-155dBc/Hz @ 1MHz
- Phase Noise (max @ 25°C):
-80dBc/Hz @ 10Hz
-110dBc/Hz @ 100Hz
-135dBc/Hz @ 1kHz
-145dBc/Hz @ 10kHz
-148dBc/Hz @ 100kHz
-150dBc/Hz @ 1MHz


Outline (mm)

Recommended Solder Pad Layout

Sales Office Contact Details:

UK: +44 (0)1460 270200

USA: +1.760.318.2824

 Email: info@iqdfrequencyproducts.com

 Web: www.iqdfrequencyproducts.com

Environmental Parameters

- Storage Temperature Range: -55 to 105°C
- ESD Level:
Human Body Model: Class 2: 2000V to 4000V, JEDEC JS-001-2010
Machine Model: Class B: 200V to 400V, JEDEC JESD22-A115C
- Shock: 100g, 6ms, half sine wave (3 times for each 3 directions X, Y, Z), IEC 68-2-27 Test Ea/Severity 50A
- Vibration: Test Condition: 0.75mm, acceleration 10g, 10Hz~2000Hz, one cycle per 30 min, test 2 hour. (3 times for each 3 directions X, Y, Z). IEC 68-2-06 Test Fc
- RoHS Terminations
- RoHS Reflow Temp 260°C for 30s max

Compliance

- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JEDEC-STD-033): 3

Packaging Details

- Pack Style: Reel Tape & reel in accordance with EIA-481-D
Pack Size: 600
- *Alternative packing option available*

Sales Office Contact Details:

UK: +44 (0)1460 270200

USA: +1.760.318.2824

Email: info@iqdfrequencyproducts.comWeb: www.iqdfrequencyproducts.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IQD Frequency Products:](#)

[LFTCXO085771](#)