

CABLE TYPE
24 AWG TPU-TEAL


ERWPAU7016M005

LENGTH
M005 - 0.5M
M050 - 5M
M250 - 25M

ADDITIONAL CABLE INFORMATION

PHYSICAL CHARACTERISTICS:	
CONDUCTOR SIZE	24AWG 2 PAIR (19/0.12mm) BARE COPPER
INSULATION MATERIAL	POLYOLEFIN
SHIELD/BRAID	TINNED COPPER 85% COVERAGE
JACKET MATERIAL	TPU (TEAL)
CONDUCTOR	ORANGE, ORANGE-WHITE & GREEN, GREEN-WHITE
TAPE	ALUMINUM-POLYESTER

CABLE:	
TEMPERATURE RATING (STORAGE)	-40 / +80°C
TEMPERATURE RATING (OPERATION)	-20 / +50°C
WELD SLAG RESISTANCE	YES, S-300 MOLEX TEST
FREE SUBSTANCE'S	FCKW, SILICONE, AND PB
FIRE PERFORMANCE	IEC60332-1, UL1581
OIL RESISTANCE	ISO6722, UL758/2556



NOTES:

STANDARDS:
PROTECTION:
IP20 RJ45 END
IP67 M12 END

WRAP LABEL:
MARKED WITH P/N, DATE CODE, VOLTAGE & AMPERAGE

ELECTRICAL
ACCORDING TO CAT5e
VOLTAGE RATING: 125V AC/DC
AMPERAGE: 1.5A

QTY	DESCRIPTION	MATERIAL	FINISH
1	LABEL	VINYL	BLACK/YELLOW
1	INSTERT	NYLON	BLACK
4	CONTACTS	COPPER ALLOY	GOLD PLATED
1	HOUSING	BRASS	NICKEL PLATED
1	RJ45 OVERMOLD	TPU	BLACK
1	RJ45 PLUG	POLYCARBONATE	CLEAR
1	O-RING	VITON	RED
-	CABLE	TPU	TEAL

UPDATE OVERMOLD
EC NO: IPG2017-0306
DRWN: MZIELINS 2017/01/12
CHKD: RSTONE 2017/01/12
APPR: BWOODMAN 2015/06/03

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	
	mm	INCH
▽=0	4 PLACES ±---	±---
▽C=0	3 PLACES ±---	±.005
	2 PLACES ±0.05	±.010
	1 PLACE ±0.10	±.020
	ANGULAR ±.5°	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE	
IN/MM	
DRAWN BY	DATE
MZIELINS	2015/05/05
CHECKED BY	DATE
BARDEN	2015/06/04
APPROVED BY	DATE
BWOODMAN	2015/06/03
MATERIAL NO.	---

SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
NTS	INCH	THIRD ANGLE PROJECTION
TITLE		
M12 RECEP./RJ45 4P M12 RECEP./RJ45 ST #24-2TP TEAL PUR CAT5E		
MOLEX INCORPORATED		
DOCUMENT NO.	SHEET NO.	
SD-120108-082	1 OF 1	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		