

SENCITY® OMNI-M cellular / LTE antenna 1399.17.0231

SWA-0827/360/2/0/V

Description

Omni-directional multiband antenna for LTE 800, GSM 900, GSM 1800, GSM/PCS 1900, UMTS, LTE 2300 and 2600
 WLAN 802.11 b/g WiFi 2400 MHz band
 Gain 2 / 3 dBi, vertical polarized antenna
 Ingress protection IP67 (IEC 60529)
 For outdoor and indoor applications

 L-bracket (AISI 316L) for pole or wall mounting scenario included



Product Configuration

Technical Data

Electrical Data

	Band 1	Band 2
Frequency (MHz)	790 - 960	1710 - 2690
VSWR	2	1.9
Impedance (Ohm)	50	50
Gain (dBi)	2	3

Ports

	Port 1
Connector	N, jack (female)
Polarization	vertical

General Data

IMD level 143 dBc at carrier power 2x 30dBm
 Composite Power max (W) 25

Mechanical Data

Dimensions (mm) 263 x 32 (Height x Diameter)
 Weight (kg) 0.4

INCLUDED MOUNTING MATERIAL: Bracket 9091.99.0173 and 2 metal-bands for mast-diameter 25mm - 101mm, all piece parts made of stainless steel

Environmental Data

Environmental conditions outdoor
 Operation temperature (°C) -40 to 85
 Storage temperature (°C) -55 to 85
 Transport temperature (°C) -40 to 85
 IP rating IP67
 RoHS 2011/65/EC compliant
 Lead-free soldered yes
 REACH 2006/1907/EC compliant

LOW TEMPERATURE: IEC 60068-2-1 72h -55°C
 HIGH TEMPERATURE: IEC 60068-2-2 72h +85°C
 HUMIDITY: ETSI EN300-2-4 T4, 1E 144h 95%
 SALT SPRAY: EN 60068-2-11 / GB-T 10125 96h
 MECHANICAL SHOCK: IEC 60721-3-4, 4M5
 VIBRATION: IEC 60721-3-4 30 min/axis random 4M5

SENCITY® OMNI-M cellular / LTE antenna 1399.17.0231

Material Data

Radome colour	RAL 9003 (signal white)
Radome material	Glass Fibre

Related Products

9091.99.0173 L - bracket for omni stick antennas

Related Documents

Mounting instruction	DOC-0000296554
Painting instruction	DOC-0000256180
Security instruction	DOC-0000278984
Outline drawing	DOU-00295553
3D-model	DOC-0000711593

Additional Information

Mounting accessory included