


### Ultrafast recovery - 1200 V diode

Datasheet - production data



#### **Features**

- Ultrafast, soft recovery
- · Very low conduction and switching losses
- High frequency and/or high pulsed current operation
- High reverse voltage capability
- High junction temperature
- ECOPACK<sup>®</sup>2 compliant component for DPAK on demand
- Insulated package: TO-220FPACInsulated voltage: 2000 V<sub>RMS</sub> sine

#### **Description**

The high quality design of this diode has produced a device with low leakage current, regularly reproducible characteristics and intrinsic ruggedness. These characteristics make it ideal for heavy duty applications that demand long term reliability.

Such demanding applications include industrial power supplies, motor control, and similar mission-critical systems that require rectification and freewheeling. These diodes also fit into auxiliary functions such as snubber, bootstrap, and demagnetization applications.

The improved performance in low leakage current, and therefore thermal runaway guard band, is an immediate competitive advantage for this device.

**Table 1. Device summary** 

	· · · · · · · · · · · · · · · · · · ·
Symbol	Value
I <sub>F(AV)</sub>	5 A
V <sub>RRM</sub>	1200 V
T <sub>j</sub> (max)	175 °C
V <sub>F</sub> (typ)	1.25 V
t <sub>rr</sub> (typ)	48 ns

Characteristics STTH512

### 1 Characteristics

Table 2. Absolute ratings (limiting values at 25 °C, unless otherwise stated)

Symbol	Parame	Value	Unit			
$V_{RRM}$	Repetitive peak reverse voltage	Repetitive peak reverse voltage				
	RMS forward current	TO-220AC / TO-220	FPAC	30	Α	
I <sub>F</sub> (RMS)	Rivis forward current	DPAK		10	A	
	Average forward current, $\delta = 0.5$ , square	TO-220AC / DPAK	T <sub>c</sub> = 145° C	5	Α	
I <sub>F(AV)</sub>	wave	TO-220FPAC	T <sub>c</sub> = 105° C	5	A	
I <sub>FRM</sub>	Repetitive peak forward current	t <sub>p</sub> = 5 μs, F = 5 kHz s	$t_p = 5 \mu s$ , $F = 5 kHz square$		Α	
I <sub>FSM</sub>	Surge non repetitive forward current	n repetitive forward current $t_p = 10 \text{ ms Sinusoidal}$			Α	
T <sub>stg</sub>	Storage temperature range	-65 to + 175	°C			
T <sub>j</sub>	Maximum operating junction temperature			175	°C	

Table 3. Thermal resistance

Symbol	Parameter	Value	Unit	1
D	Junction to case	2.5	°C/W	
R <sub>th(j-c)</sub>	TO-220FPAC	5.8	C/VV	

Table 4. Static electrical characteristics

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
I <sub>R</sub> <sup>(1)</sup>	Reverse leakage current	T <sub>j</sub> = 25° C	\/- <b>-</b> \/			5	μA
'R'	Theverse leakage current	T <sub>j</sub> = 125° C	$V_R = V_{RRM}$		3	30	μΛ
		T <sub>j</sub> = 25° C				2.20	
V <sub>F</sub> <sup>(2)</sup>	Forward voltage drop	T <sub>j</sub> = 125° C	I <sub>F</sub> = 5 A		1.30	2.00	V
		T <sub>j</sub> = 150° C			1.25	1.90	

<sup>1.</sup> Pulse test:  $t_p = 5 \text{ ms}$ ,  $\delta < 2\%$ 

To evaluate the conduction losses use the following equation:

$$P = 1.5 \times I_{F(AV)} + 0.08 I_{F^2(RMS)}$$

57

<sup>2.</sup> Pulse test:  $t_p = 380 \mu s$ ,  $\delta < 2\%$ 

STTH512 Characteristics

**Table 5. Dynamic characteristics** 

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
	Reverse recovery time	$I_F = 1 \text{ A, } dI_F/dt = -50 \text{ A/}\mu\text{s,}$ $V_R = 30 \text{ V, } T_j = 25 \text{ °C}$			95	ns
t <sub>rr</sub>	Reverse recovery time	$I_F = 1 \text{ A, } dI_F/dt = -100 \text{ A/}\mu\text{s,}$ $V_R = 30 \text{ V, } T_j = 25 \text{ °C}$		48	70	115
I <sub>RM</sub>	Reverse recovery current	$I_F = 5 \text{ A}, dI_F/dt = -200 \text{ A/µs},$ $V_R = 600 \text{ V}, T_j = 125 \text{ °C}$		11	16	Α
S	Softness factor	$I_F = 5 \text{ A}, dI_F/dt = -200 \text{ A/µs},$ $V_R = 600 \text{ V}, T_j = 125 \text{ °C}$		2		
t <sub>fr</sub>	Forward recovery time	$I_F = 5 \text{ A}$ $dI_F/dt = 50 \text{ A/}\mu\text{s}$ $V_{FR} = 1.5 \text{ x V}_{Fmax}, T_j = 25 \text{ °C}$			400	ns
V <sub>FP</sub>	Forward recovery voltage	$I_F = 5 \text{ A, d}I_F/dt = 50 \text{ A/}\mu\text{s,}$ $T_j = 25 \text{ °C}$		9.5		V


3.0

Figure 3. Relative variation of thermal

Figure 1. Conduction losses versus average

Figure 2. Forward voltage drop versus forward current I<sub>FM</sub>(A) 50 45 40 35 30 25 20 15 10 V<sub>FM</sub>(V) 0.0 0.5 1.0 1.5 2.0 2.5 3.0 3.5 4.0 4.5 5.0

impedance junction to case versus pulse duration  $Z_{th(j-c)}/R_{th(j-c)}$ 1.0 0.9 0.8 0.7 0.6 0.5 0.4 0.2 0.0 1.E-03 1.E-02 1.E-01 1.E+00





Characteristics STTH512






Figure 6. Reverse recovery time versus dl<sub>F</sub>/dt (typical values) t<sub>rr</sub>(ns) dl<sub>F</sub>/dt(A/µs) 


Figure 7. Reverse recovery charges versus dl<sub>F</sub>/dt (typical values)

Qrr(nC)

2000
1800
T<sub>j=125°C</sub>







4/13 DocID12154 Rev 3

STTH512 Characteristics





Figure 13. Thermal resistance junction to ambient versus copper surface under tab




Package information STTH512

### 2 Package information

- Epoxy meets UL94, V0
- Cooling method: by conduction (C)
- Recommended torque values: 0.55 N·m for TO-220AC and TO-220FPAC
- Maximum torque value: 0.7 N⋅m for TO-220AC and TO-220FPAC

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK<sup>®</sup> packages, depending on their level of environmental compliance. ECOPACK<sup>®</sup> specifications, grade definitions and product status are available at: <a href="https://www.st.com">www.st.com</a>. ECOPACK<sup>®</sup> is an ST trademark.

### 2.1 TO-220AC package information



Downloaded from **Arrow.com**.

STTH512 Package information

Table 6. TO-220AC package mechanical data

			Dime	nsions		
Ref.		Millimeters			Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α	4.40		4.60	0.173		0.181
С	1.23		1.32	0.048		0.051
D	2.40		2.72	0.094		0.107
Е	0.49		0.70	0.019		0.027
F	0.61		0.88	0.024		0.034
F1	1.14		1.70	0.044		0.066
G	4.95		5.15	0.194		0.202
H2	10.00		10.40	0.393		0.409
L2		16.40 typ.			0.645 typ.	
L4	13.00		14.00	0.511		0.551
L5	2.65		2.95	0.104		0.116
L6	15.25		15.75	0.600		0.620
L7	6.20		6.60	0.244		0.259
L9	3.50		3.93	0.137		0.154
М		2.60 typ.			0.102 typ.	
Diam. I	3.75		3.85	0.147		0.151

Package information STTH512

# 2.2 TO-220FPAC package information




Figure 15. TO-220FPAC package outline



STTH512 Package information

Table 7. TO-220FPAC package mechanical data

			Dimer	nsions		
Ref.		Millimeters			Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
А	4.40		4.60	0.173		0.181
В	2.50		2.70	0.098		0.106
D	2.50		2.75	0.098		0.108
E	0.45		0.70	0.018		0.027
F	0.75		1.00	0.030		0.039
F1	1.15		1.70	0.045		0.067
G	4.95		5.20	0.195		0.205
G1	2.40		2.70	0.094		0.106
Н	10.00		10.40	0.393		0.409
L2		16.00 Typ.			0.630 Typ.	
L3	28.60		30.60	1.126		1.205
L4	9.80		10.60	0.386		0.417
L6	15.90		16.40	0.626		0.646
L7	9.00		9.30	0.354		0.366
Dia.	3.00		3.20	0.118		0.126



Package information STTH512

### 2.3 DPAK package information

b4 Thermal pad L2 D1 D Н <u>A2</u> **√**Gauge plane

Figure 16. DPAK package outline

Note:

This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.

10/13 DocID12154 Rev 3




STTH512 Package information

Table 8. DPAK package mechanical data

				Dimensions		
Ref.		Millimeters			Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α	2.18		2.40	0.085		0.094
A1	0.90		1.10	0.035		0.043
A2	0.03		0.23	0.001		0.009
b	0.64		0.90	0.025		0.035
b4	4.95		5.46	0.194		0.214
С	0.46		0.61	0.018		0.024
c2	0.46		0.60	0.018		0.023
D	5.97		6.22	0.235		0.244
D1	4.95		5.60	0.194		0.220
E	6.35		6.73	0.250		0.264
E1	4.32		5.50	0.170		0.216
е		2.28			0.090	
e1	4.40		4.70	0.173		0.185
Н	9.35		10.40	0.368		0.409
L	1.00		1.78	0.039		0.070
L2			1.27			0.050
L4	0.60		1.02	0.023		0.040
V2	-8°		+8°	-8°		8°

Figure 17. Footprint (dimensions in mm)





Ordering information STTH512

# 3 Ordering information

**Table 9. Ordering information** 

Order code	Marking	Package	Weight	Base qty	Delivery mode
STTH512D	STTH512D	TO-220AC	1.86 g	50	Tube
STTH512FP	STTH512FP	TO-220FPAC	1.9 g	50	Tube
STTH512B-TR	STTH512B	DPAK	0.32 g	2500	Tape and reel

## 4 Revision history

Table 10. Document revision history

Date	Revision	Changes
02-Mar-2006	1	First issue.
26-Nov-2014	2	Updated DPAK package information and reformatted to current standard.
24-Feb-2016	3	Updated DPAK package information and reformatted to current standard.

#### **IMPORTANT NOTICE - PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2016 STMicroelectronics – All rights reserved



DocID12154 Rev 3 13/13