


www.vishay.com

## Vishay Semiconductors

# Optocoupler, Phototransistor Output, AC Input




#### **DESCRIPTION**

The SFH620A (DIP) and SFH6206 (SMD) feature a high current transfer ratio, low coupling capacitance and high isolation voltage. These couplers have a GaAs infrared diode emitter, which is optically coupled to a silicon planar phototransistor detector, and is incorporated in a plastic DIP-4 or SMD package.

The coupling devices are designed for signal transmission between two electrically separated circuits. The couplers are end-stackable with 2.54 mm lead spacing. Creepage and clearance distances of > 8 mm are achieved with option 6. This version complies with IEC 60950 (DIN VDE 0805) for reinforced insulation to an operation voltage of 400  $V_{\rm RMS}$  or DC.

ODDEDING INFORMATION

#### **FEATURES**





- Isolation test voltage, 5300 V<sub>RMS</sub>
- High collector emitter voltage, V<sub>CEO</sub> = 70 V
- Low saturation voltage
- Fast switching times
- Low CTR degradation
- Temperature stable
- Low coupling capacitance
- End-stackable, 0.100" (2.54 mm) spacing
- High common-mode interference immunity
- Material categorization: for definitions of compliance please see <a href="https://www.vishay.com/doc?99912"><u>www.vishay.com/doc?99912</u></a>

#### AGENCY APPROVALS

The safety application model number covering all products in this datasheet is SFH620A and SHF6206. This model number should be used when consulting safety agency documents.

- UL1577, file no. E52744 system code H, double protection
- CSA 93751
- BSI EN 60950, EN 60065
- DIN EN 60747-5-5 (VDE 0884-5), available with option 1
- CQC GB8898-2011, GB4943.1-2011

ORDERING INFO	RMATION							
S F H PART	6 2 0 NUMBER		TR PACKAG	# # GE OPTION	TAPE AND REEL Option			
AGENCY CERTIFIED/PACKAGE	CTR (%)							
	± 10 mA							
OLITIII ILD/I AOIGAGE	SFH620A			SFH6206				
UL, cUL, BSI	40 to 125	63 to 200	100 to 320	40 to 125	63 to 200	100 to 320		
DIP-4	SFH620A-1	SFH620A-2	SFH620A-3	-	-	-		
DIP-4, 400 mil, option 6	SFH620A-1X006	SFH620A-2X006	SFH620A-3X006	-	-	-		
SMD-4, option 7	-	SFH620A-2X007T (1)	-	-	-	-		
SMD-4, option 9	-	=	-	SFH6206-1T (1)	SFH6206-2T (1)	SFH6206-3T <sup>(1)</sup>		
VDE, UL, CUL, BSI	40 to 125	63 to 200	100 to 320	40 to 125	63 to 200	100 to 320		
DIP-4	SFH620A-1X001	SFH620A-2X001	SFH620A-3X001	-	-	-		
DIP-4, 400 mil, option 6	-	SFH620A-2X016	SFH620A-3X016	-	-	-		
SMD-4, option 7	-	SFH620A-2X017T	-	-	=	-		
SMD-4, option 9	_	-	_	_	SFH6206-2X001T (1)	SFH6206-3X001T (1)		

#### **Notes**

Rev. 2.3, 31-Aug-15

- Additional options may be possible, please contact sales office.
- (1) Also available in tubes; do not add T to end.

Document Number: 83675



ABSOLUTE MAXIMUM RATINGS (T <sub>amb</sub> = 25 °C, unless otherwise specified)								
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT				
INPUT								
DC forward current		I <sub>F</sub>	± 60	mA				
Surge forward current	t <sub>p</sub> ≤ 10 μs	I <sub>FSM</sub>	± 2.5	Α				
Power dissipation		P <sub>diss</sub>	100	mW				
OUTPUT								
Collector emitter voltage		$V_{CEO}$	70	V				
Emitter collector voltage		$V_{ECO}$	7	V				
Collector current		I <sub>C</sub>	50	mA				
Collector current	t <sub>p</sub> ≤ 1 µs	I <sub>C</sub>	100	mA				
Power dissipation		P <sub>diss</sub>	150	mW				
COUPLER								
Total power dissipation		P <sub>tot</sub>	250	mW				
Storage temperature range		T <sub>stg</sub>	-55 to +150	°C				
Ambient temperature range		T <sub>amb</sub>	-55 to +100	°C				
Junction temperature		Tj	100	°C				
Soldering temperature (1)	max. 10 s, dip soldering distance to seating plane ≥ 1.5 mm	T <sub>sld</sub>	260	°C				

#### Notes

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not
  implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute
  maximum ratings for extended periods of the time can adversely affect reliability.
- (1) Refer to reflow profile for soldering conditions for surface mounted devices (SMD). Refer to wave profile for soldering conditions for through hole devices (DIP).

<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)								
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT	
INPUT								
Forward voltage	$I_F = \pm 60 \text{ mA}$		$V_{F}$		1.25	1.65	V	
Capacitance	$V_R = 0 V, f = 1 MHz$		Co		50		pF	
Thermal resistance			R <sub>thja</sub>		750		K/W	
OUTPUT								
Collector emitter capacitance	V <sub>CE</sub> = 5 V, f = 1 MHz		C <sub>CE</sub>		6.8		pF	
Thermal resistance			R <sub>thja</sub>		500		°C/W	
COUPLER								
Collector emitter saturation voltage	$I_F = \pm 10 \text{ mA}, I_C = 2.5 \text{ mA}$		V <sub>CEsat</sub>		0.25	0.4	V	
Coupling capacitance			C <sub>C</sub>		0.2		pF	
	V <sub>CE</sub> = 10 V	SFH620A-1	I <sub>CEO</sub>		2	50	nA	
		SFH6206-1	I <sub>CEO</sub>		2	50	nA	
Collector emitter leakage current		SFH620A-2	I <sub>CEO</sub>		2	50	nA	
Collector entitler leakage current		SFH6206-2	I <sub>CEO</sub>		2	50	nA	
		SFH620A-3	I <sub>CEO</sub>	•	5	100	nA	
		SFH6206-3	I <sub>CEO</sub>		5	100	nA	

#### Note

Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering
evaluation. Typical values are for information only and are not part of the testing requirements.
 Still air, coupler soldered to PCB or base.



CURRENT TRANSFER RATIO (T <sub>amb</sub> = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
	$V_{CE} = 5 \text{ V}, I_{F} = \pm 10 \text{ mA}$	SFH620A-1	CTR	40		125	%
		SFH6206-1	CTR	40		125	%
		SFH620A-2	CTR	63		200	%
		SFH6206-2	CTR	63		200	%
		SFH620A-3	CTR	100		320	%
1 /		SFH6206-3	CTR	100		320	%
I <sub>C</sub> /I <sub>F</sub>	V <sub>CE</sub> = 5 V, I <sub>F</sub> = ± 1 mA	SFH620A-1	CTR	13	30		%
		SFH6206-1	CTR	13	30		%
		SFH620A-2	CTR	22	45		%
		SFH6206-2	CTR	22	45		%
		SFH620A-3	CTR	34	70		%
			CTR	34	70		%




Fig. 1 - Switching Times Linear Operation (without Saturation)

<b>SWITCHING CHARACTERISTICS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Turn-on time	$R_L = 75 \Omega$ , $I_F = \pm 10 \text{ mA}$ , $V_{CC} = 5 \text{ V}$	t <sub>on</sub>		3		μs
Rise time	$R_L = 75 \Omega$ , $I_F = \pm 10 \text{ mA}$ , $V_{CC} = 5 \text{ V}$	t <sub>r</sub>		2		μs
Turn-off time	$R_L = 75 \Omega$ , $I_F = \pm 10 \text{ mA}$ , $V_{CC} = 5 \text{ V}$	t <sub>off</sub>		2.3		μs
Fall time	$R_L = 75 \Omega$ , $I_F = \pm 10$ mA, $V_{CC} = 5$ V	t <sub>f</sub>		2		μs
Cut-off frequency	$R_L = 75 \Omega$ , $I_F = \pm 10 \text{ mA}$ , $V_{CC} = 5 \text{ V}$	t <sub>ctr</sub>		208		kHz

SAFETY AND INSULATION RATINGS							
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT			
Climatic classification	According to IEC 68 part 1		55/115/21				
Pollution degree	According to DIN VDE 0109		2				
Comparative tracking index	Insulation group IIIa	CTI	175				
Maximum rated withstanding isolation voltage	According to UL1577, t = 1 min	V <sub>ISO</sub>	4470	$V_{RMS}$			
Tested withstanding isolation voltage	According to UL1577, t = 1 s	V <sub>ISO</sub>	5300	V <sub>RMS</sub>			
Maximum transient isolation voltage	According to DIN EN 60747-5-5	V <sub>IOTM</sub>	8000	V <sub>peak</sub>			
Maximum repetitive peak isolation voltage	According to DIN EN 60747-5-5	V <sub>IORM</sub>	890	V <sub>peak</sub>			
Isolation resistance	$T_{amb} = 25  ^{\circ}\text{C},  V_{IO} = 500  \text{V}$	R <sub>IO</sub>	≥ 10 <sup>12</sup>	Ω			
Isolation resistance	$T_{amb} = 100  ^{\circ}\text{C},  V_{IO} = 500  \text{V}$	R <sub>IO</sub>	≥ 10 <sup>11</sup>	Ω			
Output safety power		P <sub>SO</sub>	700	mW			
Input safety current		I <sub>SI</sub>	400	mA			
Input safety temperature		T <sub>S</sub>	175	°C			
Creepage distance	DIP-4		≥ 7	mm			
Clearance distance	DIP-4		≥ 7	mm			
Creepage distance	DIP-4, 400 mil, option 6		≥ 8	mm			
Clearance distance	DIP-4, 400 mil, option 6		≥ 8	mm			
Creepage distance	SMD-4, option 7 and option 9		≥ 7	mm			
Clearance distance	SMD-4, option 7 and option 9		≥ 7	mm			
Insulation thickness		DTI	≥ 0.4	mm			

#### Note

As per DIN EN 60747-5-5, § 7.4.3.8.2, this optocoupler is suitable for "safe electrical insulation" only within the safety ratings. Compliance
with the safety ratings shall be ensured by means of protective circuits.

## TYPICAL CHARACTERISTICS (T<sub>amb</sub> = 25 °C, unless otherwise specified)




Fig. 2 - Current Transfer Ratio (CTR) vs. Temperature




Fig. 5 - Transistor Capacitance (Typ.) vs. Collector Emitter Voltage




Fig. 3 - Output Characteristics (Typ.) Collector Current vs. Collector Emitter Voltage




Fig. 6 - Permissible Pulse Handling Capability Forward Current vs. Pulse Width




Fig. 4 - Diode Forward Voltage (Typ.) vs. Forward Current




Fig. 7 - Permissible Power Dissipation vs. Ambient Temperature







Fig. 8 - Permissible Diode Forward Current vs. Ambient Temperature

### **PACKAGE DIMENSIONS** in millimeters


#### DIP-4, Standard










## DIP-4, Option 6







## SMD-4, Option 7













Rev. 2.3, 31-Aug-15 6 Document Number: 83675

### SMD-4, Option 9










### **PACKAGE MARKING** (example)




### Notes

- Only options 1 and 7 are reflected in the package marking.
- The VDE logo is only marked on option1 parts.
- Tape and reel suffix (T) is not part of the package marking.

#### **SOLDER PROFILES**








Fig. 10 - Lead (Pb)-free Reflow Solder Profile According to J-STD-020 for SMD-8 Devices

Rev. 2.3, 31-Aug-15 **7** Document Number: 83675



## HANDLING AND STORAGE CONDITIONS

ESD level: HBM class 2 Floor life: unlimited

Conditions:  $T_{amb}$  < 30 °C, RH < 85 %

Moisture sensitivity level 1, according to J-STD-020

# **Legal Disclaimer Notice**



Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.