EAO – Your Expert Partner for **Human Machine Interfaces**

10-2J13.1062 - Single-LED

10-2J13.1062 - Single-LED



Attention: The preview is based on a sample product. This can differ from your current configuration.

Other Attributes

Weight 0,002 kg Operating voltage 28 V AC/DC +10 % Operation current $7/14 \text{ mA} \pm 15 \text{ }\%$

Illumination

 $\begin{array}{ccc} \text{Socket} & & \text{T1 } \% \text{ MG} \\ \text{LED colour} & & \text{red} \end{array}$

Optics


Lumi. intensity 330 mcd Dom. wavelength 630 nm

eao 🔳

EAO – Your Expert Partner for **Human Machine Interfaces**

10-2J13.1062 - Single-LED

Dimensions



Additional information

When using AC/DC types with AC operation, slight flickering can occure

Luminous intensity data of the LEDs on direct voltage Electrical and optical data are measured at 25 °C

The specified versions are built with a protection diode (halve wave rectifier) in series and the LED

Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination

For supply voltages above 48 V, it is necessary to use a voltage reduction element (external series resistor or transformer)

eao 🔳

Stand: 27.11.2017