



Search within category

BUY NOW

DESIGN / INSTALL



PLT3S-C186

Pan-Ty® locking tie, standard cross section, 11.5 (292mm) length, metal detectable polypropylene, dark blue.

[Specs](#)
[Packaging Details](#)
[Tools](#)
[★ Add to Favorites](#)
[🛒 Add to BOM](#)

Documents

Material	Metal Impregnated Polypropylene
Application	Metal Detectable
Color	Dark Blue
Cross Section	Standard
Locking Style	Locking
Continuous Use Temperature Range	-40°F (-40°C) - 239°F (115°C)
Plenum-Rated	No
Tool	GTS-E, GS2B, GTH-E, GS4H, PTS, PTH, PPTS, STH2, STS2
Length In (mm)	11.5 (292)
Thickness In (mm)	0.057 (1.4)
Bundle Diameter Range In. (mm)	0.13 (3.3) - 3.00 (76)
CE Compliant	No
CSA Certified	No
Mil. Std. Part Number	NA
UL 62275 Compliant (Type 1, 11)	No
UL 62275 Compliant (Type 2, 21)	No
UL Listed (File #E56854)	No
UL Recognized (File #E56854)	No
Environment	Indoor
Installation Temperature	-4°F (-20°C) - 32°F (0°C)
Min. Loop Tensile Strength (Lbs.)	30
Min. Loop Tensile Strength (N)	133
Operating Temperature	-40°F (-40°C) - 239°F (115°C)
Part Features	One-piece locking wedge for consistent performance and reliability. Low thread force and high loop tensile strength.
Width In (mm)	0.19 (4.8)
RoHS Compliancy Status	Compliant

Min. Order Qty.	100
-----------------	-----

[LEGAL INFORMATION](#) | [PRIVACY POLICY](#) | [CONTACT US](#) | [SITE MAP](#) | [WHERE TO BUY](#) | [JOBS](#) | [UNSUBSCRIBE](#)