







This document is the property of Amphenol Corporation and is addressed to the customer. It is loaned to the customer for their use only. It is not to be reproduced, copied, or disseminated in any form without the prior consent of Amphenol Corporation. If you are not an authorized recipient, you are notified that disclosing the information contained in this document to any other person is strictly prohibited.

Customer drawing



Positions	A	B	C	E	F
15	30.81	24.99	16.92	2.29	19.20
26	39.20	33.30	25.25	2.29	27.70
44	53.04	47.04	38.96	2.29	41.10
62	69.40	63.50	55.42	2.41	57.30




REVISONS				
SNV	ECN	DESCRIPTION	DATE	APPROVED
1	HK--	First Release Drawing	10/13/14	IP
2	HK--	Add pin number	08/31/17	IP

D-SUB TECHNICAL DATA

- SHELL : Steel, 100u" min Tin over 50u" min nickel over 50u" min Copper
- BODY : Glass filled thermoplastic, Flame retardant to UL94 V-0, PBT, Color Black
- CONTACTS : Copper alloy
- Gold flash over 50" min nickel on Contact area
- 100u" min tin over 50" min nickel on Solder area
- SCREWLOCK : Brass, Nickel Plated
- ELECTRICAL : Volt/age Rating : 250 VAC/rms 60Hz
- Current Rating : 3 AMP
- Withstanding Voltage : 1000 VAC/rms 60Hz for 1 minute
- Insulation resistance : 1000 M Ohms
- Contact resistance 20 mOhms max.
- MARKING : Amphenol---(Series No.)
- Commercial reference
- Manufacturing date

PRODUCT CODE

L 7117 HD X XX P VF



DIMENSION SPECIFIED		APPROVAL		DATE	
TOLERANCES	U.S.	DRAWN	Checked	10/09/17	10/09/17
	FRA	Checked	Checked	10/09/17	10/09/17
	Metric				
FOR MATERIALS AND FINISHES SEE NOTES					
REMOVE SHARP EDGES					
DIMENSIONS		TOLERANCES		ANGLE OF PROJECTION	
DB-S	Metric				
Metric	Metric				
DRAWING FILE :					
TITLE					
D-sub Connector,solder cup,HD serial					
SIZE		DRAWING NO.		REV.	
A4	L717HDXXXPVF			2	
SCALE		NONE		SHEET 1 OF 1	

Amphenol

78 Positions