

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0349690140](#)  
**Status:** **Active**  
**Overview:** [Stac64 Single, Multi-Pocket and Hybrid Header System](#)  
**Description:** [Stac64 Hybrid Receptacle Assembly, 14 Circuit, Black, Polarization A](#)

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-34729-020-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Packaging Specification PK-31301-201-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Brochure (PDF)</a>
<a href="#">Product Specification PS-34969-100-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 347290200-AS-CH-000 (PDF)</a>	

**General**

Product Family	Crimp Housings
Series	34969
Application	Automotive, Power, Signal, Wire-to-Board
Comments	Current is dependent on connector size, ambient temperature, blade size and related factors. 2.80mm – 30.0A; 0.64mm - 6.0A. . Polarization A, 10 x 0.64 and 4 x 2.8
Overview	<a href="#">Stac64 Single, Multi-Pocket and Hybrid Header System</a>
Product Name	Stac64
UPC	887191311913

**Physical**

Circuits (maximum)	14
Circuits Detail	21 x 0.64 and 4 x 2.8
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Resin	Modified Polystyrene
Net Weight	7.690/g
Number of Rows	2
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	2.54mm, 5.25mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +105°C

**Electrical**

Current - Maximum per Contact	30.0A, 6.0A
-------------------------------	-------------

**Solder Process Data**

Lead-free Process Capability	N/A
------------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	347290200-AS-CH-000, AS-34729-020-001
Packaging Specification	PK-31301-201-001
Product Specification	PS-34969-100-001
Sales Drawing	SD-34969-010-001



Series image - Reference only

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contained Per -  
D(2021)4569-DC (8  
July 2021)  
bis(2-(2-  
methoxyethoxy)ethyl)  
ether  
Octanoic acid,  
2,2,3,3,4,4,5,5,6,6,7,7,8,8,8-  
pen  
Disodium 3,3'-[[1,1'-  
Biphenyl]-4,4'-  
Diy]bis(Azo)  
1,2-  
Benzenedicarboxylic  
acid, bis(3-  
methylbutyl)  
Dibutyltin-dichloride  
C.I. Direct Black 38  
Disodium-octaborate  
2-ethylhexyl 10-  
ethyl-4,4-dioctyl-7-  
oxo-8-oxa-3,  
2-(2H-Benzotriazol-2-  
yl)-4,6-  
ditertpentylphenol  
Terphenyl,  
hydrogenated  
1,2-  
Benzenedicarboxylic  
acid, dihexyl ester,  
bra  
diisohexyl phthalate  
n-pentyl-  
isopentylphthalate  
Boric acid  
Aluminosilicate  
Refractory Ceramic  
Fibres

**China RoHS**

Zirconia  
Aluminosilicate  
Refractory Ceramic  
Fibr  
Tris(4-nonylphenyl,  
branched and linear)  
phosphi  
Perfluorobutane  
sulfonic acid (PFBS)  
and its sal  
Fluoranthene  
Pyrene  
reaction mass of  
2-ethylhexyl 10-  
ethyl-4,4-dioct  
Perfluorohexane-1-  
sulphonic acid and its  
salts  
Imidazolidine-2-thione  
Lead chromate  
Lead chromate  
molybdate sulfate red  
Potassium  
hydroxyoctaoxidizincatedichromate  
Pentazinc-chromate-  
octahydroxide  
1,2-  
Benzenedicarboxylic  
acid, bis(2-  
methoxyethyl  
1,2-Dimethoxyethane  
1,2-bis(2-  
methoxyethoxy)ethane  
Decabromodiphenylether  
Diboron-trioxide  
Cadmium-oxide  
Cadmium-sulphide  
Lead(II,IV)-oxide  
Lead  
Cadmium  
pyrochlore, antimony  
lead yellow  
Lead-dinitrate  
Lead-titanium-trioxide  
Dioxobis(stearato)trilead  
Lead titanium  
zirconium oxide  
Cyanamide, lead(2+)  
salt (1:1)  
[Phthalato(2-)]dioxotrilead  
Dicyclohexyl-  
phthalate

**Halogen-Free  
Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

**Search Parts in this Series**  
[34969 Series](#)

**Mates With**  
34773 , 34772 Stac64 Hybrid Receptacle  
Connector

**Use With**  
CTX64 Terminal 34803

This document was generated on 10/04/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34969-0140](#)