



Part number		nb of cont.	A	B	C	D	E	G
15 22 006	x601 xxx	006	2.54	6.96	8.89	5.56	4.56	1.19
15 22 008	x601 xxx	008	3.81	8.23	10.16	6.83	5.83	1.19
15 22 010	x601 xxx	010	5.08	9.50	11.43	8.10	7.10	2.46
15 22 012	x601 xxx	012	6.35	10.77	12.70	9.37	8.37	2.46
15 22 014	x601 xxx	014	7.62	12.04	13.97	10.64	9.64	3.73
15 22 016	x601 xxx	016	8.89	13.31	15.24	11.91	10.91	3.73
15 22 018	x601 xxx	018	10.16	14.58	16.51	13.18	12.18	5.00
15 22 020	x601 xxx	020	11.43	15.85	17.78	14.45	13.45	5.00
15 22 022	x601 xxx	022	12.70	17.12	19.05	15.72	14.72	6.27
15 22 024	x601 xxx	024	13.97	18.39	20.32	16.99	15.99	6.27
15 22 026	x601 xxx	026	15.24	19.66	21.59	18.26	17.26	7.54
15 22 028	x601 xxx	028	16.51	20.93	22.86	19.53	18.53	7.54
15 22 030	x601 xxx	030	17.78	22.20	24.13	20.80	19.80	8.81
15 22 032	x601 xxx	032	19.05	23.47	25.40	22.07	21.07	8.81
15 22 034	x601 xxx	034	20.32	24.74	26.67	23.34	22.34	10.08
15 22 036	x601 xxx	036	21.59	26.01	27.94	24.61	23.61	10.08
15 22 038	x601 xxx	038	22.86	27.28	29.21	25.88	24.88	11.35
15 22 040	x601 xxx	040	24.13	28.55	30.48	27.15	26.15	11.35
15 22 042	x601 xxx	042	25.40	29.82	31.75	28.42	27.42	12.62
15 22 044	x601 xxx	044	26.67	31.09	33.02	29.69	28.69	12.62
15 22 046	x601 xxx	046	27.94	32.36	34.29	30.96	29.69	13.89
15 22 048	x601 xxx	048	29.21	33.63	35.56	32.23	31.23	13.89
15 22 050	x601 xxx	050	30.48	34.90	36.83	33.50	32.50	15.16
15 22 052	x601 xxx	052	31.75	36.17	38.10	34.77	33.77	15.16
15 22 054	x601 xxx	054	33.02	37.44	39.37	36.04	35.04	16.43
15 22 056	x601 xxx	056	34.29	38.71	40.64	37.31	36.31	16.43
15 22 058	x601 xxx	058	35.56	39.98	41.91	38.58	37.58	17.70
15 22 060	x601 xxx	060	36.83	41.25	43.18	39.85	38.85	17.70
15 22 062	x601 xxx	062	38.10	42.52	44.45	41.12	40.12	18.97
15 22 064	x601 xxx	064	39.37	43.79	45.72	42.39	41.39	18.97
15 22 066	x601 xxx	066	40.64	45.06	46.99	43.66	42.66	20.24
15 22 068	x601 xxx	068	41.91	46.33	48.26	44.93	43.93	20.24
15 22 070	x601 xxx	070	43.18	47.60	49.53	46.20	45.20	21.51
15 22 072	x601 xxx	072	44.45	48.87	50.80	47.47	46.47	21.51
15 22 074	x601 xxx	074	45.72	50.14	52.07	48.74	47.74	22.78
15 22 076	x601 xxx	076	46.99	51.41	53.34	50.01	49.01	22.78
15 22 078	x601 xxx	078	48.26	52.68	54.61	51.28	50.28	24.05
15 22 080	x601 xxx	080	49.53	53.95	55.88	52.55	51.55	24.05
15 22 082	x601 xxx	082	50.80	55.22	57.15	53.82	52.82	25.32
15 22 084	x601 xxx	084	52.07	56.49	58.42	55.09	54.09	25.32
15 22 086	x601 xxx	086	53.34	57.76	59.69	56.36	55.36	26.59
15 21 088	x601 xxx	088	54.61	59.03	60.96	57.63	56.63	26.59
15 21 090	x601 xxx	090	55.88	60.30	62.23	58.90	57.90	27.86
15 21 092	x601 xxx	092	57.15	61.57	63.50	60.17	59.17	27.86
15 22 094	x601 xxx	094	58.42	62.84	64.77	61.44	60.44	29.13
15 22 096	x601 xxx	096	59.69	64.11	66.04	62.71	61.71	29.13
15 22 098	x601 xxx	098	60.96	65.38	67.31	63.98	62.98	30.40
15 22 100	x601 xxx	100	62.23	66.65	68.58	65.25	64.25	30.40

Performance level	
PL1 : > 500 mating cycles	2
PL2 : > 250 mating cycles	6
PLS4 : min. 0.06µm Au over 0.7+0.2µm PdNi	5

Packaging	
tape & reel with 280 pcs per reel	000
samples	333

	All Dimensions in mm Original Size DIN A3	Scale 1:1	Free size tol.	Ref. Sub.
	All rights reserved Department EL PD	Created by PLMMIG	Inspected by PLMMIG	Standardisation Date 2014-04-14
HARTING Electronics GmbH D-32339 Espelkamp	Title har-flex str. fe. 9.05mm, vacuum cover			State Final Release
	Type TB	Number 1522XXXX601_XXX	Doc-Key / ECM-Nr. 10022447/UGD/002/C 5000005900	Rev. C
				Page 1/1

Find further technical information on the drawing DS 1521 110 03 01