TOSHIBA Field-Effect Transistor Silicon P-Channel MOS Type (U-MOSVI)

SSM3J332R

•Power Management Switch Applications

- 1.8-V drive
- Low ON-resistance: $RDS(ON) = 144 \text{ m}\Omega \text{ (max)} (@VGS = -1.8 \text{ V})$
 - $R_{DS(ON)} = 72.0 \text{ m}\Omega \text{ (max)} (@V_{GS} = -2.5 \text{ V})$
 - RDS(ON) = $50.0 \text{ m}\Omega \text{ (max)} (@VGS = -4.5 \text{ V})$
 - RDS(ON) = $42.0 \text{ m}\Omega \text{ (max)} (@VGS = -10 \text{ V})$

Absolute Maximum Ratings (Ta = 25°C)

Characteristic		Symbol		Rating	Unit	
Drain-Source voltage		VDSS		-30	V	
Gate-Source voltage		V _{GSS}		± 12	V	
Drain current	DC	ID	I _D (Note 1) -6.0		^	
	Pulse	IDP (I	Note 1,2)	-24.0	A	
Power dissipation		PD (Note 3)		1	W	
			t < 10s	2	vv	
Channel temperature		T _{ch}		150	°C	
Storage temperature range		T _{stg}		-55 to 150	°C	

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings.

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling

Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).

Note 1: The channel temperature should not exceed 150°C during use.


Note 2: PW \leq 1ms, Duty \leq 1%


Note 3: Mounted on FR4 board.


 $(25.4 \text{ mm} \times 25.4 \text{ mm} \times 1.6 \text{ mm}, \text{Cu Pad: } 645 \text{ mm}^2)$

Marking

Equivalent Circuit (Top View)







1

Unit: mm

- A

1.0[±]

42 -0.05

⊕ 0.1 ® A

- 	
<u> </u>	BOTTOM VIEW
SOT-23F	1: Gate 2: Source 3: Drain
JEDEC	_
JEITA	_
TOSHIBA	2-3Z1S

Weight: 11 mg (typ.)

2.9 ±0.2

з¢

Electrical Characteristics (Ta = 25°C)


Chara	cteristic	Symbol	Test Conditions		Min	Тур.	Max	Unit
Drain-Source breakdown voltage		V (BR) DSS	I _D = -10 mA, V _{GS} = 0 V		-30	—	—	V
		V (BR) DSX	I _D = -10 mA, V _{GS} = 8 V	(Note 5)	-22			V
Drain cut-off current		IDSS	V _{DS} = -30 V, V _{GS} = 0 V		_		-1	μA
Gate leakage current		IGSS	V _{GS} = ±10 V, V _{DS} = 0 V		_		±1	μA
Gate threshold voltage		Vth	V _{DS} = -3 V, I _D = -1 mA		-0.5	_	-1.2	V
Forward transfer a	admittance	Y _{fs}	V _{DS} = -3 V, I _D = -2.5 A	(Note 4)	5.7	11.3	—	S
Drain–source ON-resistance		I _D = -5.0 A, V _{GS} = -10 V	(Note 4)	_	36.0	42.0	mΩ	
	Decision	ID = -4.0 A, VGS = -4.5 V	(Note 4)	_	42.5	50.0		
	R _{DS} (ON)	I _D = -2.5 A, V _{GS} = -2.5 V	(Note 4)	_	57.5	72.0		
		I _D = -0.5 A, V _{GS} = -1.8 V	(Note 4)	_	76.5	144		
Input capacitance		Ciss	V _{DS} = -15 V, V _{GS} = 0 V f = 1 MHz		_	560	_	
Output capacitance		Coss			_	80	—	pF
Reverse transfer capacitance		Crss			_	65	—	
Switching time	Turn-on time	ton	V _{DD} = -15 V, I _D = -2.0 A		_	15	—	
	Turn-off time	toff	V _{GS} = 0 to -4.5 V, R _G = 10 Ω		_	75	—	ns
Total Gate Charge		Qg			_	8.2	_	
Gate-Source Charge		Qgs1	V _{DD} = -15 V, I _D = -6.0 A, V _{GS} = -4.5 V		_	1.1	_	nC
Gate-Drain Charge		Q _{gd}	VGS4.3 V		_	2.2	—	
Drain-Source forward voltage		VDSF	I _D = 6.0 A, V _{GS} = 0 V	(Note 4)	_	0.90	1.2	V


Note4: Pulse test

Note5: If a forward bias is applied between gate and source, this device enters V(BR)DSX mode. Note that the drain-source breakdown voltage is lowered in this mode.

Switching Time Test Circuit

(a) Test Circuit





Notice on Usage

Let V_{th} be the voltage applied between gate and source that causes the drain current (I_D) to be low (-1 mA for the SSM3J332R). Then, for normal switching operation, V_{GS}(on) must be higher than V_{th}, and V_{GS}(off) must be lower than V_{th}. This relationship can be expressed as: V_{GS}(off) < V_{th} < V_{GS}(on).

Take this into consideration when using the device.


Handling Precaution


When handling individual devices that are not yet mounted on a circuit board, make sure that the environment is protected against electrostatic discharge. Operators should wear antistatic clothing, and containers and other objects that come into direct contact with devices should be made of antistatic materials.


Thermal resistance Rth (ch-a) and power dissipation PD vary depending on board material, board area, board thickness and pad area. When using this device, please take heat dissipation into consideration


© 2010 - 2018	
Toshiba Electronic Devices & Storage Corporation	


TOSHIBA




















TOSHIBA




<u>TOSHIBA</u>





Safe Operating Area



Downloaded from Arrow.com.

TOSHIBA

RESTRICTIONS ON PRODUCT USE

Toshiba Corporation and its subsidiaries and affiliates are collectively referred to as "TOSHIBA". Hardware, software and systems described in this document are collectively referred to as "Product".

- TOSHIBA reserves the right to make changes to the information in this document and related Product without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.
- PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT ("UNINTENDED USE"). Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, lifesaving and/or life supporting medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, and devices related to power plant. IF YOU USE PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT. For details, please contact your TOSHIBA sales representative or contact us via our website.
- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without
 limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile
 technology products (mass destruction weapons). Product and related software and technology may be controlled under the
 applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the
 U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited
 except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.

TOSHIBA ELECTRONIC DEVICES & STORAGE CORPORATION

https://toshiba.semicon-storage.com/