



Neohm | Neohm R

TE Internal #: 5-1622796-3

348 Ω, Thin Film, Precision Resistor, .1 %, 6.3 x 2.3 mm, 2 Termination, Ammo Packed, .25 W, ±15 ppm/°C, Copper Termination, Axial-Leaded, Neohm R

[View on TE.com >](#)

Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Precision Resistor**

Passive Component Dimensions: **6.3 x 2.3 mm**

Number of Terminations: **2**

Packaging Method: **Ammo Packed**

Passive Component Tolerance: **.1 %**

## Features

### Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film

### Configuration Features

Number of Resistors	1
---------------------	---

### Electrical Characteristics

Operating Voltage	250 V
Passive Component Tolerance	.1 %
Resistance Class	Up to 1kΩ
Resistance Value	348 Ω
Power Rating	.25 W

### Body Features

Lead Type	Axial-Leaded
-----------	--------------

### Termination Features

Number of Terminations	2
Termination Area Base Material	Copper

### Dimensions

Passive Component Dimensions	6.3 x 2.3 mm
------------------------------	--------------



### Usage Conditions

Operating Temperature Range	-65 – 155 $^{\circ}\text{C}$
Temperature Coefficient	$\pm 15$ ppm/ $^{\circ}\text{C}$

### Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

### Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260 $^{\circ}\text{C}$

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 2-1676913-6  
YR1 0.1% 1K0



TE Part # 1622796-1  
YR1 0.1% 100K



TE Part # 1622796-2  
YR1 0.1% 100R



TE Part # 1622796-6  
YR1 0.1% 10K




TE Part # 2-1676913-7  
YR1 0.1% 1M0

Also in the Series | **Neohm R**



Eurocard Connectors(1)



Through-Hole Resistors(484)

Customers Also Bought



TE Part #3-640441-9  
09P MTA100 CONN ASSY WHT



TE Part #DTF13-6P  
DEUTSCH DT Headers



TE Part #640456-9  
09P MTA100 HDR ASSY F/L SQ STR



TE Part #2301840-1  
AMPL REC HD20, VERT, 15P, B/L,4-40 S/LOC



TE Part #2-2176327-5  
CRGP 0805 1K0 1%



TE Part #6-6447163-9  
FSN-24A-20



TE Part #4-1623927-3  
CFR16 5% 1R8



## Documents

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_5-1622796-3\\_BA.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_5-1622796-3\\_BA.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_5-1622796-3\\_BA.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[1309350\\_PASSIVE\\_COMPONENT](#)

English