

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results


 Text Search: 'HSEC1.55'

Your search criteria matched only one product, shown below

HSEC1.55



- Shrink ratio of 3:1 insulates a wide range of diameters and irregular shapes, which reduces inventory costs
- Cross-linked UV resistant material improves chemical and temperature resistance
- Hot melt adhesive seals and insulates in one step to speed installation

Part Number	HSEC1.55
RoHS Compliancy Status	Compliant
Part Description	Thick Wall End Caps provide protection for sealing ends of wire or cable
Material	Polyolefin cross-linked with adhesive
Color	Black
Copper Conductor Size Range	#250 - #500 MCM
Cap Length (In.)	3.8
Cap Length (mm)	98.0
Conductor Size Range (mm ²)	120 to 240
Max. Recovered I.D. (In.)	.68
Max. Recovered I.D. (mm)	17.3
Min. Expanded I.D. (In.)	1.58
Min. Expanded I.D. (mm)	40.1
Nominal Recovered Wall Thickness (In.)	.110
Nominal Recovered Wall Thickness (mm)	2.8
Pricing Description	Heat Shrink Thick Adhesive End Cap, 1.6"(40mm)
Shrink Ratio	3:1
Temperature Range	-67°F to 221°F (-55°C to 105°C)
Min. Order UOM	PC
Min. Order Qty.	5
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.