

HUBER+SUHNER® DATA SHEET

Coaxial PCB Connector: 82_MMCX-S50-0-2/111_K

Rev.: D



Description

Straight PCB jack

Interface Standards
SUHNER-MMCX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Board mounting type edge mount
Weight 0.0007 kg

Environmental Data

Operating Temperature -55 °C to 155 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

Centre contact	Copper Beryllium Alloy
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE

Surface Plating

Gold Plating (Nickel underplated)
Gold Plating (Nickel underplated)
Gold Plating (Nickel underplated)

Related Documents

Outline drawing	DOU-00013081
Catalogue drawing	DCA-00013083

Ordering Information

Tape and Reel package	82_MMCX-S50-0-2/111_KL
Bulk 100 pcs package	82_MMCX-S50-0-2/111_KH
Tape and Reel package	82_MMCX-S50-0-2/111_KG
Single package	82_MMCX-S50-0-2/111_KE

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions